



# SSL34F-SSL36F

## Surface Mount Low VF Schottky Rectifiers

Reverse Voltage - 40V -60V

Forward Current - 3.0A

### FEATURES

- Metal silicon junction, majority carrier conduction
- For surface mounted applications
- Low power loss, high efficiency
- High forward surge current capability
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications

### PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Simplified outline SMAF and symbol

### MECHANICAL DATA

- Case: SMAF
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 27mg 0.00095oz

### Absolute Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz resistive or inductive load, for capacitive load, derate by 20 %

Parameter	Symbols	SSL34F	SSL345F	SSL36F	Units
Maximum Repetitive Peak Reverse Voltage	$V_{RRM}$	40	45	60	V
Maximum RMS voltage	$V_{RMS}$	28	21.5	42	V
Maximum DC Blocking Voltage	$V_{DC}$	40	45	60	V
Maximum Average Forward Rectified Current	$I_{(AV)}$	3.0			A
Peak Forward Surge Current, 8.3ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	$I_{FSM}$	80			A
Max Instantaneous Forward Voltage at 3 A	$V_F$	0.45		0.55	V
Maximum DC Reverse Current $T_a = 25^\circ C$ at Rated DC Reverse Voltage $T_a = 100^\circ C$	$I_R$	0.3 5			mA
Typical Junction Capacitance <sup>1)</sup>	$C_j$	450			pF
Typical Thermal Resistance <sup>2)</sup>	$R_{\theta JA}$	40			°C/W
Operating Junction Temperature Range	$T_j$	-55 ~ +125			°C
Storage Temperature Range	$T_{stg}$	-55 ~ +150			°C

1) Measured at 1MHz and applied reverse voltage of 4 V D.C.

2) P.C.B. mounted with 0.2 X 0.2" (5 X 5 mm) copper pad areas.



# SSL34F-SSL36F

## Surface Mount Low VF Schottky Rectifiers

**Characteristic Curves** ( $T_A=25^\circ\text{C}$  unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Forward Characteristic




Fig.4 Typical Junction Capacitance




Fig.5 Maximum Non-Repetitive Peak Forward Surge Current





Fig.6- Typical Transient Thermal Impedance






# SSL34F-SSL36F

## Surface Mount Low VF Schottky Rectifiers


### PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SMAF



### The recommended mounting pad size



### Marking

Type number	Marking code
SSL34F	SSL34
SSL345F	SSL345
SSL36F	SSL36