



Part Number: 1752A

CAT5e+ Patch Bonded-Pair, 4pr, UTP, PVC Jkt, CM

Product Description

CAT5e+ (350MHz), 4-Bonded-Pair, U/UTP-unshielded, CM, Premise Patch cable, 24 AWG Bonded stranded (7x32) tinned copper conductors, polyolefin insulation, PVC jacket, RJ-45 compatible

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	Premise Patch Cable Designed for Attenuation Stability in High Humidity Environments, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Noisy Environments

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	7x32	TC - Tinned Copper, Bonded Strands	4

Conductor Count:	8
Total Number of Pairs:	4
Conductor Size:	24 AWG

Insulation

Material	PO - Polyolefin
Bonded-Pair:	Yes

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outer Jacket Material

Material	Nominal Diameter	Ripcord
PVC - Polyvinyl Chloride	0.220 in	No

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
90 Ohm/km	3 %

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
160 pF/100m	15 pF/ft

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
100 MHz	537.6 ns/100m	25 ns/100m	70 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2.4 dB/100m	65.3 dB	65.3 dB	63.8 dB	60.8 dB	20.0 dB	100 ± 12 Ohm	105 ± 10 Ohm
4 MHz	4.8 dB/100m	56.3 dB	56.3 dB	51.7 dB	48.7 dB	23.0 dB	100 ± 12 Ohm	100 ± 10 Ohm
8 MHz	6.8 dB/100m	51.8 dB	51.8 dB	45.7 dB	42.7 dB	24.5 dB	100 ± 12 Ohm	100 ± 10 Ohm
10 MHz	7.7 dB/100m	50.3 dB	50.3 dB	43.8 dB	40.8 dB	25.0 dB	100 ± 12 Ohm	100 ± 10 Ohm
16 MHz	9.8 dB/100m	47.3 dB	47.3 dB	39.7 dB	36.7 dB	25.0 dB	100 ± 12 Ohm	100 ± 10 Ohm
20 MHz	11.0 dB/100m	45.8 dB	45.8 dB	37.7 dB	34.7 dB	25.0 dB	100 ± 12 Ohm	100 ± 10 Ohm
25 MHz	12.4 dB/100m	44.3 dB	44.3 dB	35.8 dB	32.8 dB	19.0 dB	100 ± 15 Ohm	100 ± 10 Ohm
31.25 MHz	13.9 dB/100m	42.9 dB	42.9 dB	33.9 dB	30.9 dB	19.0 dB	100 ± 15 Ohm	100 ± 10 Ohm
62.5 MHz	20.1 dB/100m	38.4 dB	38.4 dB	27.8 dB	24.8 dB	19.0 dB	100 ± 15 Ohm	100 ± 10 Ohm
100 MHz	26.1 dB/100m	35.3 dB	35.3 dB	23.8 dB	20.8 dB	19.0 dB	100 ± 15 Ohm	100 ± 10 Ohm
155 MHz	33.3 dB/100m	32.5 dB	32.5 dB	19.9 dB	16.9 dB	19.0 dB	100 ± 18 Ohm	100 ± 10 Ohm
200 MHz	38.4 dB/100m	30.8 dB	30.8 dB	17.7 dB	14.7 dB	19.0 dB	100 ± 18 Ohm	100 ± 10 Ohm
250 MHz	43.7 dB/100m	29.3 dB	29.3 dB	15.8 dB	12.8 dB	18.0 dB	100 ± 20 Ohm	100 ± 10 Ohm
300 MHz	48.6 dB/100m	28.2 dB	28.2 dB	14.2 dB	11.2 dB	18.0 dB	100 ± 20 Ohm	100 ± 10 Ohm
310 MHz	49.5 dB/100m	27.9 dB	27.9 dB	13.9 dB	10.9 dB	18.0 dB	100 ± 20 Ohm	100 ± 10 Ohm
350 MHz	53.2 dB/100m	27.2 dB	27.2 dB	12.9 dB	9.9 dB	17.0 dB	100 ± 22 Ohm	100 ± 10 Ohm

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Installation Temp Range:	0°C To +50°C
UL Temp Rating:	75°C
Storage Temp Range:	-20°C To +75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	21 lbs/1000ft
Max Recommended Pulling Tension:	40 lbs
Min Bend Radius/Minor Axis:	1.0 in
Min Bend Radius/Installation:	2.2 in

Standards

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class D Patch
Data Category:	Category 5e
ANSI Compliance:	S-90-661-2012 Category 5e Patch, ANSI/NEMA WC-63.1 Category 5e Patch
Telecommunications Standards:	ANSI/TIA-568-C.2 Category 5e Patch
IEEE Specification:	IEEE 802.3bt Type 1, Type 2, Type 3
Third Party Performance Verification:	Category 5e Patch

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes

EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL 1685 (UL 1581) Vertical Tray
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Footnote
1752A 0101000	Black	C
1752A 010U1000	Black	
1752A 0061000	Blue	C
1752A 006U1000	Blue	
1752A F2V1000	Gray	C
1752A F2VU1000	Gray	
1752A 0051000	Green	C
1752A 005U1000	Green	
1752A 0031000	Orange	C
1752A 003U1000	Orange	
1752A 007U1000	Purple	
1752A 0021000	Red	C
1752A 002U1000	Red	
1752A 0041000	Yellow	C
1752A 004U1000	Yellow	

Footnote:	C - CRATE REEL PUT-UP.
Patent:	https://www.belden.com/resources/patents

Product Notes

Notes:	Print Includes Descending Footage Markings.
--------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.