

This low-profile, board-in connector, with a mounting height of only 4.25mm and a thickness of 2.4mm, is soldered directly onto printed circuit boards. The solder tail of the contact is resilient for easy assembly. The housing lances facilitate insertion of contacts.

- Slim, low-profile design
- Housing lances
- Easy mounting onto printed circuit boards
- Rugged contact construction


## Specifications -

- Current rating: 0.7A AC, DC (AWG #26)
- Voltage rating: 50V AC, DC
- Temperature range: -25°C to +85°C (including temperature rise in applying)
  - electrical current)
- Insulation resistance: 500M  $\Omega$  min.
- Withstanding voltage: 500V AC/minute
- Applicable wire: AWG #30 to #26
- Applicable PC board thickness: 0.6 to 1.2mm
- \* RoHS compliant products are published.
- \* Refer to "General Instruction and Notice when using Terminals and Connectors" at the end of this catalog.
- \* Contact JST for details.

## Standards ·

- Recognized E60389
- GE Certified LR20812

PC board layout (viewed from soldering side) and Assembly layout




Note: 1. Tolerances are non-cumulative: ±0.03mm for all centers.

2. Hole dimensions differ according to the kind of PC board and piercing method. The dimensions above should serve as a guideline. Contact JST for details.

## **SZN CONNECTOR**

Contact



| Model No.      | Applicable wire |       | Insulation O.D. (mm) | O'tu /rool |
|----------------|-----------------|-------|----------------------|------------|
|                | mm <sup>2</sup> | AWG#  | Insulation O.D. (mm) | Q ty/reei  |
| SZN-002T-P0.7K | 0.08~0.13       | 28~26 | 0.8~1.1              | 14,000     |
| SZN-003T-P0.7K | 0.05~0.08       | 30~28 | 0.7~0.9              | 15,000     |
|                |                 |       |                      |            |

Material and Finish


Phosphor bronze, tin-plated (reflow treatment)

RoHS compliance Note: Contact JST for brass products.

| Contact        | Crimping machine |                  |               |                            |  |
|----------------|------------------|------------------|---------------|----------------------------|--|
|                |                  | Crimp applicator | Dies          | Crimp applicator with dies |  |
| SZN-003T-P0.7K | AP-K2N           | MKS-L            | MK/SZN-003-07 | APLMK SZN003-07            |  |
|                |                  | *MKS-SC          | SC/SZN-003-07 | APLSC SZN003-07            |  |

Note: \*Strip-crimp applicator

## Housing



| Circuits | Model No. | Dimens | O'tu /hou |         |
|----------|-----------|--------|-----------|---------|
|          | Model No. | A      | В         | Q'ty/ba |
| 2        | 2P-SZN    | 1.5    | 4.0       | 1,000   |
| 3        | 3P-SZN    | 3.0    | 5.5       | 1,000   |
| 4        | 4P-SZN    | 4.5    | 7.0       | 1,000   |
| 5        | 5P-SZN    | 6.0    | 8.5       | 1,000   |
| 6        | 6P-SZN    | 7.5    | 10.0      | 1,000   |
| 7        | 7P-SZN    | 9.0    | 11.5      | 1,000   |
| 8        | 8P-SZN    | 10.5   | 13.0      | 1,000   |
| 9        | 9P-SZN    | 12.0   | 14.5      | 1,000   |
| 10       | 10P-SZN   | 13.5   | 16.0      | 1,000   |
| 11       | 11P-SZN   | 15.0   | 17.5      | 1,000   |
| 12       | 12P-SZN   | 16.5   | 19.0      | 1,000   |
| 13       | 13P-SZN   | 18.0   | 20.5      | 1,000   |

PA 66, UL94V-0, natural (white)

RoHS compliance