

Axial Power Inductor

AIAP-03



RoHS/RoHS II Compliant



22.9 x φ11.4mm

FEATURES:

- Low cost axial leaded inductors
- High current rating
- Wide inductance range
- Covered with UL heat shrink tubing

APPLICATIONS:

- Power supplies
- Switching circuits
- TV and audio equipment
- Telecommunication devices
- RF and other filters

ELECTRICAL SPECIFICATIONS:

Part No.	L(μH)	Tolerance	DCR(Ω)	I _{DC} (A)	Inductance Code
		(%)	(max)	(max)	
AIAP-03-3R9	3.9	M	0.007	15.50	3R9M
AIAP-03-4R7	4.7	M	0.008	13.90	4R7 M
AIAP-03-5R6	5.6	M	0.011	12.60	5R6 M
AIAP-03-6R8	6.8	M	0.013	11.60	6R8 M
AIAP-03-8R2	8.2	K	0.017	9.89	8R2K
AIAP-03-100	10	K	0.019	8.70	100K
AIAP-03-120	12	K	0.020	8.21	120K
AIAP-03-150	15	K	0.022	7.34	150K
AIAP-03-180	18	K	0.023	6.64	180K
AIAP-03-220	22	K	0.026	6.07	220K
AIAP-03-270	27	K	0.027	5.36	270K
AIAP-03-330	33	K	0.032	4.83	330K
AIAP-03-390	39	K	0.033	4.36	390K
AIAP-03-470	47	K	0.035	3.98	470K
AIAP-03-560	56	K	0.037	3.66	560K
AIAP-03-680	68	K	0.047	3.31	680K
AIAP-03-820	82	K	0.060	3.10	820K
AIAP-03-101	100	K	0.090	2.79	101K
AIAP-03-121	120	K	0.113	2.54	121K
AIAP-03-151	150	K	0.129	2.22	151K
AIAP-03-181	180	K	0.150	1.98	181K
AIAP-03-221	220	K	0.162	1.89	221K
AIAP-03-271	270	K	0.208	1.63	271K
AIAP-03-331	330	K	0.212	1.51	331K
AIAP-03-391	390	K	0.281	1.39	391K
AIAP-03-471	470	K	0.380	1.24	471K
AIAP-03-561	560	K	0.420	1.17	561K
AIAP-03-681	680	K	0.548	1.050	681K
AIAP-03-821	820	K	0.655	0.970	821K
AIAP-03-102	1000	K	0.844	0.870	102K
AIAP-03-122	1200	K	1.04	0.790	122K
AIAP-03-152	1500	K	1.18	0.700	152K
AIAP-03-182	1800	K	1.56	0.640	182K
AIAP-03-222	2200	K	2.00	0.580	222K
AIAP-03-272	2700	K	2.06	0.530	272K
AIAP-03-332	3300	K	2.63	0.470	332K
AIAP-03-392	3900	K	2.75	0.430	392K
AIAP-03-472	4700	K	3.19	0.390	472K
AIAP-03-562	5600	K	3.92	0.359	562K
AIAP-03-682	6800	K	5.69	0.322	682K
AIAP-03-822	8200	K	6.32	0.293	822K
AIAP-03-103	10000	K	7.30	0.266	103K
AIAP-03-123	12000	K	10.0	0.257	123K
AIAP-03-153	15000	K	11.2	0.230	153K

Axial Power Inductor

AIAP-03

 RoHS/RoHS II Compliant



Test Conditions and equipments

Test frequency: 1kHz 0.25Vrms

I_{DC}: 10% inductance drops typical

Operating Temperature

-40°C ~ +125 °C (including self-heating)

Storage Temperature

-40°C ~ +125 °C

PART NUMBER IDENTIFICATION

AIAP-03-



Packing (100pcs / box)

Inductance Code


Please refer to the table above

Tolerance

K: ±10%

M: ±20%

OUTLINE DRAWING:



Dimension: inch/mm

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[AIAP-03-100-K](#) [AIAP-03-101-K](#) [AIAP-03-102-K](#) [AIAP-03-103-K](#) [AIAP-03-120-K](#) [AIAP-03-121-K](#) [AIAP-03-122-K](#)
[AIAP-03-123-K](#) [AIAP-03-150-K](#) [AIAP-03-151-K](#) [AIAP-03-152-K](#) [AIAP-03-153-K](#) [AIAP-03-180-K](#) [AIAP-03-181-K](#)
[AIAP-03-182-K](#) [AIAP-03-220-K](#) [AIAP-03-221-K](#) [AIAP-03-222-K](#) [AIAP-03-270-K](#) [AIAP-03-271-K](#) [AIAP-03-272-K](#)
[AIAP-03-330-K](#) [AIAP-03-331-K](#) [AIAP-03-332-K](#) [AIAP-03-390-K](#) [AIAP-03-391-K](#) [AIAP-03-392-K](#) [AIAP-03-470-K](#)
[AIAP-03-471-K](#) [AIAP-03-472-K](#) [AIAP-03-4R7-K](#) [AIAP-03-560-K](#) [AIAP-03-561-K](#) [AIAP-03-562-K](#) [AIAP-03-5R6-K](#)
[AIAP-03-680-K](#) [AIAP-03-681-K](#) [AIAP-03-682-K](#) [AIAP-03-6R8-K](#) [AIAP-03-820-K](#) [AIAP-03-821-K](#) [AIAP-03-822-K](#)
[AIAP-03-8R2-K](#) [AIAP-03-151K](#) [AIAP-03-390K](#) [AIAP-03-4R7K](#) [AIAP-03-682K](#) [AIAP-03-152K](#) [AIAP-03-331K](#) [AIAP-](#)
[03-271K](#) [AIAP-03-562K](#) [AIAP-03-150K](#) [AIAP-03-221K](#) [AIAP-03-561K](#) [AIAP-03-681K](#) [AIAP-03-270K](#) [AIAP-03-391K](#)
[AIAP-03-472K](#) [AIAP-03-560K](#) [AIAP-03-272K](#) [AIAP-03-122K](#) [AIAP-03-222K](#) [AIAP-03-120K](#) [AIAP-03-180K](#) [AIAP-03-](#)
[220K](#) [AIAP-03-470K](#) [AIAP-03-8R2K](#) [AIAP-03-332K](#) [AIAP-03-6R8K](#) [AIAP-03-820K](#) [AIAP-03-103K](#) [AIAP-03-121K](#)
[AIAP-03-153K](#) [AIAP-03-101K](#) [AIAP-03-822K](#) [AIAP-03-102K](#) [AIAP-03-182K](#) [AIAP-03-392K](#) [AIAP-03-5R6K](#) [AIAP-03-](#)
[100K](#) [AIAP-03-181K](#) [AIAP-03-123K](#) [AIAP-03-471K](#) [AIAP-03-330K](#) [AIAP-03-821K](#) [AIAP-03-680K](#)