



MODEL NO.	* RESISTANCE VALUE Ω
4119-50	50
4119-75	75
4119-93	93
4119-600	600

MATERIALS:

Body and Fittings: Brass, Alloy 360, 1/2 Hard.

Center Contact: Male – Brass, Alloy 360, 1/2 Hard.

Female – Beryllium Copper per Cond. Ht.

Outer Contact: Beryllium Copper, Cond. Ht.

Dielectric: Teflon per L-P-403.

Gasket/Seals: Silicone rubber per zz-r-765, Class 11a, Grade 50.

Finish:

Body and Fittings: Tarnish Resistant.

Center Contact: Male – Gold plated.

Outer Contact: Tarnish Resistant.

Marking: "Pomona Elect. 4119-*" and resistance value marked on label.

Specifications: 2%, 2 Watt, Carbon-film resistor deposited over Ceramic Core.

VSWR: 1.1 Max. from D.C. to 250 MHz.

1.2 Max. from 250 MHz to 500 MHz.

RATINGS:

Operating Temperature: +102°C (+216°F) Max.

ORDERING INFORMATION: Model 4119-*

* = Resistance value (see table above)

All dimensions are in inches. Tolerances (except noted): .xx = ± 0.02 " (.51 mm), .xxx = ± 0.005 " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4119-600](#) [4119-75](#)