受 控

控 SPECIFICATION

Customer:

Applied To:

Product Name: Piezo Buzzer

Model Name: KPR-G2212

Drawing No.: KP3.840.395

Compliance with ROHS(本品符合ROHS指令)

Signature of Approval

Signature of KEPO

Approved by	Checked by	Issued by	Date
Jan -	梅楚性	安全	

宁波凯普电子有限公司



Ningbo Kepo Electronics Co.,Ltd.

宁波东钱湖镇东钱湖工业区宝源路 25 号

TEL:+86-574-88370330 FAX:+86-574-88370329

No.25 Baoyuan road Dongqian Lake, Industry Area, Dongqian town, Ningbo City, China(Post Code:315121)

Sales@chinaacoustic.com

www.chinaacoustic.com

Specification for Buzzer	Page	2/9
	Revision No.	1.0
Model No.: KPR-G2212	Drawing No.	KP3.840.395

CONTENTS

1. Scope

范围

2. General

概要

3. Maximum Rating

额定极限条件

4. Electrical Characteristics

电性能

5. Measuring Method

测试方法

6. Physical Characteristics

机械性能

7. Environmental Characteristics

环境性能

8. Dimensions

尺寸

9. Packaging Standard

包装标准

10. Cautions

警告

11. Cautions for Use

注意事项

12. Revision

履历表

Specification for Buzzer		Page	3/9
		Revision No.	1.0
Model No. :	KPR-G2212	Drawing No.	KP3.840.395

1. 范围 Scope

This product specification is applied to the piezoelectric sounder in alarm systems. Please contact us when using this product for any other applications than described in the above.

本规格书适用于压电式蜂鸣器,通常它用在系统中做报警或提示的蜂鸣器用,如果将该产品用于其它领域,请与我们取得联系。

2. 概要 General

2.1 Out-Diameter : Ø22mm

外径:

Ø22 mm

2.2 Height

: 5.3mm

高度:

5.3 mm

2.3 Weight

: 2.5 gr.

重量:

2.5克

2.4 Case Material/Color:

PBT+20%玻纤/Black

壳体材质/颜色: PBT+20%玻纤/黑

3. 额定极限条件 Maximum Rating

	项目 Item	规格 Specification
3.1	最高输入电压 Maximum input Voltage	30Vp-p Square Wave /max.
3.2	工作温度范围 Operating Temperature Range	-30 ∼ +85℃
3.3	储存温度范围 Storage Temperature Range	-40 ∼ +95°C

Specification for Buzzer		Page	4/9
		Revision No.	1.0
Model No. :	KPR-G2212	Drawing No.	KP3.840.395

4. 电性能 Electrical Characteristics

	项目 Item	规格 Specification
4.1	声压 Sound Pressure Level	85dB at 12Vp-p /4.0KHz/10cm
4.2	容量 Capacitance at 100Hz	14000pF±30%


测试条件参见下项

Refer to next item for measuring method.

5. 测试方法 Measuring Method


5.1 声压测试线路 S.P.L. Measuring Circuit

输入信号:12Vp-p,4.0KHz,方波 Input Signal:12Vp-p,4.0KHZ,Square wave



S.G.: DF1010 振荡器或等同品

S.G.: DF1010 Oscillater or equivalent



5.2 测试环境 Measuring Condition

温度+25±3℃,湿度60±10%R.H.标准测试状态,在没有疑问的场合,可以在温度+5~+35℃,湿度45~85%R.H.的范围内测试.

Part shall be measured under a condition (Temperature :+5 to +35 $\,^{\circ}$ C,Humidity :45 to 85%R.H.)unless the standard condition (Temperature :+25 $\pm 3\,^{\circ}$ C,Humidity :60 \pm 10 %R.H.) is regulated measure.

Specification for Buzzer		Page	5/9
<u>'</u>		Revision No.	1.0
Model No. :	KPR-G2212	Drawing No.	KP3.840.395

6. 机械性能 Physical Characteristics

实验项目	实验条件	实验后规格
Item	Test Condition	Specification
耐冲击性	峰值加速度490m/s ² ,半正弦波,XYZ三个方向各3次冲击实验后,测试声响器.	
Shock	Sounder shall be measured after being applied shock(490m/s2) for each three mutually perpendicular directions to each of 3 times by half sine wave.	符合表1的要求 The measured
耐振动性	振动频率 10~55 Hz,1.5mm 全振幅,XYZ 三个方向各2小时试验后,测试声响器.	value shall meet Table 1.
Vibration Resistant	Sounder shall be measured after being applied vibration of amplitude of 1.5mm with 10 to55Hz band of vibration frequency to each of 3 perpendicular directions for 2 hours.	
可焊性 Solderability	先将声响器的插针浸入松香液 5秒钟,然后浸入+230±5℃熔融的锡槽中3±0.5秒. Lead terminals are immersed in rosin for 5 seconds and then immersed in solder bath of +230±5℃ for 3±0.5 seconds.	插针表面90%以 上被焊锡润湿.(插 针的段面除外) 90% min. lead terminals shall be wet with solder. (Except the edge of terminal)
	Item 耐冲击性 Shock 耐振动性 Vibration Resistant	Item Test Condition 峰值加速度 490m/s², 半正弦波, XYZ三个方向各3次冲击实验后, 测试声响器. Sounder shall be measured after being applied shock(490m/s²) for each three mutually perpendicular directions to each of 3 times by half sine wave.

Specification for Buzzer		Page	6/9
<u>'</u>		Revision No.	1.0
Model No. :	KPR-G2212	Drawing No.	KP3.840.395

7. 环境性能 Environmental Characteristics


	实验项目 Item	实验条件 Test Condition	实验后规格 Specification
7.1	High Temperature Test 高温试验	After being woked in a chamber with +90±2 ℃ for 2h and then being placed in natural condition for 2h, sounder shall be measured. 将产品置于 +90±2 ℃试验箱中,先工作 2小时,然后在正常大气压条件下恢复2小时后,进行测量	
7.2	Low Temperature Test 低温试验	After being woked in a chamber with -40±2 ℃ for 2h and then being placed in natural condition for 2h, sounder shall be measured. 将产品置于 -40±2 ℃试验箱中,先工作 2小时,然后在正常大气压条件下恢复2小时后,进行测量	符合表1的要求 The measured value shall meet
7.3	耐湿性 Humidity	放置于 90%~95% R.H.,温度+40±2℃的环境试验箱内96小时,然后取出,在常温下放置2小时后,测试声响器。 After being placed in a chamber with 90 to 95 %R.H. at +40±2℃ for 96 hours and then being placed in natural condition for 2hours, sounder shall be measured.	Table 1.
7.4	温度循环 Temperature Cycle	先放置于温度-40±2℃的制冷箱内30分钟,然后放置于室温(+20℃)15分钟后,放置于+85±2℃的烘箱内30分钟,再放置于室温(+20℃)15分钟. 经过以上循环5次,在常温下放置2小时后,测试声响器。 After being placed in a chamber at -40±2℃ for 30 minutes, sounder shall be placed at room temperature(+20℃). After 15 minutes at this temperature , sounder shall be placed in a chamber at +85±2℃. After 30 minutes at this temperature, sounder shall be returned to room temperature (+20℃) for 15 minutes. After 5 above cycles, sounder shall be measured after being placed in natural condition for 2 hours.	

表 1 Table 1

项 目	试验后变化量
Item	Specification after test
声压级	初始值±10dB
Sound Pressure Level	Initial Value±10dB

Specification for Buzzer		Page	7/9
'		Revision No.	1.0
Model No. :	KPR-G2212	Drawing No.	KP3.840.395

8. Dimensions



FIRST ANGLE PROJECTION

 \Leftrightarrow

 mm

± 0.5

UNIT :

Tolerance:

Specification for Buzzer		Page	8/9	
	KPR-G2212	Revision No.	1.0	
Model No. :		Drawing No.	KP3.840.395	

9. 包装标准 Packaging Standard

产品的外包装是纸箱,它应该清楚的标明型号,数量,出厂检验批号.在运输及储存的过程中,产品必须不会受到机械损伤.

Each minimum package unit of products shall be in a carton box and it shall be clearly marked with Part Number, quantity and outgoing inspection number.

There shall be no mechanical damage on products during transportation and/or in storage.

10. 警告 Cautions

如果产品使用于下列高可靠性的装置时,请与我们取得联系,以免对人的生命,财产和身体造成损害.

Please contact us before using our products for the undermentioned applications requiring especially high reliability in order to prevent defects which might directly cause damage to other party'slife, body or property(listed below).

- (1)Aircraft equipment 飞行设备
- (2)Aerospace equipment 航天设备
- (3)Undersea equipment 潜水设备
- (4)Medical equipment 医疗设备
- (5)Transportation equipment (automobiles, trains, ships) 交通设施
- (6)Traffic signal equipment 交通信号设备
- (7)Disaster prevention/crime prevention equipment 防灾害/防犯罪设备
- (8)Data-processing equipment 数据处理设备
- (9)Applications of similar complexity or reliability requirements comparable to the applications listed in the above 以及与上述相类似或可靠性要求更高的设备

11. 注意事项 Cautions for Use

11.1 如果产品所承受的机械应力超过规定的值,元件可能被破坏.

The component may be damaged if mechanical stress over this specification is applied.

11.2 请注意保护工作电路不会因失误,跌落和温度变化而产生浪涌电压.

Please pay attention to protect operating circuit from surge voltage provided by something of force such as failing ,shock and temperature changing.

11.3 请注意永远不要给压电声响器施加直流电压.

Please pay attention never to be applied DC voltage to piezo sounder.

11.4 该声响器不适合洗涤,因为它不密封.

Washing of the component is not acceptable. Because it is not sealded.

11.5 在使用烙铁的情况下,应注意烙铁头的温度应该保持在+350℃以下,并且焊接时间控制在3秒内.

In case of using solder iron for soldering, the top of soldering iron's temperature should be kept less than +350 $^{\circ}$ C. Moreover the soldering time should be also kept with in 3seconds.

Specification for Buzzer				Page	Page 9/9	
Model No. : KPR-G2212				Revision No. 1.		
			'R-G2212	Drawing No. KP3.84		.395
12.	Revisio	n				
Rev. No.	DATE	PAGE	DESCRIP	DESCRIPTION		
1.0	2011.11.23	/	primar	у		