

# FLK 40/EZ-DR/ 400/KONFEK - Cable



2289052

<https://www.phoenixcontact.com/us/products/2289052>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Round cable set; connection 1: IDC/FLK socket strip (1x 40-position); connection 2: IDC/FLK socket strip (1x 40-position); cable length: 4 m

## Your advantages

- Unshielded

## Commercial data

Item number	2289052
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	CK2211
Catalog page	Page 567 (C-5-2019)
GTIN	4017918057442
Weight per piece (including packing)	575 g
Weight per piece (excluding packing)	565 g
Customs tariff number	85444290
Country of origin	DE

# FLK 40/EZ-DR/ 400/KONFEK - Cable



2289052

<https://www.phoenixcontact.com/us/products/2289052>

## Technical data

### Product properties

Product type	System cable
--------------	--------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-40 °C ... 70 °C (fixed installation) -10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

### Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Nominal operating mode	100% operating factor
Current (Per path, 50°C)	≤ 1 A (Uncoiled, see derating)
Current (Per path, 70°C)	≤ 0.6 A (Uncoiled, see derating)

### Cable/line

Cable length	4 m
--------------	-----

#### 40X0.14 [PVC]

UL AWM Style	2464/1061
Number of positions	40
Shielded	no
Cable type	40X0.14 [PVC]
Conductor type	Round cable set
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	40x 0.14 mm <sup>2</sup>
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	9.90 mm ±0.4 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)
Smallest bending radius, fixed installation	82 mm
Smallest bending radius, movable installation	155 mm
Max. bending cycles	5000 (at a radius of ≥ 15x outside diameter)

# FLK 40/EZ-DR/ 400/KONFEK - Cable



2289052

<https://www.phoenixcontact.com/us/products/2289052>

Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable)
	VDE 0842, Part 332-1-2 (raw cable)
	IEC 60332-3-22 (raw cable)
	UL VW-1
	CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)
IDC/FLK40 (1)	IDC/FLK40 (1) = black
IDC/FLK40 (2)	IDC/FLK40 (2) = brown
IDC/FLK40 (3)	IDC/FLK40 (3) = red
IDC/FLK40 (4)	IDC/FLK40 (4) = orange
IDC/FLK40 (5)	IDC/FLK40 (5) = yellow
IDC/FLK40 (6)	IDC/FLK40 (6) = green
IDC/FLK40 (7)	IDC/FLK40 (7) = blue
IDC/FLK40 (8)	IDC/FLK40 (8) = violet
IDC/FLK40 (9)	IDC/FLK40 (9) = gray
IDC/FLK40 (10)	IDC/FLK40 (10) = white
IDC/FLK40 (11)	IDC/FLK40 (11) = white-black
IDC/FLK40 (12)	IDC/FLK40 (12) = white-brown
IDC/FLK40 (13)	IDC/FLK40 (13) = white-red
IDC/FLK40 (14)	IDC/FLK40 (14) = white-orange
IDC/FLK40 (15)	IDC/FLK40 (15) = white-yellow
IDC/FLK40 (16)	IDC/FLK40 (16) = white-green
IDC/FLK40 (17)	IDC/FLK40 (17) = white-blue
IDC/FLK40 (18)	IDC/FLK40 (18) = white-violet
IDC/FLK40 (19)	IDC/FLK40 (19) = white-gray
IDC/FLK40 (20)	IDC/FLK40 (20) = brown-black
IDC/FLK40 (21)	IDC/FLK40 (21) = brown-red
IDC/FLK40 (22)	IDC/FLK40 (22) = brown-orange
IDC/FLK40 (23)	IDC/FLK40 (23) = brown-yellow
IDC/FLK40 (24)	IDC/FLK40 (24) = brown-green
IDC/FLK40 (25)	IDC/FLK40 (25) = brown-blue
IDC/FLK40 (26)	IDC/FLK40 (26) = brown-violet
IDC/FLK40 (27)	IDC/FLK40 (27) = brown-gray
IDC/FLK40 (28)	IDC/FLK40 (28) = brown-white
IDC/FLK40 (29)	IDC/FLK40 (29) = green-black
IDC/FLK40 (30)	IDC/FLK40 (30) = green-brown
IDC/FLK40 (31)	IDC/FLK40 (31) = green-red
IDC/FLK40 (32)	IDC/FLK40 (32) = green-orange
IDC/FLK40 (33)	IDC/FLK40 (33) = green-blue
IDC/FLK40 (34)	IDC/FLK40 (34) = green-violet
IDC/FLK40 (35)	IDC/FLK40 (35) = green-gray
IDC/FLK40 (36)	IDC/FLK40 (36) = green-white
IDC/FLK40 (37)	IDC/FLK40 (37) = yellow-black

# FLK 40/EZ-DR/ 400/KONFEK - Cable



2289052

<https://www.phoenixcontact.com/us/products/2289052>

IDC/FLK40 (38)	IDC/FLK40 (38) = yellow-brown
IDC/FLK40 (39)	IDC/FLK40 (39) = yellow-red
IDC/FLK40 (40)	IDC/FLK40 (40) = yellow-orange
Cable type	Cable for one module

## Connection data

### Connection 1

Connection in acc. with standard	based on IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	40
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

### Connection 2


Connection in acc. with standard	based on IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	40
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

## Drawings

Diagram



Maximum permissible current per path in uncoiled state

# FLK 40/EZ-DR/ 400/KONFEK - Cable



2289052

<https://www.phoenixcontact.com/us/products/2289052>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2289052>



### EAC

Approval ID: RU\*-DE.HB\*35.B00385



### UL Listed

Approval ID: FILE E 238705

	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	125 V	1 A	-	-



### cUL Listed

Approval ID: FILE E 238705

	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	125 V	1 A	-	-

### cULus Listed

# FLK 40/EZ-DR/ 400/KONFEK - Cable



2289052

<https://www.phoenixcontact.com/us/products/2289052>

## Classifications

### ECLASS

ECLASS-11.0	27242220
ECLASS-12.0	27242220
ECLASS-13.0	27242220

### ETIM

ETIM 9.0	EC000237
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# FLK 40/EZ-DR/ 400/KONFEK - Cable



2289052

<https://www.phoenixcontact.com/us/products/2289052>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------



# FLK 40/EZ-DR/ 400/KONFEK - Cable

2289052

<https://www.phoenixcontact.com/us/products/2289052>



## Accessories

### KME - Cable marker carrier

0807083

<https://www.phoenixcontact.com/us/products/0807083>



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable ties, cable diameter: > 5 mm, lettering field size: 20 x 8 mm

---

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)