

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1053081212](#)  
**Status:** **Active**  
**Overview:** [Nano-Fit Power Connectors](#)  
**Description:** Nano-Fit Receptacle Housing, TPA Capable, 2.50mm Pitch, Dual Row, 12 Circuits, Black, Glow-Wire Capable

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-105300-100-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Application Specification AS-105300-100-001 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-105308-100-000 (PDF)</a>
<a href="#">Product Specification 1053001000-PS-CH-000 (PDF)</a>	<a href="#">Test Summary 1053000000-TS-000 (PDF)</a>
<a href="#">Product Specification 1053001000-PS-ES-000 (PDF)</a>	<a href="#">Test Summary 1053001000-TS-000 (PDF)</a>
<a href="#">Product Specification 1053001000-PS-JP-000 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification 1053001000-PS-SK-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">105308</a>
Application	Power, Wire-to-Board
Comments	Operating temperature is -40#C to +105#C for tin and -40#C to +115#C for gold
Overview	<a href="#">Nano-Fit Power Connectors</a>
Product Name	Nano-Fit
UPC	889056023757

**Physical**

Circuits (maximum)	12
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.050/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C, -40° to +115°C

**Electrical**

Current - Maximum per Contact	6.5A
-------------------------------	------

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-105300-100-001
Packaging Specification	PK-105308-100-000
Product Specification	1053001000-PS-CH-000, 1053001000-PS-ES-000, 1053001000-PS-JP-000, 1053001000-PS-SK-000, PS-105300-100-001



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)10043-DC (17  
Jan 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[105308](#) Series

**Mates With**

Nano-Fit Vertical Through Hole Headers  
[1053101112](#) , [1053101212](#) , [1053101312](#) ,  
[1053121112](#) , [1053121212](#) , [1053121312](#) .  
 Nano-Fit Right-Angle Through Hole Headers  
[1053141112](#) , [1053141212](#) , [1053141312](#) .  
 Nano-Fit Vertical SMT Headers [1054291112](#)  
 , [1054291212](#) , [1054291312](#) , [1054291412](#)  
 . Nano-Fit Right-Angle SMT Headers  
[1054051112](#) , [1054051212](#) , [1054051312](#)  
 . Nano-Fit Plug Housings [2014441112](#) ,  
[2014441212](#)

**Use With**

Nano-Fit Crimp Terminal [105300](#) . Nano-Fit Pre-Crimped Leads (Gold) [797582129](#) , [797582130](#) . Nano-Fit Pre-Crimped Leads (Tin) [797582139](#) , [797582140](#) . Nano-Fit TPA Retainer [105325](#)

This document was generated on 03/10/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**