

Features at a Glance

RUGGED PRODUCT WITH LONG RANGE BLE CONNECTIVITY

Gather sensor data from the harshest environments and ensure the wireless signal gets through.

MULTIPLE SENSOR INTERFACE OPTIONS FOR ULTIMATE DESIGN CHOICE

Analog (Voltage or Current), digital inputs, dry contact, digital outputs, I2C, UART, SPI, and external sensor power source.

BROAD CERTIFICATION AND APPROVALS

Fully certified for FCC, IC, CE, MIC and ASNZS as well as Bluetooth SIG listing.

OVER-THE-AIR UPDATES AND CLOUD PLATFORM CAPABLE

Stay up to date with OTA capabilities from supporting mobile applications as well as Cloud deployment with integrated support with Laird's Sentrius™ gateways.

PERSONAL SUPPORT FOR YOUR IMPLEMENTATION

Partner with Laird Connectivity's Tier 2 support and engineering to help configure and deploy your application.



Sentrius™ BT610 I/O Sensor + Thermistor Assemblies

Long Range Bluetooth 5 Sensor + Thermistor Cable Assemblies (sold separately)

Laird Connectivity's **Sentrius™ BT610 I/O** Sensor with Bluetooth 5 turns your wired sensors into IP67-rated battery-operated wireless nodes, providing robust, secure, and cloud ready messaging. Leveraging our BL654 module, it provides full Bluetooth 5 capabilities, opening up industrial and equipment monitoring applications.

This pre-canned configuration is designed with control hut monitoring in mind, enabling administrators to remotely monitor the health and status of control huts / houses that store electrical equipment, such as HVAC units.

This configuration enables the user to read and report sensor data into the cloud via Bluetooth connected gateway as well as set alarms and configure the sensors through a mobile app.

- **Two Software Options**
 - Ready-to-deploy Binary Software + Mobile App
 - Application development environment using nRF Connect SDK / Zephyr RTOS SDK for customizable applications
- **Comprehensive Certifications** for FCC, IC, CE, ASNZS, NCC
- **Industrial temperature range** (-40° to +85° C)
- **Industrial IP67 enclosure**
- **Advanced deployment tools** including mobile app (Android and iOS), sensor to cloud ecosystem, and engineering services.
- **Industry-leading support** works directly with our engineers to help customize and deploy your design. Replaceable large capacity battery



HVAC Monitoring



Control Hut Monitoring



Temperature Monitoring

Shared Specifications

Category	Feature	Specification	
Chipset	Bluetooth® 5	Laird BL654 module with Nordic nRF52840	
	Processor	Cortex M4F – 1MB Flash and 256k RAM	
Antenna	Integrated	Laird FlexPIFA	
Interfaces	Wired	Internal Screw Terminal Block for sensor connections Relevant to this focused application: 4x Thermistor inputs <i>See datasheet for more details.</i>	
	Buttons	2x buttons (accessible with cover removed) for reset, configuration, and pairing	
	Magnet switch	1x for pairing	
	LED Indicator	Red/Green indicator visible outside housing for configuration, pairing, and activity indication	
	Battery	3.6V Lithium Thionyl Chloride AA size - replaceable	
Power	Battery	3.6V Lithium Thionyl Chloride AA size - replaceable	
	Software	Configuration	Mobile App – Android & iOS – Configuration and/or sensor data IoT Gateway – Configuration and/or sensor display to Cloud
		OTA Update	Mobile App – Android and iOS – OTA firmware update
Programming	Field accessible 10-pin ARM Cortex micro header (cover removed)		
Regulatory	Approvals	FCC, IC, CE, ASNZS, NCC, and Bluetooth SIG	
Physical	Dimensions	126.5mm x 81.5mm x 40mm	
Environmental	Operating Temp.	-40° to +85°C	
Enclosure	Housing	IP67 moulded Polycarbonate plastic housing with pressure equalising vent and removable cover	
	Tamper Detection	Indication provided when cover is removed during operation	
	Cable Glands	4x M12 waterproof inlets with IP-rated gaskets for wiring to external sensors	
	Plugs	3x M12 waterproof plugs with IP-rated gaskets to cap off inputs where not required	
	Mounting	Screws, Bracket Mounts	
Accessories	Included	Magnet (for external activation of pairing mode)	
Warranty		1 Year	
Customization	Options**	Branding on front label, packaging, or mobile app. Enclosure colors. Custom firmware.	

**Dependent on commercial case

TEMPERATURE SENSOR (133-00719)

The temperature sensor probes enable BT610 to accurately measure and wirelessly monitor temperature with **up to 4** individual probes per BT610

Feature	Specification
Probe Temperature Range	-40°C to +125°C (-40°F to 257°F)
Accuracy	±1°C (±1.8°F)
Number of Probes	1-4 individual sensor probes supported
Temperature Probe Length	2 meters (+/-20 mm)
Temperature Probe Material	SUS 304 stainless steel
Temperature Probe dimensions	40 mm x Ø5 mm
Customization Options*	Temperature cable length

*Dependent on commercial case

ORDERING INFORMATION

Note: Sensor cable assemblies sold **separately**. Order a BT610 I/O Sensor in addition to your chosen sensor assemblies.

Part	Description
450-00121-K1	Sentrius™ BT610 I/O Sensor – including magnet kit
450-00136B	Sentrius™ BT6xx Magnet Kit – Bulk (50x Magnets)

CABLE ASSEMBLIES

Part	Description
133-00719	Sentrius™ BT6xx Thermistor Sensor Cable Assembly
133-00719B	Sentrius™ BT6xx Thermistor Sensor Cable Assembly – BULK Carton 40pcs