



Click [here](#) for the 3D model.

Dimensions	
L	24mm MAX
H	15mm MAX
T	9mm MAX
S	20.3mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	200

General Information	
Series	PMR205/P405
Dielectric	Metallized Paper
Style	Radial
Features	RC Unit not approved
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Construction	Molded
Component Weight	4.5 g
Miscellaneous	Resistor Tolerance: +/-30%. Resistor= 470 Ohms.

Specifications	
Capacitance	0.47 uF
Capacitance Tolerance	20%
Voltage AC	125 VAC
Voltage DC	250 VDC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Insulation Resistance	2.128 GOhms
Safety Class	X2