

# MHLL6060-300

## PHYSICAL DIMENSIONS:



A	60.0[2.362]	+ 1.50[.059]
B	60.0[2.362]	+ 1.50[.059]
C	0.05[.002]	+ 0.01[.0004]
D	0.09[.004]	MAX



## ELECTRICAL CHARACTERISTICS:

Initial Permeability(u') (13.56MHz)	130±20%
Initial Permeability(u'') (13.56MHz)	5 Max

## PRODUCTS SHAPE AND DIMENSIONS



MEASURED BY ANGILENT E4991A , 1Ts .



## NOTES: UNLESS OTHERWISE SPECIFIED

1. OPERATING TEMPERATURE RANGE  $-40^{\circ}\text{C}$  TO  $85^{\circ}\text{C}$ .
2. FLEXIBLE FERRITE SHEET.
3. D IS MEASURED AFTER REMOVING PAPER LINER OF ADHESIVE

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
				<b>Laird</b>			
PROJECT/PART NUMBER:				REV	PART TYPE:	DRAWN BY:	
MHLL6060-300				C	CO-FIRE	QIU	
C	UPDATE U' SPEC AND PERM CURVE	06/24/14	QIU				
B	CHANGE D FROM 0.10	03/06/14	QIU	DATE:	12/30/13	SCALE:	NTS
A	ORIGINAL DRAFT	12/30/13	QIU	CAD #		SHEET:	1 of 1
REV	DESCRIPTION	DATE	INT	MHLL6060-300-C		TOOL #	-

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[MHLL6060-300](#)