



48820-Xiaomi 67W GaN Charger 2C1A



48820/BHR7493EU

67W Max. Fast Charging

Triple-port Output

Compact and Portable

GaN (gallium nitride) material

This charger adopts GaN (gallium nitride) material and is compatible with mainstream digital devices on the market with a maximum output power of 67 W. It is compact and portable with triple-port output.



Specs:

Model	A07ZMEU
Product Size	53 × 28 × 91.1 mm
Color	White
Input	200–240 V~, 50 Hz, 1.8 A
Single-port Output	Type-C 1/Type-C 2: 5.0 V=2.0 A 10.0 W, 5.0 V=3.0 A 9.0 V=3.0 A 11.0 V=6.1 A 67.0 W Max. 12.0 V=3.0 A 15.0 V=3.0 A 20.0 V=3.25 A 65.0 W Type-A: 5.0 V=2.0 A 10.0 W, 5.0 V=3.0 A 9.0 V=2.5 A 10.0 V=2.25 A 12.0 V=1.87 A 22.44 W
Dual-port Output:	Type-C 1 + Type-C 2: 5.0 V=2.0 A 10.0 W, 5.0 V=3.0 A 9.0 V=3.0 A 11.0 V=3.0 A 12.0 V=3.0 A 15.0 V=2.0 A 20.0 V=2.25 A 45.0 W + 5.0 V=2.0 A 10.0 W, 5.0 V=2.4 A 9.0 V=2.0 A 12.0 V=1.5 A 18.0 W Type-C 1 + Type-A: 5.0 V=2.0 A 10.0 W, 5.0 V=3.0 A 9.0 V=3.0 A 11.0 V=3.0 A 12.0 V=3.0 A 15.0 V=2.0 A 20.0 V=2.25 A 45.0 W + 5.0 V=2.0 A 10.0 W, 5.0 V=2.4 A 9.0 V=2.0 A 12.0 V=1.5 A 18.0 W Type-C 2 + Type-A: 5.0 V=2.0 A 10.0 W, 5.0 V=3.0 A Max. Type-C 1 + (Type-C 2 + Type-A) Output: 5.0 V=2.0 A 10.0 W, 5.0 V=3.0 A 9.0 V=3.0 A 11.0 V=3.0 A 12.0 V=3.0 A 15.0 V=2.0 A 20.0 V=2.25 A 45.0 W + (5.0 V=2.0 A 10.0 W, 5.0 V=2.4 A Max.)
Operating Temperature:	0°C to 40°C
Accessory	Charger, Type-C to Type-C cable, user manual, warranty notice