


1

Pushbutton, opaque, mounting hole diameter 15.2 mm, 250 V/0.7 A



Pict.: Screw terminals, red

Technical data

General information

Form of lens protruding lens
Colour of lens see order block
Form of collar round

Dimensions

Diameter of collar 19 mm
Overall height 8.2 mm
Mounting depth 21.5 mm
Mounting hole 15.2 mm

Mechanical design

Mounting ring nut
Terminals see order block
Contact system bridge contact
Contact function momentary
Contact arrangement see order block
Contact materials Ag
Illuminability no
Lamp socket no

Mechanical characteristics

Operating force max. 7.5 N
Operating travel 3 mm
Switching travel NC 1.2 mm
Switching travel NO 2.0 mm
Robustness min. 100 N

Electrical characteristics

Rated voltage AC max. 250 V
Rated current max. 0.7 A
Contact resistance when new max. 50 mΩ
Contact resistance acc. to life max. 300 mΩ

Other specifications

Operating life 25000
Degree of protection from front side IP40 (IP65 with sealing cap)
Ambient temp. operating min. -25 °C
Ambient temp. operating max. +85 °C
Storage temperature min. -40 °C
Storage temperature max. +90 °C
Resistance to constant environment according to IEC 600 68-2-3 and 2-30
Resistance at variable environment according to IEC 600 68-2-14 and 2-33
Weight 7 g
Approvals ENEC T 85/55
Flame class acc. to UL 94 V 0
Hot wire ignition acc. to IEC 60695-2-1 yes

Other Pushb.

Accessories Pushbutton, opaque, mounting hole diameter 15.2 mm, 250 V/0.7 A

Description	Photo	Order no.	Page
Sealing cap, transparent (IP65)		5.52.008.115/0000	
Fixing spanner M 15, M 16		5.58.002.019/0105	5 - 23

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[RAFI:](#)

[1.10.001.001/0301](#) [1.10.001.001/0104](#) [1.10.001.011/0301](#) [1.10.001.001/0205](#) [1.10.001.001/0507](#)
[1.10.001.151/0301](#)