## **DATASHEET - EMR6-F500-G-1**



Error within supply voltage

Status indication

Output relay energized

Status indicator (LED)

Phase sequence relays, 200 - 500 V AC, 50/60 Hz

Part no. EMR6-F500-G-1 Catalog No. 184789 Eaton Catalog No. EMR6-F500-G-1



Ext. 213 (14)			
Technical data			
General			
Standards			IEC/EN 60255-6,
Lifespan, mechanical	Operations	x 10 <sup>6</sup>	30
Climatic proofing			Damp heat, cyclical to IEC 60068-2-30: 24 h cycle, 55° C, 93% relative humidity, 96 l
Ambient temperature			
Operation		°C	
Operating ambient temperature min.		°C	-20
Operating ambient temperature max.		°C	+ 60
Storage		°C	- 40 - 85
Mounting position			As required
Shock resistance			Class 2
Degree of protection			
Terminals			IP20
Enclosures			IP50
Terminal capacities		$mm^2$	
Solid		mm <sup>2</sup>	2 x 2.5
Flexible with ferrule		mm <sup>2</sup>	2 x 2.5/2 x AWG14
Standard screwdriver		mm	5.5 x 0.8
Tightening torque		Nm	0.5 - 0.8
Fixing			Snap fixing, top-hat rail IEC/EN 60715
Contacts			
Rated impulse withstand voltage	$U_{imp}$	V AC	4000
Overvoltage category/pollution degree			III/3
Power supply			
Supply voltage			200 - 500 V AC, 50/60 Hz
Voltage tolerance		x U <sub>c</sub>	0.85 - 1.1
Power consumption		VA	11
Rated frequency	f	Hz	50 - 60
Duty factor		% DF	100
Measuring circuits			
Monitoring voltage	$U_n$	V AC	
Monitoring voltage, min.		V AC	200
Monitoring voltage, max.		V AC	500
Frequency		Hz	
Min. frequency range		Hz	50
Max. frequency range		Hz	60
Frequency		Hz	50 - 60
Frequency		Hz	50 - 60
Measuring cycle		ms	500
Temperature error		%/°C	0.06

0.5

LED, yellow

Red, solid: Phase failure

			Red, flashing: Phase sequence fault
Relay output contacts			
Rated operational voltage	U <sub>e</sub>	V AC	500
Rated operational current	I <sub>e</sub>	Α	
AC-12 at 230 V	I <sub>e</sub>	Α	4
AC-15 with 230 V	I <sub>e</sub>	Α	3
DC-12 at 24 V	l <sub>e</sub>	Α	4
DC-13 at 24 V	I <sub>e</sub>	Α	2
Lifespan, electrical (AC-12/230 V/4 A)	Operations	x 10 <sup>6</sup>	
Lifespan, electrical	Operations	x 10 <sup>6</sup>	0.3
Short-circuit rating			
max. fuse	Fast/gL	Α	10
Electromagnetic compatibility (EMC)			
Electromagnetic compatibility			IEC/EN 60947-6-2
ESD	Air/contact discharge	kV	IEC/EN 61000-4-2 level 3
HF-immunity to radiation			IEC/EN 61000-4-3 level 3
Burst			IEC/EN 61000-4-4 level 3
Surge			IEC/EN 61000-4-5 Level 4

## Design verification as per IEC/EN 61439

Technical data for design verification		
Operating ambient temperature min.	°C	-20
Operating ambient temperature max.	°C	60

IEC/EN 61000-4-6 level 3

## **Technical data ETIM 7.0**

HF-immunity to line-conducted interference

Relays (EG000019) / Phase monitoring relay (EC001441)

Electric engineering, automation, process control engineering / Low-voltage switch technology / Monitoring equipment (low-voltage switch technology) / Asymmetry monitoring equipment (ecl@ss10.0.1-27-37-18-03 [AKF097014])

Type of electric connection		Screw connection
With detachable clamps		No
Rated control supply voltage Us at AC 50HZ	V	200 - 500
Rated control supply voltage Us at AC 60HZ	V	200 - 500
Rated control supply voltage Us at DC	V	0 - 0
Voltage type for actuating		AC
Phase sequence monitoring		Yes
Phase failure detection		Yes
Function under voltage detection		No
Function over voltage detection		No
Phase imbalance monitoring		No
Voltage measurement range	V	200 - 500
Min. adjustable delay-on energization time	s	0
Max. permitted delay-on energization time	s	0
Min. adjustable off-delay time	s	0
Max. permitted off-delay time	s	0
Number of contacts as normally closed contact		0
Number of contacts as normally open contact		0
Number of contacts as change-over contact		2
Width	mm	23
Height	mm	85
Depth	mm	110

##