


M1 Multi Meter

3-in1 for measuring volts, amps or frequency



Advanced Panel Meter (APM)



Overview

Measurement:

- Volts: 0-600 AC or DC
- Amps: 0-5A Direct
0-10,000A via CT
- Frequency: 2Hz-400Hz

Outputs:

- 2x digital open collector
- 1x analogue 4-20mA

Configuration:

- PC Application via USB

Display Options:

- Positive LCD
- Negative LCD



Key Features

- User configurable to measure voltage, current or frequency via APM application.
- User-programmable bar graph and alarms to immediately alert operators when a parameter is out of range.
- 4 character messaging area displays custom messages, alarms and annunciators.
- Interface to other equipment using digital and analogue outputs.
- Two LCD options: Positive (as shown) for use in bright conditions or Negative for use in darker environments.
- Customizable scale, including offset and gain, range (min and max) and linear.
- ***NEW*** T20 point non-linearization scaling for non-linear sensors e.g. thermocouples and pressure transducers.
- ***NEW*** 10 independent alarm set-points can be configured to change the backlight and/or message when input is in or out of range.
- ***NEW*** Configurable digital output delays (control the time output stays open/closed - .5 seconds – 120 seconds).

Go to www.trumeter.com/apm for further information

Specifications

POWER SUPPLY

Input	12-24V AC/DC +/-10%
Max Power	1.6W
Supply Frequency	50-400Hz

ENVIRONMENTAL

Temperature - operating	-10 to +60°C
Temperature - storage	-40 to +70°C
IP rating (from the front)	IP65, NEMA type 4 and NEMA type 12

DISPLAY

User Configurable Backlight Colours	Red, Green, White
-------------------------------------	-------------------

ANALOGUE OUTPUT

Output	4-20 mA
Accuracy	0.50 %
Resolution	0.02 mA

OPEN COLLECTOR OUTPUTS


Max voltage (open collector outputs)	34 VDC
Max current (open collector outputs)	500 mA

CERTIFICATION

CE, RoHS, UL, cUL

MECHANICAL

Dimensions	72mm x 72mm x 53mm [2.83" x 2.83" x 2.09"]
Cutout	68mm x 68mm [2.68" x 2.63"]
Connection Type	Screw Terminals
Wire Gauge	0.8mm ² - 3.3mm ² (18AWG to 12AWG)
Weight	180 grams



Part Numbers

APM-M1-APO	APM M1 Meter Positive LCD
APM-M1-ANO	APM M1 Meter Negative LCD
022128-01	USB Cable

Full specifications available online www.trumeter.com/apm

