Revision: 03-Mar-2020

For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000

1

Vishay General Semiconductor

Surface-Mount Ultrafast Plastic Rectifier

FEATURES

- Glass passivated pellet chip junction
- · Ideal for automated placement
- Ultrafast recovery times for high efficiency
- · Low forward voltage, low power losses
- High forward surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified available - Automotive ordering code: base P/NHE3 or P/NHM3
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

TYPICAL APPLICATIONS

For use in high frequency rectification and freewheeling application in switching mode converters and inverters for consumer, computer, automotive, and telecommunication.

MECHANICAL DATA

Case: SMB (DO-214AA) Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade Base P/N-M3 - halogen-free, RoHS-compliant, commercial grade Base P/NHE3 X - RoHS-compliant and AEC-Q101 gualified

Base P/NHME3_X - halogen-free, RoHS-compliant, and AEC-Q101 gualified

("_X" denotes revision code e.g. A, B,)

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3, M3, HE3, and HM3 suffix meets JESD 201 class 2 whisker test

Document Number: 88587

Polarity: color band denotes cathode end

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise noted)							
PARAMETER	SYMBOL	ES2A	ES2B	ES2C	ES2D	UNIT	
Device marking code		EA	EB	EC	ED		
Maximum repetitive peak reverse voltage	V _{RRM}	50	50 100 150		200	V	
Maximum RMS voltage	V _{RMS}	35	70	105	140	V	
Maximum DC blocking voltage	V _{DC}	50 100 150 200		200	V		
Maximum average forward rectified current at T_L = 110 $^\circ C$	I _{F(AV)}	2.0					
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	50					
Operating junction and storage temperature range	T _J , T _{STG}	-55 to +150					



www.vishay.com





ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS							
I _{F(AV)}	2.0 A						
V _{RRM}	50 V, 100 V, 150 V, 200 V						
I _{FSM}	50 A						
t _{rr}	20 ns						
V _F	0.90 V						
T _J max.	150 °C						
Package	SMB (DO-214AA)						
Circuit configuration	Single						





www.vishay.com

ES2A, ES2B, ES2C, ES2D

Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS ($T_A = 25 \text{ °C}$ unless otherwise noted)								
PARAMETER	TEST CONDITION	SYMBOL	ES2A	ES2B	ES2C	ES2D	UNIT	
Maximum instantaneous forward voltage	2.0 A		V _F ⁽¹⁾	0.90			V	
Maximum DC reverse current at rated		T _A = 25 °C	l n		μA			
DC blocking voltage		T _A = 100 °C	I _R	350				
Max. reverse recovery time	I _F = 0.5 A, I _R = 1.0 A, I _{rr} = 0.25 A		t _{rr}	20			ns	
Maximum reverse recovery time	I _F = 2.0 A, V _R = 30 V,	T _J = 25 °C	+		3	0		20
Maximum reverse recovery time	dI/dt = 50 A/µs, I _r = 10 % I _{RM}	T _J = 100 °C	t _{rr}	50			ns	
Maximum stored charge	I _F = 2.0 A, V _R = 30 V,	T _J = 25 °C	0	10			nC	
Maximum stored charge	dI/dt = 50 A/ μ s, I _r = 10 % I _{RM}	T _J = 100 °C	Q _{rr}		2	5		no
Typical junction capacitance	4.0 V, 1 MHz		CJ		1	8		pF

Note

⁽¹⁾ Pulse test: 300 ms pulse width, 1 % duty cycle

THERMAL CHARACTERISTICS ($T_A = 25 \text{ °C}$ unless otherwise noted)						
PARAMETER	SYMBOL	ES2A	ES2B	ES2C	ES2D	UNIT
Typical thermal resistance		75				°C/W
		20			0/00	

Note

 $^{(1)}\,$ Units mounted on PCB 5.0 mm x 5.0 mm (0.013 mm thick) land areas

ORDERING INFORMATION (Example)							
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE			
ES2D-E3/52T	0.096	52T	750	7" diameter plastic tape and reel			
ES2D-E3/5BT	0.096	5BT	3200	13" diameter plastic tape and reel			
ES2DHE3_A/H ⁽¹⁾	0.096	Н	750	7" diameter plastic tape and reel			
ES2DHE3_A/I ⁽¹⁾	0.096	I	3200	13" diameter plastic tape and reel			
ES2D-M3/52T	0.096	52T	750	7" diameter plastic tape and reel			
ES2D-M3/5BT	0.096	5BT	3200	13" diameter plastic tape and reel			
ES2DHM3_A/H ⁽¹⁾	0.096	Н	750	7" diameter plastic tape and reel			
ES2DHM3_A/I ⁽¹⁾	0.096	I	3200	13" diameter plastic tape and reel			

Note

(1) AEC-Q101 qualified



ES2A, ES2B, ES2C, ES2D

Vishay General Semiconductor

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)




Fig. 1 - Maximum Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 4 - Typical Reverse Leakage Characteristics





Fig. 5 - Typical Junction Capacitance





 Revision: 03-Mar-2020
 3
 Document Number: 88587


 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com
 THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000




ES2A, ES2B, ES2C, ES2D

Vishay General Semiconductor

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)







Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.