



## Surface Mount High Efficient Rectifier



### Features

- Low profile package
- Ideal for automated placement
- Glass passivated chip junction
- High forward surge capability
- Super fast reverse recovery time
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C

### Typical Applications

For use in high frequency rectification of power supplies, inverters, converters, and freewheeling diodes for consumer, and telecommunication.

### Mechanical Data

- **Package:** DO-214AC (SMA)  
Molding compound meets UL 94 V-0 flammability rating, RoHS-compliant, halogen-free
- **Terminals:** Tin plated leads, solderable per J-STD-002 and JESD22-B102
- **Polarity:** Cathode line denotes the cathode end

### ■ Maximum Ratings (T<sub>a</sub>=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	HS2AA	HS2BA	HS2DA	HS2FA	HS2GA	HS2JA	HS2KA	HS2MA
Device marking code			HS2AA	HS2BA	HS2DA	HS2FA	HS2GA	HS2JA	HS2KA	HS2MA
Maximum Repetitive peak reverse voltage	V <sub>RRM</sub>	V	50	100	200	300	400	600	800	1000
Average rectified output current @60Hz sine wave, Resistance load, TL (FIG.1)	I <sub>O</sub>	A	2.0							
Forward Surge Current (Non-repetitive) @60Hz Half-sine wave, 1 cycle, T <sub>a</sub> =25°C	I <sub>FSM</sub>	A	50							
Storage temperature	T <sub>stg</sub>	°C	-55~+150							
Junction temperature	T <sub>j</sub>	°C	-55 ~ +150							

### ■ Electrical Characteristics (T<sub>a</sub>=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	TEST CONDITIONS	HS2AA	HS2BA	HS2DA	HS2FA	HS2GA	HS2JA	HS2KA	HS2MA
Maximum instantaneous forward voltage drop per diode	V <sub>F</sub>	V	I <sub>FM</sub> =2.0A	1.0			1.3		1.7		
Maximum reverse recovery time	T <sub>RR</sub>	ns	I <sub>F</sub> =0.5A, I <sub>R</sub> =1.0A, I <sub>r</sub> =0.25A	50					75		
Maximum DC reverse current at rated DC blocking voltage per diode@ VRM=VRRM	I <sub>RRM</sub>	μA	T <sub>a</sub> =25°C	5							
			T <sub>a</sub> =125°C	100							



# HS2AA THRU HS2MA

## ■ Thermal Characteristics (T<sub>a</sub>=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	HS2AA	HS2BA	HS2DA	HS2FA	HS2GA	HS2JA	HS2KA	HS2MA
Typical Thermal Resistance	R <sub>θ</sub> J-A	°C/W	75 <sup>(1)</sup>							
	R <sub>θ</sub> J-L	°C/W	25 <sup>(1)</sup>							
	R <sub>θ</sub> J-C	°C/W	20 <sup>(1)</sup>							

Note

(1) Thermal resistance from junction to ambient and from junction to lead mounted on P.C.B. with 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pad areas

## ■ Characteristics (Typical)

FIG.1: I<sub>o</sub>-T<sub>L</sub> Cure




FIG.2: Forward Surge Current Capability




FIG.3: Typical Forward Characteristics






FIG.4: Typical Reverse Characteristics





# HS2AA THRU HS2MA


FIG.5: Diagram of circuit and Testing wave form of reverse recovery time



## Ordering Information (Example)

PREFERRED P/N	PACKAGE CODE	UNIT WEIGHT(g)	MINIMUM PACKAGE(pcs)	INNER BOX QUANTITY(pcs)	OUTER CARTON QUANTITY(pcs)	DELIVERY MODE
HS2AA-HS2MA	F1	Approximate 0.059	5000	10000	80000	13" reel
HS2AA-HS2MA	F2	Approximate 0.059	7500	15000	120000	13" reel
HS2AA-HS2MA	F3	Approximate 0.059	7500	15000	60000	13" reel
HS2AA-HS2MA	F4	Approximate 0.059	1800	7200	57600	7" reel
HS2AA-HS2MA	F5	Approximate 0.059	2000	8000	64000	7" reel
HS2AA-HS2MA	F6	Approximate 0.059	5000	10000	100000	13" reel

## Outline Dimensions




DO-214AC(SMA)		
Dim	Min	Max
A	1.25	1.58
B	2.40	2.83
C	4.25	4.75
D	1.90	2.30
E	4.93	5.28
F	0.76	1.41
G	0.08	0.20
H	0.15	0.31



## HS2AA THRU HS2MA

### ■ Suggested Pad Layout



DO-214AC(SMA)	
Dim	Millimeters
P1	4.00
P2	1.50
P3	6.50
Q1	2.50
Q2	1.70



## HS2AA THRU HS2MA

---

### Disclaimer

The information presented in this document is for reference only. Yangzhou Yangjie Electronic Technology Co., Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), Yangjie or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.

This publication supersedes & replaces all information previously supplied. For additional information, please visit our website [http:// www.21yangjie.com](http://www.21yangjie.com) , or consult your nearest Yangjie's sales office for further assistance.