

## 20V N-Channel Enhancement-Mode MOSFET

$V_{DS} = 20V$

$R_{DS(ON)}, V_{GS}@4.5V, I_{DS}@5.0A = 41m$

$R_{DS(ON)}, V_{GS}@2.5V, I_{DS}@4.5A = 47m$

### Features

Advanced trench process technology

High Density Cell Design For Ultra Low On-Resistance

we declare that the material of product

compliance with RoHS requirements.

S- Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable.

▼ Capable of 2.5V gate drive



▼ Lower on-resistance

▼ Surface mount package

### Ordering Information

Device	Marking	Shipping
LN2312LT1G S-LN2312LT1G	N12	3000/Tape&Reel
LN2312LT3G S-LN2312LT3G	N12	10000/Tape&Reel

LN2312LT1G  
S-LN2312LT1G



### Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
$V_{DS}$	Drain-Source Voltage	20	V
$V_{GS}$	Gate-Source Voltage	$\pm 8$	V
$I_D@T_A=25^\circ C$	Continuous Drain Current <sup>3</sup> , $V_{GS} @ 4.5V$	4.9	A
$I_D@T_A=70^\circ C$	Continuous Drain Current <sup>3</sup> , $V_{GS} @ 4.5V$	3.4	A
$I_{DM}$	Pulsed Drain Current <sup>1,2</sup>	15	A
$P_D@T_A=25^\circ C$	Total Power Dissipation	0.75	W
	Linear Derating Factor	1.3	W/ $^\circ C$
$T_{STG}$	Storage Temperature Range	-55 to 150	$^\circ C$
$T_J$	Operating Junction Temperature Range	-55 to 150	$^\circ C$

### Thermal Data

Symbol	Parameter	Value	Unit
Rthj-a	Thermal Resistance Junction-ambient <sup>3</sup>	Max. 140	$^\circ C/W$

## LN2312LT1G , S-LN2312LT1G

**Electrical Characteristics@T<sub>j</sub>=25°C(unless otherwise specified)**

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
<b>Static</b>						
Drain-Source Breakdown Voltage	$BV_{DSS}$	$V_{GS} = 0V, I_D = 250\mu A$	20	-	-	V
Drain-Source On-State Resistance	$R_{DS(on)}$	$V_{GS} = 1.8V, I_D = 4.0A$		31	57	mΩ
Drain-Source On-State Resistance	$R_{DS(on)}$	$V_{GS} = 2.5V, I_D = 4.5A$		24	47	
Drain-Source On-State Resistance	$R_{DS(on)}$	$V_{GS} = 4.5V, I_D = 5A$		21	41	
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = 250\mu A$	0.4	0.6	1	V
Zero Gate Voltage Drain Current	$I_{DSS}$	$V_{DS} = 20V, V_{GS} = 0V$			1	μA
Gate Body Leakage	$I_{GSS}$	$V_{GS} = \pm 8V, V_{DS} = 0V$			± 100	nA
Gate Resistance	$R_g$					
Forward Transconductance	$g_{fs}$	$V_{DS} = 10V, I_D = 5A$		40		S
<b>Dynamic</b>						
Total Gate Charge	$Q_g$	$V_{DS} = 10V, I_D = 5A$ $V_{GS} = 4.5V$		11.2		nC
Gate-Source Charge	$Q_{gs}$			1.4		
Gate-Drain Charge	$Q_{gd}$			2.2		
Turn-On Delay Time	$t_{d(on)}$	$V_{DD} = 10V,$ $I_D = 1A, V_{GEN} = 4.5V$ $R_G = 6\Omega$		15	25	ns
Turn-On Rise Time	$t_r$			40	60	
Turn-Off Delay Time	$t_{d(off)}$			48	70	
Turn-Off Fall Time	$t_f$			31	45	
Input Capacitance	$C_{iss}$	$V_{DS} = 8V, V_{GS} = 0V$ $f = 1.0\text{ MHz}$		500		pF
Output Capacitance	$C_{oss}$			300		
Reverse Transfer Capacitance	$C_{rss}$			140		
<b>Source-Drain Diode</b>						
Max. Diode Forward Current	$I_S$				1.7	A
Diode Forward Voltage	$V_{SD}$	$I_S = 1.7A, V_{GS} = 0V$			1.2	V

**Notes:**

- 1.Pulse width limited by Max. junction temperature.
- 2.Pulse width  $\leq 300\mu s$  , duty cycle  $\leq 2\%$ .
- 3.Surface mounted on 1 in<sup>2</sup> copper PCB board

LN2312LT1G , S-LN2312LT1G




Fig 1. Typical Output Characteristics




Fig 2. Typical Output Characteristics




Fig 3. On-Resistance v.s. Gate Voltage




Fig 4. Normalized On-Resistance v.s. Junction Temperature




Fig 5. Forward Characteristic of Reverse Diode




Fig 6. Gate Threshold Voltage v.s. Junction Temperature

LN2312LT1G , S-LN2312LT1G




Fig 7. Gate Charge Characteristics




Fig 8. Typical Capacitance Characteristics




Fig 9. Maximum Safe Operating Area




Fig 10. Effective Transient Thermal Impedance




Fig 11. Switching Time Circuit





Fig 12. Gate Charge Circuit

LN2312LT1G , S-LN2312LT1G

SOT-23

NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M,1982
2. CONTROLLING DIMENSION: INCH.



DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.1102	0.1197	2.80	3.04
B	0.0472	0.0551	1.20	1.40
C	0.0350	0.0440	0.89	1.11
D	0.0150	0.0200	0.37	0.50
G	0.0701	0.0807	1.78	2.04
H	0.0005	0.0040	0.013	0.100
J	0.0034	0.0070	0.085	0.177
K	0.0140	0.0285	0.35	0.69
L	0.0350	0.0401	0.89	1.02
S	0.0830	0.1039	2.10	2.64
V	0.0177	0.0236	0.45	0.60

