

## Glass Passivated Bridge Rectifier

**Voltage**

**1000 V**

**Current**

**35A**

### Features



- Glass passivated chip junction
- Superior thermal conductivity
- Lead free in compliance with EU RoHS 2.0
- Halogen-free according to IEC 61249 standard


### Mechanical Data

- Case : GBU-2 Package
- Terminals : Solderable per MIL-STD-750, Method 2026
- Approx. Weight : 3.8348 grams

### Application

- Computing Power / Desktop Power
- Game Console Power
- Server Power
- Air Conditioner out door power board
- High Power/High Efficiency Power
- Home Appliances Power Board

## GBU-2



| Key Parameters     |              |
|--------------------|--------------|
| Parameter          | Value        |
| $V_{RRM}$          | <b>1000V</b> |
| $I_F(AV)$          | <b>35A</b>   |
| $I_{FSM}$          | <b>400A</b>  |
| $I_R$              | <b>5uA</b>   |
| $T_J \text{ max.}$ | <b>175°C</b> |
| <b>Package</b>     | <b>GBU-2</b> |

**Maximum Ratings and Thermal Characteristics** ( $T_A = 25\text{ }^\circ\text{C}$  unless otherwise noted)

| PARAMETER  | SYMBOL                              | LIMIT   | UNITS                |
|--|-------------------------------------|---------|----------------------|
| Maximum Repetitive Peak Reverse Voltage  | $V_{RRM}$                           | 1000    | V                    |
| Maximum RMS Voltage  | $V_{RMS}$                           | 700     | V                    |
| Maximum DC Blocking Voltage  | $V_{DC}$                            | 1000    | V                    |
| Maximum Average Forward Current  | With heatsink                       | 35      | A                    |
|  | Without heatsink                    | 4.5     |                      |
| Peak Forward Surge Current : 8.3 ms<br>Single Half Sine-Wave Superimposed<br>On Rated Load | @ $T_A = 25\text{ }^\circ\text{C}$  | 400     | A                    |
|  | @ $T_A = 125\text{ }^\circ\text{C}$ | 320     |                      |
| Peak Forward Surge Current : 1.0 ms<br>Single Half Sine-Wave Superimposed<br>On Rated Load | @ $T_A = 25\text{ }^\circ\text{C}$  | 800     | A                    |
|  | @ $T_A = 125\text{ }^\circ\text{C}$ | 640     |                      |
| $I^2 t$ rating for fusing ( $t = 8.3\text{ms}$ )   | $I^2 t$                             | 664     | $\text{A}^2\text{S}$ |
| Typical Junction Capacitance<br>Measured at 1 MHz And Applied $V_R = 4\text{ V}$           | $C_J$                               | 130     | pF                   |
| Typical Thermal Resistance (Note 1) (with heatsink)  | $R_{\theta JA}$                     | 6       | $^\circ\text{C/W}$   |
|  | $R_{\theta JL}$                     | 2       |                      |
|  | $R_{\theta JC}$                     | 1.5     |                      |
| Operating junction and storage temperature range   | $T_J, T_{STG}$                      | -55~175 | $^\circ\text{C}$     |
| Mounting torque @ Recommend torque:5Kg.cm  | Tor                                 | 8       | Kg.cm                |


**Electrical Characteristics** ( $T_A = 25\text{ }^\circ\text{C}$  unless otherwise noted)

| PARAMETER       | SYMBOL | TEST CONDITION   | MIN. | TYP. | MAX. | UNITS |
|-----------------|--------|--|------|------|------|-------|
| Forward Voltage | $V_F$  | $I_F = 17.5\text{ A}, T_J = 25\text{ }^\circ\text{C}$  | -    | -    | 1.1  | V     |
| Reverse Current | $I_R$  | $V_R = 1000\text{ V}, T_J = 25\text{ }^\circ\text{C}$  | -    | -    | 5    | uA    |
|                 |        | $V_R = 1000\text{ V}, T_J = 125\text{ }^\circ\text{C}$ | -    | -    | 100  |       |


NOTES :

1. Device mounted on 10 cm \* 9.4 cm \* 2.6 cm Fin type heat sink


**TYPICAL CHARACTERISTIC CURVES**




**Fig.1 Forward Current Derating Curve**



**Fig.2 Typical Junction Capacitance**



**Fig.3 Typical Reverse Characteristics**




**Fig.4 Typical Forward Characteristics**

**Part No. Marking Code Version**

| Approved Part No. | Package Type | Packing Type  | Marking  |
|-------------------|--------------|---------------|----------|
| GBU3510H          | GBU-2        | 20 pcs / tube | GBU3510H |

**Packaging Information**



## Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panjit:

[GBU3510H\\_T0\\_00601](#)