Notice for TAIYO YUDEN products

Please read this notice before using the TAIYO YUDEN products.

/!\ REMINDERS

Product Information in this Catalog

Product information in this catalog is as of January 2021. All of the contents specified herein and production status of the products listed in this catalog are subject to change without notice due to technical improvement of our products, etc. Therefore, please check for the latest information carefully before practical application or use of our products.

Please note that TAIYO YUDEN shall not be in any way responsible for any damages and defects in products or equipment incorporating our products, which are caused under the conditions other than those specified in this catalog or individual product specification sheets.

Approval of Product Specifications

Please contact TAIYO YUDEN for further details of product specifications as the individual product specification sheets are available. When using our products, please be sure to approve our product specifications or make a written agreement on the product specification with TAIYO YUDEN in advance.

Pre-Evaluation in the Actual Equipment and Conditions

Please conduct validation and verification of our products in actual conditions of mounting and operating environment before using our products.

Limited Application

1. Equipment Intended for Use

The products listed in this catalog are intended for general-purpose and standard use in general electronic equipment (e.g., AV equipment, OA equipment, home electric appliances, office equipment, information and communication equipment including, without limitation, mobile phone, and PC) and other equipment specified in this catalog or the individual product specification sheets.

TAIYO YUDEN has the line-up of the products intended for use in automotive electronic equipment, telecommunications infrastructure and industrial equipment, or medical devices classified as GHTF Classes A to C (Japan Classes I to III). Therefore, when using our products for these equipment, please check available applications specified in this catalog or the individual product specification sheets and use the corresponding products.

2. Equipment Requiring Inquiry

Please be sure to contact TAIYO YUDEN for further information before using the products listed in this catalog for the following equipment (excluding intended equipment as specified in this catalog or the individual product specification sheets) which may cause loss of human life, bodily injury, serious property damage and/or serious public impact due to a failure or defect of the products and/or malfunction attributed thereto.

- (1) Transportation equipment (automotive powertrain control system, train control system, and ship control system, etc.)
- (2) Traffic signal equipment
- (3) Disaster prevention equipment, crime prevention equipment
- (4) Medical devices classified as GHTF Class C (Japan Class III)
- (5) Highly public information network equipment, dataprocessing equipment (telephone exchange, and base station, etc.)
- (6) Any other equipment requiring high levels of quality and/or reliability equal to the equipment listed above

3. Equipment Prohibited for Use

Please do not incorporate our products into the following equipment requiring extremely high levels of safety and/or reliability.

- (1) Aerospace equipment (artificial satellite, rocket, etc.)
- (2) Aviation equipment *1
- (3) Medical devices classified as GHTF Class D (Japan Class IV), implantable medical devices *2

- (4) Power generation control equipment (nuclear power, hydroelectric power, thermal power plant control system, etc.)
- (5) Undersea equipment (submarine repeating equipment, underwater work equipment, etc.)
- (6) Military equipment
- (7) Any other equipment requiring extremely high levels of safety and/or reliability equal to the equipment listed above

*Notes:

- 1. There is a possibility that our products can be used only for aviation equipment that does not directly affect the safe operation of aircraft (e.g., in-flight entertainment, cabin light, electric seat, cooking equipment) if such use meets requirements specified separately by TAIYO YUDEN. Please be sure to contact TAIYO YUDEN for further information before using our products for such aviation equipment.
- Implantable medical devices contain not only internal unit which is implanted in a body, but also external unit which is connected to the internal unit.

4. Limitation of Liability

Please note that unless you obtain prior written consent of TAIYO YUDEN, TAIYO YUDEN shall not be in any way responsible for any damages incurred by you or third parties arising from use of the products listed in this catalog for any equipment that is not intended for use by TAIYO YUDEN, or any equipment requiring inquiry to TAIYO YUDEN or prohibited for use by TAIYO YUDEN as described above.

Safety Design

When using our products for high safety and/or reliability-required equipment or circuits, please fully perform safety and/or reliability evaluation. In addition, please install (i) systems equipped with a protection circuit and a protection device and/or (ii) systems equipped with a redundant circuit or other system to prevent an unsafe status in the event of a single fault for a failsafe design to ensure safety.

Intellectual Property Rights

Information contained in this catalog is intended to convey examples of typical performances and/or applications of our products and is not intended to make any warranty with respect to the intellectual property rights or any other related rights of TAIYO YUDEN or any third parties nor grant any license under such rights.

Limited Warranty

Please note that the scope of warranty for our products is limited to the delivered our products themselves and TAIYO YUDEN shall not be in any way responsible for any damages resulting from a failure or defect in our products. Notwithstanding the foregoing, if there is a written agreement (e.g., supply and purchase agreement, quality assurance agreement) signed by TAIYO YUDEN and your company, TAIYO YUDEN will warrant our products in accordance with such agreement

■ TAIYO YUDEN's Official Sales Channel

The contents of this catalog are applicable to our products which are purchased from our sales offices or authorized distributors (hereinafter "TAIYO YUDEN's official sales channel"). Please note that the contents of this catalog are not applicable to our products purchased from any seller other than TAIYO YUDEN's official sales channel.

Caution for Export

Some of our products listed in this catalog may require specific procedures for export according to "U.S. Export Administration Regulations", "Foreign Exchange and Foreign Trade Control Law" of Japan, and other applicable regulations. Should you have any questions on this matter, please contact our sales staff.

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).


WIRE-WOUND CHIP INDUCTORS (LB SERIES)

REFLOW

PARTS NUMBER

* Operating Temp.: -40~+105°C (Including self-generated heat)

△=Blank space



①c:			

TOCHES HAITIC	
Code	Series name
LB	Wound chip inductor

(2)Characteristics

2 Orial acteristics				
Code	Characteristics			
ΔΔ	Standard			
ΔC	High current			
ΔR	Low Rdc			
MF	Low loss			

③Dimensions (L×W)

LB/LB C/LB R

Code	Type (inch)	Dimensions (L×W)[mm]
1608	1608 (0603)	1.6 × 0.8
2012	2012(0805)	2.0 × 1.25
2016	2016(0806)	2.0 × 1.6
2518	2518(1007)	2.5 × 1.8
3218	3218(1207)	3.2 × 1.8
3225	3225(1210)	3.2 × 2.5

4 Packaging

Code	Packaging
Т	Taping

5Nominal inductance

Code (example)	Nominal inductance[μ H]
1R0	1.0
100	10
101	100

※R=Decimal point

6 Inductance tolerance

Code Inductance tolerance	
K	±10%
М	±20%

(7)Special code

	O openial code	
	Code	Special code
△ Standard		Standard
	R	Low Rdc type

8Internal code


■STANDARD EXTERNAL DIMENSIONS / STANDARD QUANTITY

LBMF

Recommended Land Patterns

Surface Mounting

- •Mounting and soldering conditions should be checked beforehand.
- •Applicable soldering process to these products is reflow soldering only.



Type	e A B		С
1608	0.55	0.7	0.9
MF1608	0.55	0.7	1.0
2012	0.60	1.0	1.45
2016	2016 0.60		1.8
2518	0.60	1.5	2.0
3218	3218 0.85		2.0
3225	3225 0.85		2.7

Unit:mm

Tumo		L W T			Standard quantity[pcs]		
Туре	L	VV		е	Paper tape	Embossed tape	
LB 1608	1.6±0.1 (0.063±0.004)	0.8±0.1 (0.031±0.004)	0.8±0.1 (0.031±0.004)	0.35±0.15 (0.014±0.006)	4000	ı	
LBMF1608	1.6±0.2 (0.063±0.008)	0.8 ± 0.2 (0.031 ± 0.008)	0.8 ± 0.2 (0.031 ± 0.008)	0.45±0.15 (0.016±0.006)	_	3000	
LB 2012 LB C2012 LB R2012	2.0±0.2 (0.079±0.008)			_	3000		
LB 2016 LB C2016	2.0±0.2 (0.079±0.008)	1.6±0.2 (0.063±0.008)	1.6±0.2 (0.063±0.008)	0.5±0.2 (0.020±0.008)	_	2000	
LB 2518 LB C2518 LB R2518	2.5±0.2 (0.098±0.008)	1.8±0.2 (0.071±0.008)	1.8±0.2 (0.071±0.008)	0.5±0.2 (0.020±0.008)	_	2000	
LB 3218	3.2±0.2 (0.126±0.008)	1.8±0.2 (0.071±0.008)	1.8±0.2 (0.071±0.008)	0.6±0.2 (0.024±0.008)	_	2000	
LB C3225	3.2±0.2 (0.126±0.008)	2.5±0.2 (0.098±0.008)	2.5±0.2 (0.098±0.008)	0.6±0.3 (0.024±0.012)	_	1000	
Unit:mm(inch)							

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

for General Electronic Equipment

PARTS NUMBER

1608	(0603)	type
------	--------	------

Parts number	EHS	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω](±30%)	Rated current [mA] (max.)	Measuring frequency [MHz]
LB 1608T1R0M	RoHS	1.0	±20%	100	0.17	160	7.96
LB 1608T2R2M	R₀HS	2.2	±20%	80	0.33	115	7.96
LB 1608T4R7M	R₀HS	4.7	±20%	45	0.55	70	7.96
LB 1608T8R2M	RoHS	8.2	±20%	32	0.70	60	2.52
LB 1608T100M	RoHS	10	±20%	32	0.70	60	2.52

Parts number	EHS	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω](±30%)	Rated current [mA] (max.)	Measuring frequency [MHz]
LBMF1608T1R0M	RoHS	1.0	±20%	100	0.09	230	7.96
LBMF1608T2R2M	RoHS	2.2	±20%	80	0.17	160	7.96
LBMF1608T3R3M	RoHS	3.3	±20%	60	0.22	130	7.96
LBMF1608T4R7M	RoHS	4.7	±20%	45	0.24	110	7.96
LBMF1608T100[]	RoHS	10	±10%, ±20%	32	0.36	80	2.52
LBMF1608T220[]	RoHS	22	±10%, ±20%	16	1.0	50	2.52
LBMF1608T470∏	R ₀ HS	47	±10%, ±20%	11	2.5	35	2.52

2012(0805)type

Parts number	EHS	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω](±30%)	Rated current [mA] (max.)	Measuring frequency [MHz]
LB 2012T1R0M	RoHS	1.0	±20%	100	0.15	405	7.96
LB 2012T2R2M	RoHS	2.2	±20%	80	0.23	260	7.96
LB 2012T3R3M	RoHS	3.3	±20%	55	0.30	235	7.96
LB 2012T4R7M	RoHS	4.7	±20%	45	0.40	190	7.96
LB 2012T6R8M	RoHS	6.8	±20%	38	0.47	135	7.96
LB 2012T100[]	RoHS	10	±10%, ±20%	32	0.70	120	2.52
LB 2012T100□R	RoHS	10	±10%, ±20%	32	0.50	120	2.52
LB 2012T150[]	RoHS	15	±10%, ±20%	28	1.3	100	2.52
LB 2012T220□	RoHS	22	±10%, ±20%	16	1.7	80	2.52
LB 2012T470[]	RoHS	47	±10%, ±20%	11	3.7	60	2.52
LB 2012T680[]	RoHS	68	±10%, ±20%	10	6.0	50	2.52
LB 2012T101[]	RoHS	100	±10%, ±20%	8	7.0	45	0.796

Parts number	EHS	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω]($\pm 30\%$)	Rated current [mA] (max.)	Measuring frequency [MHz]
LB C2012T1R0M	RoHS	1.0	±20%	100	0.19	620	7.96
LB C2012T2R2M	RoHS	2.2	±20%	70	0.33	430	7.96
LB C2012T4R7M	RoHS	4.7	±20%	45	0.50	295	7.96
LB C2012T100[]	RoHS	10	±10%, ±20%	40	1.2	200	2.52
LB C2012T220[]	RoHS	22	±10%, ±20%	16	3.7	130	2.52
LB C2012T470[]	RoHS	47	±10%, ±20%	11	5.8	90	2.52

		1	1		1	1	
Parts number	EHS	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω](±30%)	Rated current [mA] (max.)	Measuring frequency [MHz]
LB R2012T1R0M	RoHS	1.0	±20%	100	0.07	400	7.96
LB R2012T2R2M	RoHS	2.2	±20%	80	0.13	260	7.96
LB R2012T4R7M	RoHS	4.7	±20%	45	0.24	200	7.96
LB R2012T100[]	RoHS	10	±10%, ±20%	32	0.36	150	2.52
LB R2012T220[]	RoHS	22	±10%, ±20%	16	1.0	100	2.52
LB R2012T470[]	RoHS	47	±10%, ±20%	11	1.7	75	2.52
LB R2012T101[]	RoHS	100	±10%, ±20%	8	4.0	50	0.796

2016 (0806) type

2016 (0806) type							
Parts number	EHS	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω](±30%)	Rated current [mA] (max.)	Measuring frequency [MHz]
LB 2016T1R0M	RoHS	1.0	±20%	100	0.09	490	7.96
LB 2016T1R5M	RoHS	1.5	±20%	80	0.11	380	7.96
LB 2016T2R2M	RoHS	2.2	±20%	70	0.13	375	7.96
LB 2016T3R3M	RoHS	3.3	±20%	55	0.20	285	7.96
LB 2016T4R7M	RoHS	4.7	±20%	45	0.25	225	7.96
LB 2016T6R8M	RoHS	6.8	±20%	38	0.35	200	7.96
LB 2016T100	RoHS	10	±10%, ±20%	32	0.50	155	2.52
LB 2016T150	RoHS	15	±10%, ±20%	28	0.70	130	2.52
LB 2016T220□	RoHS	22	±10%, ±20%	16	1.0	105	2.52
LB 2016T330□	RoHS	33	±10%, ±20%	14	1.7	85	2.52
LB 2016T470	RoHS	47	±10%, ±20%	11	2.4	70	2.52
LB 2016T680	RoHS	68	±10%, ±20%	10	3.0	55	2.52
LB 2016T101	RoHS	100	±10%, ±20%	8	4.5	40	0.796

[•]Please specify the Inductance tolerance code (K or M)

LB/LBC series

Rated Current: The maximum DC value having inductance decrease within 10 % and temperature increase within 20 degC by the application of DC bias.

LBR serie

Rated Current: The maximum DC value having inductance decrease within 20 % and temperature increase within 20 degC by the application of DC bias.

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

Parts number	EHS	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance $[\Omega](\pm 30\%)$	Rated current [mA] (max.)	Measuring frequency [MHz]
LB C2016T1R0M	RoHS	1.0	±20%	100	0.10	690	7.96
LB C2016T1R5M	RoHS	1.5	±20%	80	0.15	600	7.96
LB C2016T2R2M	RoHS	2.2	±20%	70	0.20	520	7.96
LB C2016T3R3M	RoHS	3.3	±20%	55	0.27	410	7.96
LB C2016T4R7M	RoHS	4.7	±20%	45	0.37	355	7.96
LB C2016T6R8M	RoHS	6.8	±20%	38	0.59	290	7.96
LB C2016T100[]	RoHS	10	±10%, ±20%	32	0.82	245	2.52
LB C2016T150[]	R₀HS	15	±10%, ±20%	28	1.2	200	2.52
LB C2016T220[]	RoHS	22	±10%, ±20%	16	1.8	165	2.52
LB C2016T330[]	RoHS	33	±10%, ±20%	14	2.8	135	2.52
LB C2016T470[]	RoHS	47	±10%, ±20%	11	4.3	110	2.52
LB C2016T680[]	RoHS	68	±10%, ±20%	10	7.0	95	2.52
LB C2016T101[]	RoHS	100	±10%, ±20%	8	8.0	75	0.796

2518(1007) type

Parts number	EHS	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω]($\pm 30\%$)	Rated current [mA] (max.)	Measuring frequency [MHz]
LB 2518T1R0M	RoHS	1.0	±20%	100	0.06	665	7.96
LB 2518T1R5M	RoHS	1.5	±20%	80	0.07	405	7.96
LB 2518T2R2M	RoHS	2.2	±20%	68	0.09	340	7.96
LB 2518T3R3M	RoHS	3.3	±20%	54	0.11	280	7.96
LB 2518T4R7M	RoHS	4.7	±20%	46	0.13	240	7.96
LB 2518T4R7MR	R₀HS	4.7	±20%	46	0.10	235	7.96
LB 2518T6R8M	RoHS	6.8	±20%	38	0.15	195	7.96
LB 2518T100[]	RoHS	10	±10%, ±20%	30	0.25	165	2.52
LB 2518T150[]	RoHS	15	±10%, ±20%	23	0.32	145	2.52
LB 2518T220[]	RoHS	22	±10%, ±20%	19	0.50	115	2.52
LB 2518T330[]	RoHS	33	±10%, ±20%	15	0.70	95	2.52
LB 2518T470[]	RoHS	47	±10%, ±20%	12	0.95	85	2.52
LB 2518T680[]	RoHS	68	±10%, ±20%	9.5	1.5	70	2.52
LB 2518T101[]	RoHS	100	±10%, ±20%	9.0	2.1	60	0.796
LB 2518T151[]	RoHS	150	±10%, ±20%	7.0	3.2	45	0.796
LB 2518T221[]	RoHS	220	±10%, ±20%	5.5	4.5	40	0.796
LB 2518T331[]	RoHS	330	±10%, ±20%	4.5	7.0	30	0.796
LB 2518T471[]	RoHS	470	±10%, ±20%	3.5	10	25	0.796
LB 2518T681[]	RoHS	680	±10%, ±20%	3.0	17	20	0.796
LB 2518T102[]	RoHS	1000	±10%, ±20%	2.4	24	15	0.252

Parts number	EHS	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω](±30%)	Rated current [mA] (max.)	Measuring frequency [MHz]
LB C2518T1R0M	RoHS	1.0	±20%	100	0.08	775	7.96
LB C2518T1R0MR	RoHS	1.0	±20%	100	0.07	890	7.96
LB C2518T1R5M	R₀HS	1.5	±20%	80	0.11	730	7.96
LB C2518T2R2M	RoHS	2.2	±20%	68	0.13	630	7.96
LB C2518T3R3M	R₀HS	3.3	±20%	54	0.16	560	7.96
LB C2518T4R7M	RoHS	4.7	±20%	41	0.20	510	7.96
LB C2518T6R8M	RoHS	6.8	±20%	38	0.30	420	7.96
LB C2518T100[]	R ₀ HS	10	±10%, ±20%	30	0.36	375	2.52
LB C2518T150[]	R₀HS	15	±10%, ±20%	23	0.65	285	2.52
LB C2518T220[]	RoHS	22	±10%, ±20%	19	0.77	250	2.52
LB C2518T330[]	RoHS	33	±10%, ±20%	15	1.5	185	2.52
LB C2518T470□	RoHS	47	±10%, ±20%	12	1.9	165	2.52
LB C2518T680[]	R₀HS	68	±10%, ±20%	9.5	2.8	140	2.52
LB C2518T101[]	RoHS	100	±10%, ±20%	9.0	3.7	125	0.796
LB C2518T151	RoHS	150	±10%, ±20%	7.0	6.1	95	0.796
LB C2518T221□	RoHS	220	±10%, ±20%	5.5	8.4	80	0.796
LB C2518T331	RoHS	330	±10%, ±20%	4.5	12.3	65	0.796
LB C2518T471[]	R₀HS	470	±10%, ±20%	3.5	22	50	0.796
LB C2518T681	RoHS	680	±10%, ±20%	3.0	28	45	0.796

Parts number	EHS	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance $[\Omega](\pm 30\%)$	Rated current [mA] (max.)	Measuring frequency [MHz]
LB R2518T1R0M	RoHS	1.0	±20%	100	0.045	960	7.96
LB R2518T2R2M	RoHS	2.2	±20%	68	0.07	480	7.96
LB R2518T4R7M	RoHS	4.7	±20%	45	0.10	345	7.96
LB R2518T100[]	RoHS	10	±10%, ±20%	30	0.19	235	2.52
LB R2518T220[]	RoHS	22	±10%, ±20%	19	0.44	175	2.52
LB R2518T470[]	RoHS	47	±10%, ±20%	11	0.84	120	2.52
LB R2518T101[]	RoHS	100	±10%, ±20%	9	1.89	80	0.796

^{• []} Please specify the Inductance tolerance code (K or M)

LB/LBC series

Rated Current : The maximum DC value having inductance decrease within 10 % and temperature increase within 20 degC by the application of DC bias.

LBR series

Rated Current : The maximum DC value having inductance decrease within 20 % and temperature increase within 20 degC by the application of DC bias.

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).

for General Electronic Equipment

3218 (1207) type

Parts number	EHS	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance $[\Omega](\pm 30\%)$	Rated current [mA] (max.)	Measuring frequency [MHz]
LB 3218T1R0M	R₀HS	1.0	±20%	100	0.06	1,075	7.96
LB 3218T1R5M	RoHS	1.5	±20%	80	0.07	860	7.96
LB 3218T2R2M	RoHS	2.2	±20%	68	0.09	775	7.96
LB 3218T3R3M	RoHS	3.3	±20%	54	0.11	560	7.96
LB 3218T4R7M	RoHS	4.7	±20%	41	0.13	550	7.96
LB 3218T6R8M	RoHS	6.8	±20%	40	0.17	380	7.96
LB 3218T100[]	RoHS	10	±10%, ±20%	30	0.25	340	2.52
LB 3218T150[]	RoHS	15	±10%, ±20%	25	0.32	300	2.52
LB 3218T220	RoHS	22	±10%, ±20%	19	0.49	255	2.52
LB 3218T330[]	RoHS	33	±10%, ±20%	15	0.75	215	2.52
LB 3218T470[]	RoHS	47	±10%, ±20%	12	0.92	205	2.52
LB 3218T680[]	RoHS	68	±10%, ±20%	11	1.49	145	2.52
LB 3218T101[]	RoHS	100	±10%, ±20%	8.0	2.4	140	0.796
LB 3218T151[]	RoHS	150	±10%, ±20%	7.0	3.2	105	0.796
LB 3218T221[]	RoHS	220	±10%, ±20%	5.0	5.4	80	0.796
LB 3218T331	RoHS	330	±10%, ±20%	4.0	7.0	65	0.796
LB 3218T471	RoHS	470	±10%, ±20%	3.5	14	54	0.796
LB 3218T681	RoHS	680	±10%, ±20%	3.0	17	45	0.796
LB 3218T102[]	RoHS	1000	±10%, ±20%	2.4	27	39	0.252

3225(1210)type

Parts number	EHS	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω](±30%)	Rated current [mA] (max.)	Measuring frequency [MHz]
LB C3225T1R0MR	R₀HS	1.0	±20%	250	0.055	1,100	0.1
LB C3225T1R5MR	RoHS	1.5	±20%	220	0.060	1,000	0.1
LB C3225T2R2MR	RoHS	2.2	±20%	190	0.080	930	0.1
LB C3225T3R3MR	RoHS	3.3	±20%	160	0.095	820	0.1
LB C3225T4R7MR	RoHS	4.7	±20%	70	0.100	680	0.1
LB C3225T6R8MR	RoHS	6.8	±20%	50	0.120	620	0.1
LB C3225T100□R	RoHS	10	±10%, ±20%	23	0.133	540	0.1
LB C3225T150[R	RoHS	15	±10%, ±20%	20	0.195	420	0.1
LB C3225T220□R	RoHS	22	±10%, ±20%	17	0.27	330	0.1
LB C3225T330□R	RoHS	33	±10%, ±20%	13	0.41	300	0.1
LB C3225T470□R	RoHS	47	±10%, ±20%	10	0.67	220	0.1
LB C3225T680∏R	RoHS	68	±10%, ±20%	8	1.0	190	0.1
LB C3225T101□R	RoHS	100	±10%, ±20%	6	1.4	150	0.1

<sup>•
☐</sup> Please specify the Inductance tolerance code(K or M)

Rated Current: The maximum DC value having inductance decrease within 10 % and temperature increase within 20 degC by the application of DC bias.


[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (http://www.ty-top.com/).


WIRE-WOUND CHIP INDUCTORS (LB SERIES), WIRE-WOUND CHIP POWER INDUCTORS (CB SERIES), WIRE-WOUND CHIP INDUCTORS FOR SIGNAL LINES (LB SERIES M TYPE)


PACKAGING


1 Minimum Quantity Standard Quantity [pcs] Туре Paper Tape Embossed Tape LB C3225 1000 CB C3225 LB 3218 2000 LB R2518 LB C2518 2000 LB 2518 CB 2518 CB C2518 LBM2016 LB C2016 LB 2016 2000 CB 2016 CB C2016 LB 2012 LB C2012 LB R2012 3000 CB 2012 CB C2012 CB L2012 4000 LB 1608 4000 LBMF1608 3000 CBMF1608

②Tape material










This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).


Embossed Tape (0.315 inches wide)



Т	Chip	cavity	Insertion pitch	Tape th	ickness
Туре	Α	В	F	Т	K
LBM2016	1.75±0.1	2.1±0.1	4.0±0.1	0.3±0.05	1.9max.
	(0.069±0.004)	(0.083±0.004)	(0.157±0.004)	(0.012±0.002)	(0.075max.)
LB C3225	2.8±0.1	3.5±0.1	4.0±0.1	0.3±0.05	4.0max.
CB C3225	(0.110±0.004)	(0.138±0.004)	(0.157±0.004)	(0.012±0.002)	(0.157max.)
LB 3218	2.1±0.1	3.5±0.1	4.0±0.1	0.3±0.05	2.2max.
	(0.083±0.004)	(0.138±0.004)	(0.157±0.004)	(0.012±0.002)	(0.087max.)
LB 2518 CB 2518 LB C2518 CB C2518 LB R2518	2.15±0.1	2.7±0.1	4.0±0.1	0.3±0.05	2.2max.
	(0.085±0.004)	(0.106±0.004)	(0.157±0.004)	(0.012±0.002)	(0.087max.)
LB 2016 CB 2016 LB C2016 CB C2016	1.75±0.1 (0.069±0.004)	2.1±0.1 (0.083±0.004)	4.0±0.1 (0.157±0.004)	0.3±0.05 (0.012±0.002)	1.9max. (0.075max.)
LB 2012 CB 2012 LB C2012 CB C2012 LB R2012	1.45±0.1 (0.057±0.004)	2.25±0.1 (0.089±0.004)	4.0±0.1 (0.157±0.004)	0.25±0.05 (0.010±0.002)	1.45max. (0.057max.)
LBMF1608	1.1±0.1	1.9±0.1	4.0±0.1	0.25±0.05	1.2max.
CBMF1608	(0.043±0.004)	(0.075±0.004)	(0.157±0.004)	(0.010±0.002)	(0.047max.)

Unit:mm(inch)

Card board carrier tape (0.315 inches wide)




	Chip	cavity	Insertion pitch	Tape thickness
Туре	A	В	F	Т
OD 1 0010	1.55±0.1	2.3±0.1	4.0±0.1	1.1max.
CB L2012	(0.061 ± 0.004)	(0.091 ± 0.004)	(0.157 ± 0.004)	(0.043max.)
LD 1000	1.0±0.1	1.8±0.1	4.0±0.1	1.1max.
LB 1608	(0.039 ± 0.004)	(0.071 ± 0.004)	(0.157 ± 0.004)	(0.043max.)


Unit:mm(inch)

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

4 Leader and Blank Portion




⑤Reel Size



©Top Tape Strength

The top tape requires a peel-off force 0.2 to 0.7N in the direction of the arrow as illustrated below.

Pull direction



This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

WIRE-WOUND CHIP INDUCTORS (LB SERIES), WIRE-WOUND CHIP POWER INDUCTORS (CB SERIES), WIRE-WOUND CHIP INDUCTORS FOR SIGNAL LINES (LB SERIES M TYPE)

RELIABILITY DATA

1 Operating toward	nture Pange		
1.Operating temper	-		
Specified Value	LB, LBC, LBR, LBMF Series	40 140500 (7 1 1 1 15 15 1 1 1 1 1 1 1 1 1 1 1 1 1	
	CB, CBC, CBL, CBMF Series	$-40 \sim +105$ °C (Including self-generated heat)	
	LBM Series		
2. Storage Tempera	ture Range(after soldering)		
	LB, LBC, LBR, LBMF Series		
Specified Value	CB, CBC, CBL, CBMF Series	- -40∼+85°C	
opeemed value	LBM Series	-	
Test Methods and	LB, CB Series:		
Remarks	Please refer the term of "7. storage conditions" in precaution	ns.	
3.Rated Current			
	LB, LBC, LBR, LBMF Series	 	
Specified Value	CB, CBC, CBL, CBMF Series	Within the specified tolerance	
	LBM Series		
4.Inductance		T	
	LB, LBC, LBR, LBMF Series	-	
Specified Value	CB, CBC, CBL, CBMF Series	Within the specified tolerance	
	LBM Series		
Test Methods and	LB·LBC·LBR·CB·CBC·CBL·LBMF·CBMF·LBM Series Measuring equipment :LCR Mater(HP4285A or its equivalent)		
Remarks	Measuring frequency : Specified frequency	, and a second	
5.Q			
	LB, LBC, LBR, LBMF Series		
Specified Value	CB, CBC, CBL, CBMF Series		
	LBM Series	Within the specified tolerance	
Test Methods and	LBM Series		
Remarks	Measuring equipment : LCR Mater (HP4285A or its eq Measuring frequency : Specified frequency	quivalent)	
	incusuring requestoy . Opening requestoy		
6.DC Resisitance			
	LB, LBC, LBR, LBMF Series		
Specified Value	CB, CBC, CBL, CBMF Series	Within the specified tolerance	
	LBM Series		
Test Methods and	Measuring equipment : DC Ohmmeter (HIOKI 3227 or its equ	uivalent)	
Remarks			
7.Self-Resonant Fr	equency		
	LB, LBC, LBR, LBMF Series		
Specified Value	CB, CBC, CBL, CBMF Series	Within the specified tolerance	
-	LBM Series	† · · ·	
Test Methods and Remarks	Measuring equipment : Impedance analyzer (HP4291A or its	equivalent)	

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

8.Temperature Cha	racteristic				
	LBM2016				Inductance change : Within±5%
	LB1608	LB2012	LBR2012	CB2012	
	CBL2012	LB2016	CB2016	LB2518	Inductance change : Within±20%
Specified Value	LBR2518	CB2518	LBC3225	CBC3225	
	LBMF1608	CBMF1608	LBC2016	CBC2016	1 Walt 050/
	LBC2518	CBC2518	LB3218		Inductance change : Within±25%
	LBC2012	CBC2012			Inductance change : Within±35%
Test Methods and Remarks	Based on the	inductance at 2	0°C and Meası	ured at the ambi	ent of −40°C∼+85°C.

9.Rasistance to Flex	xure of Substrate	
	LB, LBC, LBR, LBMF Series	No damage.
Specified Value	CB, CBC, CBL, CBMF Series	
	LBM Series	
	Warp : 2mm(LB·LBC·LBR·CB·CBC·CBL·LBM·L	BMF · CBMF Series)
Test Methods and Remarks	Test substrate : Glass epoxy-resin substrate Thickness : 0.8mm(LB1608·LBMF1608·CBMF1608) : 1.0mm(Others) Pressing jig 10 20 R340 Board R5 45±2mm 45±2mm 45±2mm	

10.Body Strength		
	LB, LBC, LBR, LBMF Series	
Specified Value	CB, CBC, CBL, CBMF Series	No damage.
	LBM Series	
Test Methods and Remarks	LB·LBC·LBR·CB·CBC·CBL·LBM Applied force : 10N Duration : 10sec. LB1608·LBMF1608·CBMF1608 Applied force : 5N Duration : 10sec.	

11.Adhesion of term	ninal electrode	
	LB, LBC, LBR, LBMF Series	
Specified Value	CB, CBC, CBL, CBMF Series	No abnormality.
	LBM Series	
Test Methods and Remarks	LB·LBC·LBR·CB·CBC·CBL·LBM·LBMF·CBMF Applied force : 10N to X and Y directions Duration : 5 sec. Test substrate : Printed board LB1608·CBMF1608·LBMF1608 Applied force : 5N to X and Y directions Duration : 5 sec. Test substrate : Printed board	

[►] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

12.Resistance to vil	pration				
	LB, LBC, LBR, LBMF Series		Inductance change : Within±10%		
Specified Value	CB, CBC, CBL, CBMF Series		No significant abnormality in appearance.		
Specified value	LBM Series		Inductance change : Within±5% No significant abnormality in appearance.		
	LB·LBR·LBC·CB·CBC·CBL				
			ed depending on the conditions of the following table.		
	Vibration Frequency	10~55Hz			
Test Methods and Remarks	Total Amplitude 1.5mm (May not exceed accel		<u> </u>		
Remarks	Sweeping Method	Sweeping Method 10Hz to 55Hz to 10Hz for 1min.			
	Time		n each X, Y, and Z axis.		
	Recovery : At least 2 hrs of	frecovery under the standard of	ondition after the test, followed by the measurement within 48 hrs.		
13.Drop test					
<u>'</u>	LB, LBC, LBR, LBMF Series				
Specified Value	CB, CBC, CBL, CBMF Series		 _		
opcomou value	LBM Series		†		
	EDIM OCHOS				
14.0-1.1 1.77					
14.Solderability	ID IDO IDD ID:				
	LB, LBC, LBR, LBMF Series				
Specified Value	CB, CBC, CBL, CBMF Series		At least 90% of surface of terminal electrode is covered by new		
	LBM Series				
	LB.LBC.LBR.CB.CBC.CBL				
Test Methods and		5±5℃			
Remarks	Duration : 5±0.5sec				
	Flux : Me	thanol solution with 25% of co	юрпопу		
455 1					
15.Resistance to so	-				
	LB, LBC, LBR, LBMF Series		Inductance change : Within±10%		
Specified Value	CB, CBC, CBL, CBMF Series		Ţ		
	LBM Series		Inductance change : Within±5%		
Test Methods and	LB.LBC.LBR.CB.CBC.CBL				
Remarks	3 times of reflow oven at 230°C MIN for 40sec. with peak temperature at 260 °C for 5sec.				
	Recovery : At least 2 hrs of	recovery under the standard o	condition after the test, followed by the measurement within 48 hrs.		
16.Resisitance to so	plvent				
	LB, LBC, LBR, LBMF Series				
Specified Value	CB, CBC, CBL, CBMF Series		_		
	LBM Series]		
	Solvent temperature : Roo	om temperature			
Test Methods and Remarks	Type of solvent : Isopropyl alcohol				
rtemarks	Cleaning conditions : 90s	s. Immersion and cleaning.			
17.Thermal shock					
	LB, LBC, LBR, LBMF Series				
Specified Value	CB, CBC, CBL, CBMF Series		Inductance change : Within ± 10%		
•	No significant abnormality in appearance.				
Test Methods and					
Remarks	The given sample is soldered		tance is measured after 100cycles of the following conditions.		
	Step Temperature (°				
	1 —40±3	30±3			
	2 Room temperati				
	3 +85±2	30±3			
	4 Room temperate				
	Recovery : At least	2 hrs of recovery under the st	andard condition after the test, followed by the measurement within 48 hrs.		

[►] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

18.Damp heat life to			
	LB, LBC, LBR, LBMF Series Inductance change: Within±10%		
Specified Value	CB, CBC, CBL, CBMF Series	No significant abnormality in appearance.	
	LBM Series		
T . M .!	Temperature : 60±2°C		
Test Methods and Remarks	Humidity : 90~95%RH Duration : 1000 hrs		
		standard condition after the test, followed by the measurement within 48 hrs.	
19.Loading under da	amp heat life test		
	LB, LBC, LBR, LBMF Series		
	CB, CBC, CBL, CBMF Series	Inductance change : Within±10% No significant abnormality in appearance.	
Specified Value	LBM Series	The digital action land, in appear and the	
Test Methods and	Temperature : 60±2°C		
Remarks	Humidity : 90~95%RH Duration : 1000 hrs		
	Duration : 1000 hrs Applied current : Rated current		
		standard condition after the test, followed by the measurement within 48 hrs.	
20.High temperature	e life test		
	LB, LBC, LBR, LBMF Series	_	
Specified Value	CB, CBC, CBL, CBMF Series	Inductance change : Within±10%	
	LBM Series	No significant abnormality in appearance.	
Test Methods and	Temperature : 85±2°C		
Remarks	Duration : 1000 hrs Recovery : At least 2 hrs of recovery under the	standard condition after the test, followed by the measurement within 48 hrs.	
	The covery . At least 2 lifs of recovery under the	Standard Condition after the test, followed by the measurement within 40 ms.	
21.Loading at high t	temperature life test		
	1	Inductance change : Within±10%	
	LB, LBC, LBR, LBMF Series	(LBC3225 Series : Within±20%)	
Specified Value		No significant abnormality in appearance.	
	CB, CBC, CBL, CBMF Series		
-	LBM Series		
Test Methods and	Temperature : 85±2°C Duration : 1000 hrs		
Remarks	Duration : 1000 hrs Applied current : Rated current		
	Recovery : At least 2 hrs of recovery under the standard condition after the test, followed by the measurement within 48 hr		
22.Low temperature	e life test		
	LB, LBC, LBR, LBMF Series	Inductance change : Within±10%	
Specified Value	CB, CBC, CBL, CBMF Series	No significant abnormality in appearance.	
	LBM Series		
Test Methods and	Temperature : -40±2°C		
Remarks	Duration : 1000 hrs Recovery : At least 2 hrs of recovery under the	standard condition after the test, followed by the measurement within 48 hrs.	
	. At loast 2 his of recovery and of the	Standard Condition arts: the test, followed by the measurement within 40 ms.	
23.Standard conditi	ion		
20.0tandard conditi		Standard test conditions	
	LB, LBC, LBR, LBMF Series	Unless specified, Ambient temperature is 20±15°C and the Relative	
		humidity is $65\pm20\%$. If there is any doubt about the test results, further	
	on one one one :		
Specified Value	CB, CBC, CBL, CBMF Series	measurement shall be had within the following limits:	
Specified Value		measurement shall be had within the following limits: Ambient Temperature: 20±2°C	
Specified Value	CB, CBC, CBL, CBMF Series LBM Series	measurement shall be had within the following limits:	

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

WIRE-WOUND CHIP INDUCTORS (LB SERIES), WIRE-WOUND CHIP POWER INDUCTORS (CB SERIES), WIRE-WOUND CHIP INDUCTORS FOR SIGNAL LINES (LB SERIES M TYPE)

PRECAUTIONS

1. Circuit Design Precautions

♦Operating environment

1. The products described in this specification are intended for use in general electronic equipment, (office supply equipment, telecommunications systems, measuring equipment, and household equipment). They are not intended for use in mission-critical equipment or systems requiring special quality and high reliability (traffic systems, safety equipment, aerospace systems, nuclear control systems and medical equipment including life-support systems,) where product failure might result in loss of life, injury or damage. For such uses, contact TAIYO YUDEN Sales Department in advance.

Precautions Technical considerations PRECAUTIONS [Recommended Land Patterns] Surface Mounting • Mounting and soldering conditions should be checked beforehand. • Applicable soldering process to those products is reflow soldering only.

3. Considerations	3. Considerations for automatic placement		
Precautions	◆Adjustment of mounting machine 1. Excessive impact load should not be imposed on the products when mounting onto the PC boards. 2. Mounting and soldering conditions should be checked beforehand.		
Technical considerations	1. When installing products, care should be taken not to apply distortion stress as it may deform the products.		



4. Soldering


◆Reflow soldering(LB and CB Types)

1. For reflow soldering with either leaded or lead-free solder, the profile specified in "point for controlling" is recommended.

◆Recommended conditions for using a soldering iron

1. Put the soldering iron on the land-pattern. Soldering iron's temperature - Below 350°C Duration-3 seconds or less. The soldering iron should not come in contact with inductor directly.





- ◆Recommended conditions for using a soldering iron
 - 1. Components can be damaged by excessive heat where soldering conditions exceed the specified range

5. Cleaning Precautions ♦ Cleaning conditions Washing by supersonic waves shall be avoided. Technical considerations ♦ Cleaning conditions If washed by supersonic waves, the products might be broken.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

6. Handling	
Precautions	 ◆Handling 1. Keep the inductors away from all magnets and magnetic objects. ◆Breakaway PC boards(splitting along perforations) 1. When splitting the PC board after mounting inductors, care should be taken not to give any stresses of deflection or twisting to the board. 2. Board separation should not be done manually, but by using the appropriate devices. ◆Mechanical considerations 1. Please do not give the inductors any excessive mechanical shocks.
Technical considerations	 ◆Handling 1. There is a case that a characteristic varies with magnetic influence. ◆Breakaway PC boards(splitting along perforations) 1. Planning pattern configurations and the position of products should be carefully performed to minimize stress. ◆Mechanical considerations 1. There is a case to be damaged by a mechanical shock.

Precautions	 ◆Storage 1. To maintain the solderability of terminal electrodes and to keep the packing material in good condition, temperature and humidity in the storage area should be controlled. • Recommended conditions Ambient temperature: 0~40°C Humidity: Below 70% RH • The ambient temperature must be kept below 30°C. Even under ideal storage conditions, solderability of products electrodes may decrease as time passes. For this reason, product should be used within 6 months from the time of delivery. In case of storage over 6 months, solderability shall be checked before actual usage.
Technical considerations	◆Storage 1. Under a high temperature and humidity environment, problems such as reduced solderability caused by oxidation of terminal electrodes and deterioration of taping/packaging materials may take place.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiyo Yuden:

```
LB1608T1R0M LB1608T2R2M LB1608T4R7M LB1608T8R2M LB2012T100K LB2012T100KR LB2012T100MR LB2012T100MR LB2012T101M LB2012T150K LB2012T1R0M LB2012T20K LB2012T20M LB2012T2R2M LB2012T3R3M LB2012T470K LB2012T470M LB2012T4R7M LB2012T680K LB2012T6R8M LB2016T100K LB2016T100M LB2016T10M LB2016T10M LB2016T150K LB2016T150M LB2016T1R0M LB2016T1R5M LB2016T20K LB2016T20M LB2016T20M LB2016T20M LB2016T330K LB2016T330M LB2016T3R3M LB2016T470K LB2016T470M LB2016T4R7M LB2016T2R2M LB2016T330K LB2016T3R3M LB2016T470K LB2016T470M LB2016T4R7M LB2016T680K LB2016T680M LB2016T6R8M LB2518T100K LB2518T100M LB2518T101M LB2518T101M LB2518T102M LB2518T150K LB2518T150M LB2518T151K LB2518T151M LB2518T1R0M LB2518T185M LB2518T220K LB2518T220M LB2518T221K LB2518T221M LB2518T2R2M LB2518T330K LB2518T331M LB2518T331M LB2518T331M LB2518T331M LB2518T680M LB2518T681K LB2518T681M LB2518T68M LB2518T150M LB2518T151M LB2518T680M LB2518T100M LB3218T100M LB3218T101M LB3218T101M LB3218T102M LB3218T101M LB3218T101M LB3218T102M LB3218T331K LB3218T330M LB3218T30M LB3218T30
```