

Test Probe


GKS-050 214 050 A 1000

Item GKS-050-0001



- Well-established test probes for contacting PCBs
- For optimal contact to the test points (e.g. pads, vias, and pins), various tip styles with various diameters and finishes are available.
- Various spring forces available as well as versions with stainless steel springs suitable for high temperatures
- Used for setting the optimum stroke conditions in the test fixture, various installation heights can be achieved by combining test probes and receptacles

INGUN SELECTION



Test Probe

GKS-050 214 050 A 1000

Item GKS-050-0001



GO TO PRODUCT


ingun[®]

Partner for Future Technology

General data

| | |
|--------------------------------|---|
| Product group | ICT / FCT (in-circuit test and function test) |
| Sub-product group | Standard stroke test probe |
| Series | GKS-050 |
| Grid | 1.27 mm [50 mil] |
| Contacting from | Pad, Pin, Post |
| Magnetic | Yes |
| Installation type | Plug-in |
| Quick-exchange system | Yes |
| Adjustable installation height | No |
| Non-rotating | No |
| Compatible receptacle(s) | KS-050 |
| Min. temperature | - 40 °C [- 104 °F] |
| Max. temperature | + 80 °C [+ 176 °F] |
| RoHS-compliant | Yes |

INGUN SELECTION




Electrical data

| | |
|---------------------------------------|----------|
| Current load capacity / rated current | 2 A |
| Typical resistance (Ri) | <20 mOhm |

Mechanical data

| | |
|--------------------------------|--------------------|
| Total length | 43.2 mm [1.70 in] |
| Barrel diameter | 0.78 mm [0.030 in] |
| Maximum stroke | 6.35 mm [.25 in] |
| Spring pre-load | 0.44 N [1.58 ozf] |
| Collar height | 00 |
| Spring force at working stroke | 1 N [3.59 ozf] |
| Recommended working stroke | 4.3 mm [.169 in] |



Tip style data

| | |
|--------------------|---------------------------------|
| Tip style | 14 4-point crown, self-cleaning |
| Tip diameter | 0.5 mm [.019 in] |
| Tip style surface | A gold |
| Tip style material | 2 steel |

INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 11/22 EN

Weitere Informationen zum Thema
ICT/FCT Test probes

