

Han-Quintax module, female



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 002 3101
Specification	Han-Quintax module, female
HARTING eCatalogue	https://b2b.harting.com/09140023101

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han-Quintax® module
Size of the module	Double module

Version

Termination method	Crimp termination
Gender	Female

Technical characteristics

Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +85 °C
Mating cycles	≥ 500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

Commercial data

Packaging size	2
Net weight	14 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140019898
eCl@ss	27440207 Adapter for industrial connectors (module/contact insert)