# SPECIFICATION



Customer : QUARTZ-1

Applied To :

Product Name: Piezo Buzzer

Model Name: KPI-G3210LC-10686

Drawing No. : OEM10686R

Signature of Appronal

Signature of KEPO

Approved by	Checkde by	Issued by	Date
Toom	两楚性	zninks	2015/10/24

宁波凯普电子有限公司



Ningbo Kepo Electronics Co.,Ltd.

宁波东钱湖镇东钱湖工业区宝源路 25 号

TEL:+86-574-88370330 FAX:+86-574-88370329

No.25 Baoyuan road Dongqian Lake, Industry Area, Dongqian town, Ningbo City, China (Post Code: 315131)

China(Post Code:315121)

Sales@chinaacoustic.com www.chinaacoustic.com

Specification for Buzzer	Page	2/8
<u>'</u>	Revision No.	1.0
Model No. : KPI-G3210LC-10686	Drawing No.	OEM10686R

# **CONTENTS**

- 1. Scope
- 1.范围
- 2. General
- 2.概要
- 3. Maximum Rating
- 3.额定极限条件
- 4. Electrical Characteristics
- 4.电性能
- 5. Measuring Method
- 5.测试方法
- 6. Physical Characteristics
- 6.机械性能
- 7. Environmental Characteristics
- 7.环境性能
- 8. Dimensions
- 8.尺寸
- 9. Packaging Standard
- 9.包装标准
- 10.Cautions
- 10.警告
- 11. Cautions for Use
- 11.注意事项
- 12. Revision
- 12.履历表

Specification for Buzzer	Page	3/8
<u>'</u>	Revision No.	1.0
Model No. : KPI-G3210LC-10686	Drawing No.	OEM10686R

# 1. Scope 范围

This product specification is applied to the piezoelectric sounder in alarm systems. Please contact us when using this product for any other applications than described in the above.

本规格书适用于压电式蜂鸣器,通常它用在系统中做报警或提示的发声器件,如果将该产品用于其它领域,请与我们取得联系。

#### 2. General 概要

2.1 Out-Diameter : Φ32 mm

2.1.外径 : Φ32 mm

2.2 Height : 14.5 mm

2.2. 高度 : 14.5 mm

2.3 Weight : 4 g

2.3 重量 : 4 g

2.4 Case Material : ABS/Black

2.4 壳体材质/颜色 : ABS/Black

## 3. 额定极限条件 Maximum Rating

No.	项目 Item	规 格 Specification
3.1	最高输入电压 Maximum input Voltage	3-24VDC
3.2	工作温度范围 Operating Temperature Range	-20 ~ +60°C
3.3	储存温度范围 Storage Temperature Range	-30 ~ +70°C

# 4. 电性能 Electrical Characteristics

No.	项目 Item	规 格 Specification	
4.1	声压 Sound Pressure Level	90dB at 12VDC/30cm	
4.2	频率 Resonant Frequency	3.7±0.5KHz	
4.3	电流 Max.Rated Current	15mA at 12VDC	
4.4	音调 Tone Nature	Continuous	

测试条件参见下项


Refer to next item for measuring method.

Specification for Buzzer	Page	5/8
'	Revision No.	1.0
Model No. : KPI-G3210LC-10686	Drawing No.	OEM10686R

## 5. 测试方法 Measuring Method

5.1 声压测试线路 S.P.L. Measuring Circuit

输入信号:12VDC Input Signal:12VDC



声级计: ND10 或等同品 Sound meter: ND10 or equivalent

S.G.: DF1731SL3A稳压电源或等同品

S.G.: DF1731SL3A DC Power Supply or equivalent

#### 5.2 测试环境 Measuring Condition

温度+25±3℃,湿度60±10%R.H.标准测试状态,在没有疑问的场合,可以在温度+5~+35℃,湿度45~85%R.H.的范围内测试.

Part shall be measured under a condition (Temperature :+5 to +35 $^{\circ}$ C,Humidity:45 to 85%R.H.)unless the standard condition (Temperature :+25 $\pm$ 3 $^{\circ}$ C,Humidity:60 $\pm$ 10% is regulated measure.

# 6. 机械性能 Physical Characteristics

No.	实验项目 Item	实验条件 Test Condition	实验后规格 Specification
6.1	耐冲击性 Shock	峰值加速度490m/s²,半正弦波,XYZ三个方向各3次冲击实验后,测试声响器. Sounder shall be measured after being applied shock(490m/s²) for each three mutually perpendicular directions to each of 3 times by half sine wave.	
6.2	耐振动性 Vibration	振动频率 10~55 Hz,1.5mm 全振幅, XYZ 三个方向各2小时试验后,测试声响器. Sounder shall be measured after being applied vibration of amplitude of 1.5mm with 10 to55Hz band of vibration frequency to each of 3 perpendicular directions for 2 hours.	符合表1的要求 The measured value shall meet Table 1.
6.3	抗跌落性 Dropping	75cm高度/2回自然落到亚麻布垫上. Dropped from 75cm high to linen with 2 times.	

Specification for Buzzer	Page	4/8
<u>'</u>	Revision No.	1.0
Model No. : KPI-G3210LC-10686	Drawing No.	OEM10686R

# 7. 环境性能 Environmental Characteristics

No.	实验项目 Item	实验条件 Test Condition	实验后规格 Specification
7.1	高温放置 Dry Heat Test (Storage)	放置于温度+70±2℃的烘箱内240小时,然后取出,在常温下放置4小时后,测试声响器After being placed in a chamber with +70±2 for 240 hours and then being placed in natural condition for 4 hours, sounder shall be measured.	
7.2	低温放置 Cold Heat Test (Storage)	放置于温度-30±2℃的制冷箱内240小时,然后取出,在常温下放置4小时后,测试声响器After being placed in a chamber with -30±2 for 240 hours and then being placed in natural condition for 4 hours, sounder shall be measured.	
7.3	耐湿性 Humidity	放置于 90% ~ 95% R.H.,温度+60±2℃的环境 试验箱内240小时,然后取出,在常温下放置4小 时后,测试声响器 After being placed in a chamber with 90 to 95%R.H. at +60±2℃ for 240 hours and the being placed in natural condition for 4 hours, sounder shall be measured.	符合表1的要求 The measured value shall meet Table 1.
7.4	温度循环 Temperature Cycle	先放置于温度-30±2℃的制冷箱内30分钟,然后放置于室温(+20℃)15分钟后,放置于+70±2℃的烘箱内30分钟,再放置于室温(+20℃)15分钟,经过以上循环5次,在常温下放置4小时后,测试声响器 After being placed in a chamber at -30±2℃ for 30 minutes, sounder shall be placed at room temperature(+20℃). After 15 minutes at this temperature, sounder shall be placed in a chamber at +70±2℃. After 30 minutes this temperature, sounder shall be returned to room temperature (+20℃) for 15 minutes After 5 above cycles, sounder shall be measured after being placed in natural condition for 4 hours.	

#### 表 1 Table 1

项 目	试验后变化量
Item	Specification after test
声压级	初始值±10dB
Sound Pressure Level	Initial Value±10dB

Specification for Buzzer	Page	6/8
	Revision No.	1.0
Model No. : KPI-G3210LC-10686  8. 尺寸 Dimensions	Drawing No.	OEM10686R
(UL1007/26# Black) (UL1007/26# Red)  Housing: HRose IF3-25-27. Termind: HRose IF3-26/28SI	HRose DF3-2428SCF	
FIRST ANGLE PROJECTION		: mm nce : ±0.2

Specification for Buzzer	Page	7/8
'	Revision No.	1.0
Model No. : KPI-G3210LC-10686	Drawing No.	OEM10686R

#### 9. 包装标准 Packaging Standard

产品的外包装是纸箱,它应该清楚的标明型号,数量,出厂检验批号.在运输及储存的过程中,产品必须不会受到机械损伤.

Each minimum package unit of products shall be in a carton box and it shall be clearly marked with Part Number, quantity and outgoing inspection number.

There shall be no mechanical damage on products during transportation and/or in storage.

#### 10. 警告 Cautions

如果产品使用于下列高可靠性的装置时,请与我们取得联系,以免对人的生命,财产和身体造成损害.

Please contact us before using our products for the undermentioned applications requiring especially high reliability in order to prevent defects which might directly cause damage to other party'slife, body or property(listed below).

- (1)Aircraft equipment 飞行设备
- (2)Aerospace equipment 航天设备
- (3)Undersea equipment 潜水设备
- (4)Medical equipment 医疗设备
- (5)Transportation equipment (automobiles, trains, ships) 交通设施
- (6)Traffic signal equipment 交通信号设备
- (7)Disaster prevention/crime prevention equipment 防灾害/防犯罪设备
- (8)Data-processing equipment 数据处理设备
- (9)Applications of similar complexity or reliability requirements comparable to the applications listed in the above 以及与上述相类似或可靠性要求更高的设备

#### 11. 注意事项 Cautions for Use

11.1 如果产品所承受的机械应力超过规定的值,元件可能被破坏.

The component may be damaged if mechanical stress over this specification is applied.

11.2 请注意保护工作电路不会因失误,跌落和温度变化而产生浪涌电压.

Please pay attention to protect operating circuit from surge voltage provided by something of force such as failing ,shock and temperature changing.

11.3 该蜂鸣器不适合洗涤,因为它不密封.

Washing of the component is not acceptable. Because it is not sealded

11.4 在使用烙铁的情况下,应注意烙铁头的温度应该保持在+350℃以下,并且焊接时间控制在3秒内.

In case of using solder iron for soldering, the top of soldering iron's temperature should be kept less than  $+350^{\circ}$ C. Moreover the soldering time should be also kept w in 3seconds.

Specification for Buzzer				Page	8/8	
				Revision No.	1.0	
Model No. : KPI-G3210LC-10686				Drawing No.	OEM106	86R
	12. Revis	ion 履	<b></b>			
Rev. No.	DATE	PAGE	DESCRIPTION			вом
1.0	2015-10-24		Primary			