


Cable-sensor

Type K4RS

Issue 11/19

Sensor

1 x Pt100 F0,3 (old cl. B) DIN EN 60751
2-, 3- or 4-wire-circuit



Protective tube material

1.4571

thread x insert length

M6 x 20 mm (200°C) 4-wire -> 1
M6 x 30 mm (200°C) 4-wire -> 2
M8 x 40 mm (200°C) 2- or 3-wire -> 3
M10 x 40 mm (400°C) 2- or 3-wire -> 4

Cable


TeSi 2x0,34 or 3x0,34 or 4x0,14 (200°C)
GIGIV 2x0,34 or 3x0,22 (400°C)

Cable length

2500 mm

Order example

K4-E-4LS-200 - 1



Subject to change without notice

D- 99331 Geratal OT Geraberg, Gewerbepark 6

Tel: +49 (0) 3677 / 7956-0 // Fax: +49 (0) 3677 / 795 625

E-Mail: info@electrotherm.de

Internet: www.electrotherm.de