

## Specifications

Functions	Range	Resolution	Accuracy	BT508	BT510	BT520	BT521
Battery resistance <sup>1</sup>	3 mΩ	0.001 mΩ	1 % + 8	•	•	•	•
	30 mΩ	0.01 mΩ	0.8 % + 6	•	•	•	•
	300 mΩ	0.1 mΩ	0.8 % + 6	•	•	•	•
	3000 mΩ	1 mΩ	0.8 % + 6	•	•	•	•
Vdc	6 V	0.001 V	0.09 % + 5	•	•	•	•
	60 V	0.01 V	0.09 % + 5	•	•	•	•
	600 V	0.1 V	0.09 % + 5	•	•	•	•
	1000 V	1 V	0.09 % + 5				•
Vac (45 Hz to 500 Hz with 800 Hz filter)	600 V	0.1 V	2 % + 10		•	•	•
Frequency (displayed with Vac and Aac) <sup>2</sup>	500 Hz	0.1 Hz	0.5 % + 8		•	•	•
AC voltage ripple (20 KHz Max)	600 mV	0.1 mV	3 % + 20		•	•	•
	6000 mV	1 mV	3 % + 10		•	•	•
Adc/Aac (with accessory Fluke i410)	400 A	1 A	3.5 % + 2				•
Temperature	0 °C to 60 °C	1 °C	2 °C (4 °F)				•
Meter mode	999 records for each measurement position with time stamp						
Sequence mode	Up to 100 profiles and 100 profile templates (Each profile stores up to 450 batteries) with time stamp						

<sup>1</sup>The measurement is based on ac injection method. The injected source signal is <100 mA, 1 kHz.

<sup>2</sup>Trigger level VAC: 10 mV, Aac: 10 A

## Measurement modes

	BT508	BT510	BT520	BT521
Resistance (mΩ)	•	•	•	•
Battery voltage	•	•	•	•
Voltage dc	•	•	•	•
Voltage ac and frequency (Hz)		•	•	•
Ripple volt		•	•	•
Temperature of negative battery post				•
DC and ac current (and frequency)				•
DMM mode	•	•	•	•
Sequence mode		•	•	•
Discharge measurement mode		•	•	•
Automatic measurement save	•	•	•	•
Wireless communication				•
Memory view	•	•	•	•

## General specifications

<b>Size (HxWxD)</b>	22 cm x 10.3 cm x 5.8 cm (9 in x 4 in x 2 in)
<b>Weight</b>	850 g (1.9 lb)
<b>Screen dimensions</b>	7.7 cm x 5.6 cm (3 in x 2.2 in)
<b>Interface</b>	USB mini

## Environment specifications

<b>Operating temperature</b>	0 °C to 40 °C
<b>Storage temperature</b>	-20 °C to 50 °C
<b>Lithium-ion battery charging temperature</b>	0 °C to 40 °C
<b>Operating humidity</b>	Non-condensing (10 °C)
	<=80 % RH (at 10 °C to 30 °C)
	<=75 % RH (at 30 °C to 40 °C)
<b>Operating altitude</b>	Sea level to 2000 meters
<b>Storage altitude</b>	Sea level to 12,000 meters
<b>IP rating</b>	IP40
<b>Radio</b>	FCC Class A
<b>Vibration requirements</b>	MIL-PRF-28800F: Class 2
<b>Drop test requirements</b>	1 meter
<b>Temperature coefficients</b>	Add 0.1 x specified accuracy for each degree C above 28 °C or below 18 °C
<b>Safety compliance</b>	600 V CAT III
<b>EMC</b>	IEC 61326
<b>ROHS</b>	China, Europe
<b>Protection Class 2</b>	Pollution Degree II
<b>Battery compliance</b>	UN38.3
	UL2054
	IEC62133
	2G per IEC68-2-26, 25G, and 29

## Ordering Information

**Fluke BT508** Simple Battery Analyzer  
**Fluke BT510** Basic Battery Analyzer  
**Fluke BT520** Battery Analyzer  
**Fluke BT521** Advanced Battery Analyzer

### Accessories

**BTL10** Basic Battery Analyzer Test Leads  
**BTL20** Interactive Battery Analyzer Test Probe  
**BTL21** Interactive Battery Analyzer Test Probe with temperature sensor

**BTL-A** Voltage/Current Probe Adapter  
**C500S** Soft carrying case (small)  
**C500L** Soft carrying case (large)  
**BC500** AC Power Charger  
**BP500** Lithium-ion battery 3000 mAh  
**TPAK80-4** Magnetic Strap  
**B4WTP** 4-wire test pin  
**i410** AC/DC Current Clamp  
**L300** LED flashlight  
**BCR** Zero ohm calibration resistor

## Items supplied with each model

Equipment	Qty.	BT508	BT510	BT520	BT521
Battery analyzer	1	•	•	•	•
4-wire test pin (set)	1	•	•	•	•
BTL10 Basic Test Lead (set)	1	•	•	•	•
TL175 TwistGuard™ Test Leads with adapter	1	•	•	•	•
L300 Attachable LED Flashlight	2			•	•
BTL20 Intelligent Test Probe Set, with extender (no temperature sensor)	1			•	
BTL21 Intelligent Test Probe set, with extender and temperature sensor	1				•
i410 AC/DC Current Clamp	1				•
BP500 7.4 V 3000 mAh lithium-ion battery	1	•	•	•	•
BC500 18 V AC Charger	1	•	•	•	•
Standard mini-b USB cable (cable length:1 m)	1	•	•	•	•
Shoulder strap	1	•	•	•	•
Belt strap	1	•	•	•	•
Magnetic hanging strap	1	•	•	•	•
FlukeView® Battery Management (CD) containing USB driver and manuals in all languages	1	•	•	•	•
Soft carrying case	1	•	•	•	•
Spare fuses	2	•	•	•	•
Paper battery tags	100			•	•

**Fluke.** *Keeping your world up and running.*®

### Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

### Fluke Europe B.V.

PO Box 1186, 5602 BD Eindhoven, The Netherlands

### For more information call:

In the U.S.A. (800) 443-5853 or  
 Fax (425) 446-5116  
 In Europe/M-East/Africa +31 (0) 40 2675 200 or  
 Fax +31 (0) 40 2675 222  
 In Canada (800)-36-FLUKE or  
 Fax (905) 890-6866  
 From other countries +1 (425) 446-5500 or  
 Fax +1 (425) 446-5116  
 Web access: <http://www.fluke.com>

©2014 Fluke Corporation.  
 Specifications subject to change without notice.  
 Printed in U.S.A. 5/2014 6002460B\_EN

**Modification of this document is not permitted without written permission from Fluke Corporation.**