


	Y						B
	Au		YES	ALL	200	1-2336568-0	
	Au				200	2336568-9	
	Au		NO	ALL	100	2336568-8	
F	^D d Ni				50	2336568-7	-
	Au				200	2336568-6	
	Au		YES	ENDS	100	2336568-5	
F	^p d Ni				50	2336568-4	
	Au				200	2336568-3	
	Au		YES	ALL	100	2336568-2	
F	^D d Ni				50	2336568-1	
V	G		ICK AND ACE TAPE	HOLD DOWNS	MATING CYCLES	P A R T N U M B E R	A
С	ONTROLLED DOG	CUMENT.	Dwn 10MAY C. VALENTINE снк 10MAY D. HARMON	2018		TE Connectivity	
]	TOLERANCES OTHERWISE SPE 0 PLC ±- 1 PLC ±- 2 PLC ±-	UNLESS CIFIED:	APVD 10MAY D. HARMON PRODUCT SPEC 108-130021	RECER	PTACLE ASSEMBLY Positon, silver		
ţ	3 PLC ±- 4 PLC ±- ANGLES	±-	APPLICATION SPEC 114-130008	SIZE CAGE		RESTRICTED TO	
	FINISH	\	weight _	A 1 -			-
	<u> </u>	۲	CUSTOMER DRAWING		SCALE 8:	1 SHEET OF REV B	

2			1			
			REVISIONS			
	Р	LTR	DESCRIPTION	DATE	DWN	APVD
		A	REVISED PER ECO-19-011916	06AUG2019	AP	JW
		В	REVISED PER ECN-21-116535	07SEP2021	ТΧ	DZ

	8 This drawing is unpublished.	RELEASED FOR PUBLICATION 20
D	C COPYRIGHT 20 BY -	ALL ORGANIZERS WITHOUT HEAT STAING
C		DETAIL A SCALE 10:1
В		LETAIL C SCALE 10:1
А		

4805 (3/13)




MATERIAL
MATENTAL

\cap	
1	
_	

			REVISIONS			
Ρ	LTR		DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1		-	-	-

1


DRAWING IS A C	ONTROLLED DOCUMENT.	DWN 10MAY2018 C. VALENTINE CHK 10MAY2018	TE Connectivity
DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:	D. HARMON APVD 10MAY2018 D. HARMON	NAME RECEPTACLE ASSEMBLY, RIGHT ANGLE,
	0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±-	PRODUCT SPEC 108-130021 APPLICATION SPEC	168 POSITON, SILVER 2.0
+ 1	4 PLC ±- ANGLES ±- FINISH	114-130008 WEIGHT	SIZE CAGE CODE DRAWING NO RESTRICTED TO
		-	$\begin{vmatrix} A \end{vmatrix} - \begin{vmatrix} C - 2336568 \end{vmatrix} - \begin{vmatrix} SHEET & OF \\ REV \end{vmatrix}$
		CUSTOMER DRAWING	8:1 2 5 B



4805 (3/13)

THIS	DRAWING	ΙS	А	(
	DIMENSIONS	:		
	mm			
	\leftarrow			7
	ÐÐ	_		
MATERIA	L			

CUSTOMER DRAWING



4805 (3/13)

TE Connectivity M^eRECEPTACLE ASSEMBLY, RIGHT ANGLE, 168 POSITON, SILVER 2.0 108-130021 APPLICATION SPEC 2 PLC 3 PLC 4 PLC SIZE CAGE CODE DRAWING NO RESTRICTED TO 114-130008 C-2336568 MATERIAL WEIGHT --SCALE 10:1 SHEET OF REV B CUSTOMER DRAWING





	REVISIONS					
Ρ	LTR	DESCRIPTION	DATE	DWN	APVD	
	-	SEE SHEET 1	-	-	-	













8		7	6
THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20	
C COPYRIGHT 20 BY -	ALL RIGHTS RESERVED.		

CONNECTOR CONTACT IDENTIFICATION Δ

CONTACT NUMBER	SIDE A	SIDE B
36	SIGNAL	SIGNAL
37	SIGNAL	SIGNAL
38	GROUND	GROUND
39	SIGNAL	SIGNAL
40	SIGNAL	SIGNAL
4 1	GROUND	GROUND
42	GROUND	GROUND
43	GROUND	GROUND
44	SIGNAL	SIGNAL
4 5	SIGNAL	SIGNAL
46	GROUND	GROUND
47	SIGNAL	SIGNAL
48	SIGNAL	SIGNAL
49	GROUND	GROUND
50	SIGNAL	SIGNAL
5 1	SIGNAL	SIGNAL
52	GROUND	GROUND
53	SIGNAL	SIGNAL
54	SIGNAL	SIGNAL
55	GROUND	GROUND
56	SIGNAL	SIGNAL
57	SIGNAL	SIGNAL
58	GROUND	GROUND
59	SIGNAL	SIGNAL
60	SIGNAL	SIGNAL
6 1	GROUND	GROUND
6 2	SIGNAL	SIGNAL
63	SIGNAL	SIGNAL
64	GROUND	GROUND
65	SIGNAL	SIGNAL
66	SIGNAL	SIGNAL
67	GROUND	GROUND
68	SIGNAL	SIGNAL
6 9	SIGNAL	SIGNAL
70	GROUND	GROUND

CONTACT NUMBER	SIDE A	SIDE B
1	GROUND	GROUND
2	SIGNAL	SIGNAL
3	SIGNAL	SIGNAL
4	GROUND	GROUND
5	SIGNAL	SIGNAL
6	SIGNAL	SIGNAL
7	GROUND	GROUND
8	SIGNAL	SIGNAL
9	SIGNAL	SIGNAL
1 0	GROUND	GROUND
1 1	SIGNAL	SIGNAL
1 2	SIGNAL	SIGNAL
1 3	GROUND	GROUND
1 4	SIGNAL	SIGNAL
1 5	SIGNAL	SIGNAL
1 6	GROUND	GROUND
1 7	SIGNAL	SIGNAL
18	SIGNAL	SIGNAL
19	GROUND	GROUND
20	SIGNAL	SIGNAL
2 1	SIGNAL	SIGNAL
2 2	GROUND	GROUND
23	SIGNAL	SIGNAL
2 4	SIGNAL	SIGNAL
2 5	GROUND	GROUND
26	SIGNAL	SIGNAL
27	SIGNAL	SIGNAL
28	GROUND	GROUND
29	GROUND	GROUND
30	SIGNAL	SIGNAL
3 1	SIGNAL	SIGNAL
32	GROUND	GROUND
33	SIGNAL	SIGNAL
34	SIGNAL	SIGNAL
35	GROUND	GROUND

Α1.

DETAIL H SCALE 4:1

4805 (3/13)

HARD TRAY PACKAGING-1. DIMENSIONS: TRAY: L= (330), W= (136), H= (14.5)


2. QUANITY: 32 pieces per tray.



5


CONTACT		
NUMBER	SIDE OA	SIDE OB
1	GROUND	GROUND
2	SIGNAL	SIGNAL
3	SIGNAL	SIGNAL
4	GROUND	GROUND
5	SIGNAL	SIGNAL
6	SIGNAL	SIGNAL
7	GROUND	GROUND
8	SIGNAL	SIGNAL
9	SIGNAL	SIGNAL
1 0	GROUND	GROUND
1 1	SIGNAL	SIGNAL
1 2	SIGNAL	SIGNAL
1 3	GROUND	GROUND
1 4	GROUND	GROUND

4



3

DETAIL J SCALE 4:1




—see detail H CHAMFERED CORNER-

FIGURE 1 HARD TRAY PACKAGING APPLIES TO 2336568-1 THRU 2336568-8, AND 1-2336568-0 SCALE 1:1

THIS DRAWING IS A DIMENSIONS: mm

			1	
		REVISIONS		
Р	LTR	DESCRIPTION	DATE	DWN
	-	SEE SHEET 1	-	-
	P	P LTR -	P LTR DESCRIPTION	P LTR DESCRIPTION DATE





CONTROLLED DOCUMENT.		DWN 10MAY2018 C. VALENTINE CHK 10MAY2018	_		E T	E TE	Conne	; tivi	t y
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±-	D. HARMON APVD 10MAY2018 D. HARMON PRODUCT SPEC 108-130021	RECEPTACLE ASSEMBLY, RIGHT ANGLE, 168 POSITON, SILVER 2.0						
	3 PLC ±- 4 PLC ±- ANGLES ±- FINISH	APPLICATION SPEC 114-130008 WEIGHT _	size A 1	CAGE CODE -	drawing no				RESTRICTED TO
		CUSTOMER DRAWING				scale 8:1	SHEET	OF	5 ^{rev} B