

Industrial Power Supplies

TIB 240 Series, 240 Watt

- Slim profile, for DIN-rail mounting
- Alternative side-mounting for flat panels
- High power factor by active power correction
- Very high efficiency up to 95%
- Back power immunity
- 150% peak current for 4 sec.
- Operating temperature range: -40°C to +70°C max.
- Adjustable output voltage
- DC-OK indicator
- Short circuit and overload protection
- Class I, division 2 approval and ATEX certification for EX models
- 5-year product warranty for EX models



Other output power of same series:
www.tracopower.com/overview/tib

This generation of DIN-rail power supplies combines the most efficient circuit topology with optimized cost/performance ratio for industrial environments and for electrical control cabinets.

They have a very high efficiency of up to 95.0% which allows a very slim package design. The output voltage is adjustable from -2% to +17%. The case offers the potentially useful feature to fix the DIN-rail clip to the side wall for the mounting inside flat panels. Over a period of minimum 4 seconds they can operate with a boost power of 150%. The boost power facilitates the activation of stepper motors, solenoids or actuators. The units operate with a high power factor of up to 98% by active power factor correction which also keeps the input inrush current low. The TIB series are also available with other nominal power of 80, 120 or 480 Watt (+50% boost power). They come with the safety standard approvals for IEC/EN 60950-1, UL 60950-1 and UL 508.

Models				
Order Code	Output Power (max.)	Output Voltage nom. (adjustable)	Output Current (max.)	Efficiency (typ.)
TIB 240-124	240 W	24 VDC (23.5–28.0)	10 A	95.0 %
TIB 240-124EX				
TIB 240-148	240 W	48 VDC (47.0–56.0)	5 A	95.0 %
TIB 240-148EX				

Input Specifications

Input voltage	– nominal ranges – effective ranges	100 – 240 VAC 85 – 264 VAC (below 90 VAC a derating of 3%/V is required)
Input voltage frequency		45 – 65 Hz
Standby power consumption		2.3/2.3 W (115/230 VAC)
Power Factor Correction (PFC)		0.98/0.92 (115/230 VAC)
Harmonic limits	– acc. EN 61000-3-2	class A, D
Inrush current		15/30 A max. (115/230 VAC)

Output Specifications

Output voltage adjustment ¹⁾		24 Vout models: 23.5 – 28.0 V 48 Vout models: 47.0 – 56.0 V
Regulation	– Input variation – Load variation (10–90 %)	0.1 % max. 0.5 % max.
Temperature coefficient		0.02 %/K
Hold-up time		20 ms min.
Start-up time		2 s max.
Ripple and Noise (20MHz bandwidth)		24 Vout models: 100 mVp-p max. 48 Vout models: 200 mVp-p max.
Output overvoltage protection (OVP) ²⁾		24 Vout models: 32 – 35 V 48 Vout models: 56 – 60 V
Power back immunity ³⁾		< OVP level
Operation	– Nominal operation – Peak power operation – Constant current (cc)	100 % of Iout nom. 105 – 150 % of Iout nom. > 155 % of Iout nom.
Duty cycle ⁴⁾ (for peak and cc mode)	– Threshold – CC or peak operation timer – normal operation / off period	> 105 % 4 s max. (switch off) 10 s typ. (automatic restart after switch off or peak and cc operation timer reset)
Short circuit		Switch off after 4s delay, automatic restart
DC OK signal	– Threshold for Vout – DC ON – DC OFF	24 Vout models: on: > 22.5 V typ., off: < 21.5 V typ. 48 Vout models: on: > 45 V typ., off: < 43 V typ. relay contact closed, 1 A max., < 100 mOhm (also indicated by green LEDs: front and side) relay contact open, 30 V max.

¹⁾ Output voltage can be adjusted as indicated. However, output power has to be maintained at nominal value. This means the output nominal current has to be reduced in accordance with the increase of output voltage.

²⁾ In case of an internal error a second voltage regulation loop keeps the output voltage at a safe level, the power supply turns off and restarts after typ. 10 seconds.

³⁾ When external voltage is supplied above set output voltage and below OVP threshold, the power supply will function normally without switch off or destruction, even if external voltage is applied continuously.


⁴⁾ In case of overload or short circuit, the unit switches the output voltage off after 4 seconds and tries to restart every typ. 10 seconds.

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.


General Specifications

Operating temperature range		-40°C to +70°C max.
Derating		2 %/K above +60°C
Cooling		convection cooling, no internal fan
Overtemperature protection		switch off at overtemperature
Humidity (non condensing)		5–95 % rel. H max.
Altitude during operation		2000 m max.
Isolation Voltage	<ul style="list-style-type: none"> – Input/Ouput – Input/Chassis – Ouput/Chassis 	4250 VDC 1500 VDC 750 VDC
Creepage Clearance	<ul style="list-style-type: none"> – Input/Ouput – Input/Chassis – Output/Chassis 	8 mm 4 mm 1.5 mm
MTBF (acc. to IEC 61709 at 25°C)		> 1'300'000 h
Safety standards	<ul style="list-style-type: none"> – Information technology equipment – Safety low voltage switchgear and controlgear – ATEX for hazardous location (EX models only) – UL HazLoc (EX models only) – Certification documents 	IEC/EN 60950-1, UL 60950-1 CSA 22.2 No 60950-1-03 UL 508 EN 60079-0, EN 60079-7, EN 60079-15 (EX II3G Ex ec nC IIC GC) Class I, Division 2 www.tracopower.com/overview/tib
Electromagnetic compatibility (EMC), Emissions	<ul style="list-style-type: none"> – Conducted emission input – Radiated RI emission 	EN 61000-6-3, EN 61204-3 EN 55032, EN 55011 class B EN 55032, EN 55011 class B
Electromagnetic compatibility (EMC), Immunity	<ul style="list-style-type: none"> – Railway applications signalling apparatus – Railway applications rolling stock apparatus – Electrostatic discharge (ESD) – Radiated RF field immunity – Electrical fast transient / burst immunity – Surge immunity – Immunity to conducted RF disturbances – Power frequency field immunity – Mains voltage dips and interruptions – Voltage sag immunity 	EN 61000-6-2, EN 61204-3 EN 50121-4 EN 50121-3-2 IEC/EN 61000-4-2 4 kV/8 kV criteria A IEC/EN 61000-4-3 10 V/m criteria A IEC/EN 61000-4-4 2 kV criteria B IEC/EN 61000-4-5 1 kV/2 kV criteria B IEC/EN 61000-4-6 10 V criteria A IEC/EN 61000-4-8 30 A/m criteria A IEC/EN 61000-4-11 criteria B/C SEMI F47 (230 VAC) criteria A
Environment	<ul style="list-style-type: none"> – Railway applications shock and vibration – Vibration acc. IEC 60068-2-6-3 – Shock acc. IEC 60068-2-27 	according EN 61373 3 axis, 2 g sine sweep, 10–55 Hz, 11 okt/min 3 axis, 25 g half sine, 11 ms
Enclosure material	<ul style="list-style-type: none"> – Chassis – Cover 	aluminium stainless steel
Mounting	<ul style="list-style-type: none"> – DIN-rail mounting 	for DIN-rails as per EN 50022-35×15/7.5
Environmental compliance	<ul style="list-style-type: none"> – Reach – RoHS 	www.tracopower.com/info/reach-declaration.pdf RoHS directive 2011/65/EU
Connection		screw terminals

Function Specification




Output Characteristic




Characteristic: Output voltage vs output current for overload conditions until switch off after 4s at nominal input voltages

Output Characteristic (continued)




Derating: max load vs input voltage




Derating: Load vs ambient temperature

Outline Dimensions



* Measurement from front panel to DIN-Rail



Weight: 643g (22.68 oz)

Alternative side mounting:

