

Crimping pliers - CRIMPFOX-RCT 25-1 - 1212066

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for non-insulated conduit lugs, 10 - 25 mm², HEX crimp

Why buy this product

- ✓ CRIMPFOX-RC 10 and ...RCT 25-1 complete the range of crimping pliers for uninsulated cable lugs and insulated tube lugs
- ✓ All pliers of this type reduce the amount of force required during crimping by 25%



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 454063
Weight per Piece (excluding packing)	661.6 g
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	256 mm
Height	68 mm
Width (a)	25 mm

General

Color	black
Compression	HEX crimp
Type of contact	CU conduit lugs
Designation	Crimping position 1
Max. cross section	10 mm ²
AWG max	8
Outside diameter	7.00 mm
Internal diameter	4.50 mm

Crimping pliers - CRIMPFOX-RCT 25-1 - 1212066

Technical data

General

Designation	Crimping position 2
Max. cross section	16 mm ²
AWG max	6
Outside diameter	8.50 mm
Internal diameter	5.50 mm
Designation	Crimping position 3
Max. cross section	25 mm ²
AWG max	4
Outside diameter	10.00 mm
Internal diameter	7.00 mm

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

Approvals

Approvals

Approvals

EAC

Crimping pliers - CRIMPFOX-RCT 25-1 - 1212066

Approvals

Ex Approvals

Approvals submitted

Approval details

EAC

Accessories

Accessories

Die

Replacement die - CRIMPFOX-RCT 25-1/DIE - 1212300



Spare die for CRIMPFOX-RCT 25-1

Mounting material

Replacement spring - CRIMPFOX/ SPR-1 - 1212069



Spare recuperating spring
