

Flexible NFC Antenna

Part No: FXR.01.07.0100C.A

Description:

Flexible Near-Field Communications Reader Antenna With 100mm 1.37 cable and I-PEX MHF® I U.FL compatible

TAOGLAS

Features:

13.56MHz Peel and Stick Antenna Cable: 100mm 1.37 microcoax Connector: I-PEX MHF® I U.FL compatible Read distance out to 5 cm Adheres directly to product inner housing Dimensions: 53.3*36.8mm RoHS & Reach Compliant



1.	Introduction	3
2.	Specifications	4
3.	Antenna Characteristics in Free Space	5
4.	Antenna Characteristics on 1mm ABS	6
5.	Antenna Applications	8
6.	Mechanical Drawing	9
7.	Packaging	10
	Changelog	11

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.





1. Introduction



Taoglas has developed an NFC (Near Field Communications) antenna for use with NFC readers. This standard design is matched to a 50 Ohm system and provides a well-matched solution for NFC readers. The antenna is dimensioned to provide the capability of interrogating typical size NFC tags out to a 5 cm. distance. This standard antenna is delivered with a coaxial cable connected to the antenna element to ease use and integration into customer devices.

The flex design provides a flexible antenna that can be adhered to the plastic enclosure of the customer device. At only 0.1mm thickness it allows antenna placement in small devices and takes minimum footprint.

The standard NFC antenna has an integrated matching circuit to provide a well-matched antenna. The Q of the antenna/matching circuit combination has been selected to provide a solution where the bandwidth and read performance have been optimized for best tag interrogation performance. Along with the integrated coaxial cable, this antenna is read to connect to the reader for quick installation and operation.

This standard antenna design can be modified to provide a customized solution where the antenna area is maximized for a specific application to enhance interrogation distance. With the NFC protocol being based on magnetic coupling between the reader antenna and the NFC tag antenna, antenna area will directly relate to interrogation distance. Three areas of modification that can be undertaken are:

- Optimize area of the antenna design for a specific application
- Customize matching circuit for a specific application
- Apply ferrite material to improve interrogation distance

The cable and connector are fully customizable, for further information please contact your regional Taoglas customer support team.



Specifications

2.

Electrical				
Frequency	13.56MHz			
Return Loss	>10dB (on 1mm ABS holder)			
Impedance	50Ω			
Self-Resonance Frequency	96MHz			
Q Factor	16			
Ls	1.54uH			
Rs	8.12			

* All Testing was done using a Agilent 4285A LCR Meter calibrated at 13.56MHz.
** Testing was completed using series mode, but were was conducted using parallel method as well.

Mechanical			
Antenna Dimensions	53.3mm x 36.8mm		
Connector	I-PEX MHF [®] I U.FL compatible		
Standard Cable	100mm Mini-Coax. 1.37mm		
Adhesive	3M 467		
RoHS Compliant	Yes		
REACH Compliant	Yes		
Environmental			
Temperature Range	-40°C to 85°C		



Antenna Characteristics in Free Space





3.2 Matching

5	82 pF 0603 Components	001511L0100XXA	Ceramic	White	1
6	680 Ohm 0603 Resistor	001512A0100XXA	Ceramic	White	1
\bigcirc	39 pF 0603 Components	001512A0200XXA	Ceramic	White	1





Antenna Characteristics on 1mm ABS





4.2 Return Loss









www.taoglas.com 7





ABS Thickness

For customization reference, we place Taoglas FXR.01 antenna on ABS material boards with different

thickness.

5.1



5.2 Proximity to Metal Ground

The minimum distance of the antenna placement away from metal is 15mm recommended.





Mechanical Drawing (Units: mm)



6.



7. Packaging

10pcs FXR.01.07.0100C.A per PE Bag Bag Dimensions: 300*100mm 1000.0 Weight: 120g Doorte 300mm 1008.45 Prison. 100mm 1,000pcs FXR.01.07.0100C.A per Large PE Bag Carton: 390*470mm BORNE Weight: 1.4Kg 2 2 BORAS -Toosa 470mm **** NORT THORNE 100 511000L ----× 390mm 4,000pcs FXR.01.07.0100C.A per carton Carton: 390*270*350mm Weight: 6Kg 350mm 390mm 270mm Pallet Dimensions: 1200*1100*1100mm 45 Cartons per Pallet 9 Cartons per layer, 5 Layers 1100mm

1200mm

SPE-14-8-109-H

1100mm



Changelog for the datasheet

SPE-14-8-109 - FXR.01.07.0100C.A

Revision: H (Current Version)		
Date:	2022-05-30	
Changes:	Updated spec table	
Changes Made by:	Cesar Sousa	

Previous Revisions

Revision: G		Revision: B	n: B	
Date:	2022-03-07	Date:	2015-01-13	
Changes:	Updated spec table	Changes:	Updated Introduction	
Changes Made by:	Gary West	Changes Made by:	Aine Doyle	

Revision: F		Revision: A (Original First Release)		l First Release)
Date:	2021-02-17		Date:	2014-10-24
Changes:	New Values Added		Notes:	
Changes Made by:	Jack Conroy		Author:	Technical Writer

Revision: E		
Date:	2019-11-15	
Changes:	Images Updated	
Changes Made by:	Russell Meyler	

Revision: D		
Date:	2017-05-07	
Changes: Updated Based on PCN		
Changes Made by:	Andy Mahoney	

Revision: C			
Date:	2016-11-15		
Changes:	Packaging Details Updated		
Changes Made by:	Jack Conroy		



www.taoglas.com