


P. C. B LAYOUT  
TOP VIEW



5	TERMINAL	1	BRASS $\delta=0.2$	SILVER PLATING
4	BODY	1	PA66	BLACK
3	SPRING PLATE	1	BE-BRONZE $\delta=0.065$	SILVER PLATING
2	COVER	1	POM	BLACK
1	BUTTON	1	POM	WHITE
NO.	PART	QTY	MATERIAL	COLOR

**ELECTRIC PERFORMANCE:**

Current Range: 0.1A, 30VDC

Operation Temperature:  $-10^{\circ}\text{C} \sim +60^{\circ}\text{C}$

Storage Temperature:  $-20^{\circ}\text{C} \sim +70^{\circ}\text{C}$

Contact Resistance: 500M $\Omega$  MAX.

Insulation Resistance: 100M $\Omega$  MIN. (Measurements shall be made following application of 100VDC potential across terminals)

Dielectric Withstanding Voltage: 100VAC

B	20190306	ELECTRIC PERFORMANCE ADDED		
Rev.	Date	Description		Remark
YUBRIGHT CO., LTD.		P/N	SF-6065.0	
Title		MICRO SWITCH		
Date		20151117	Rev.	B
File		SWT009	Drw.	b37
			App.	b37
<small>Unless otherwise specified, dimensions are in millimeters.</small>				