



Range of precision balances with enormous weighing ranges – ideal for heavy tare containers or large samples

**Features**

- **A** KERN PLJ 2000-3A: **High-quality milligram balance with enormous weighing range up to 2100 g** – ideal for large samples or heavy tare containers
- **Ergonomically optimised keypad** for left and righthanded users
- KERN PLJ: **Automatic internal adjustment**, guarantees high degree of accuracy and makes the balance independent of its location of use

- Ideal for mobile applications which require verification, such as ambulatory gold and jewellery purchasing
- KERN PLS: **Adjusting program CAL** for quick setting of the balance accuracy, external test weights at an additional price, see *Test weights*
- **Draught shield** standard for models with weighing plate size **B**, weighing space  $\varnothing \times H$  60×150 mm
- **Protective working cover** included with delivery

**Technical data**


- Backlit LCD display, digit height 17 mm
- Dimensions weighing surface, stainless steel
  - A**  $\varnothing$  80 mm
  - B**  $\varnothing$  110 mm
  - C**  $\varnothing$  160 mm, see larger picture
  - D** W×D 200×175 mm
- **1** KERN PLS/PLJ-F: Strain gauge
- **2** KERN PLS/PLJ-A: Force compensation
- Permissible ambient temperature  
 KERN PLS, PLJ: 5 °C/35 °C  
 KERN PLJ-M: 15 °C/30 °C

**Accessories**

- **Protective working cover**, scope of delivery: 5 items, KERN PLJ-A01S05
- **3** **Hook for underfloor weighing**, KERN PLJ-A02
- **Set for density determination** of liquids and solids with density  $\leq/\geq 1$  for models with [d] = 0,001 g, KERN ALT-A02 [d] = 0,01 g, KERN PLT-A01
- **RS-232/Ethernet adapter** for connection to an IP-based Ethernet network, KERN YKI-01

• Further details, plenty of further accessories and suitable printers see *Accessories*

STANDARD



OPTION



FACTORY



Model	Weighing range [Max] g	Readout [d] g	Verification value [e] g	Minimal load [Min] g	Linearity g	Weighing plate	Quality code	Option				
								Verification		DAkkS Calibr. Certificate		
								M II KERN		DKD KERN		
KERN PLS 420-3F	420	0,001	-	-	± 0,004	B	BA	-	-	-	963-127	
PLS 720-3A 3	720	0,001	-	-	± 0,002	B	BC	↓	-	-	963-127	
PLS 1200-3A 3	1200	0,001	-	-	± 0,003	B	BC	-	-	-	963-127	
PLS 4200-2F 3	4200	0,01	-	-	± 0,04	C	BA	-	-	-	963-127	
PLS 6200-2A 3	6200	0,01	-	-	± 0,03	C	BC	-	-	-	963-128	
PLS 8000-2A 3	8200	0,01	-	-	± 0,04	C	BC	-	-	-	963-128	
PLS 20000-1F 3	20000	0,1	-	-	± 0,4	D	BA	↓	-	-	963-128	
PLJ 420-3F	420	0,001	-	-	± 0,003	B	BA	-	-	-	963-127	
PLJ 720-3A 3	720	0,001	-	-	± 0,002	B	CC	↓	-	-	963-127	
PLJ 1200-3A 3	1200	0,001	-	-	± 0,003	B	CC	↓	-	-	963-127	
PLJ 2000-3A 3	2100	0,001	-	-	± 0,004	A	CC	↓	-	-	963-127	
PLJ 3000-2FM*	3100	0,01	-	-	± 0,03	C	BA	-	-	-	963-127	
PLJ 4200-2F	4200	0,01	-	-	± 0,04	C	BA	-	-	-	963-127	
PLJ 6200-2A 3	6200	0,01	-	-	± 0,03	C	CC	-	-	-	963-128	
Note: For applications that require verification, please order verification at the same time, initial verification at a later date is not possible. Verification at the factory, we need to know the full address of the location of use.												
PLJ 720-3AM	720	0,001	0,01	0,02	± 0,002	B	CC	-	965-216	-	963-127	
PLJ 6200-2AM	6200	0,01	0,1	0,5	± 0,03	C	CC	↓	965-217	-	963-128	

! \* ONLY WHILE STOCKS LAST!

↓ Price reduction

# KERN Pictograms

 <b>Internal adjusting:</b> Quick setting up of the balance's accuracy with internal adjusting weight (motordriven)	 <b>GLP/ISO log:</b> The balance displays serial number, user ID, weight, date and time, regardless of a printer connection	 <b>Suspended weighing:</b> Load support with hook on the underside of the balance
 <b>Adjusting program CAL:</b> For quick setting up of the balance's accuracy. External adjusting weight required	 <b>GLP/ISO log:</b> With weight, date and time. Only with KERN printers	 <b>Battery operation:</b> Ready for battery operation. The battery type is specified for each device
 <b>Memory:</b> Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.	 <b>Piece counting:</b> Reference quantities selectable. Display can be switched from piece to weight	 <b>Rechargeable battery pack:</b> Rechargeable set
 <b>Alibi memory:</b> Secure, electronic archiving of weighing results, complying with the 2014/31/EU standard.	 <b>Recipe level A:</b> The weights of the recipe ingredients can be added together and the total weight of the recipe can be printed out	 <b>Universal mains adapter:</b> with universal input and optional input socket adapters for A) EU, GB B) EU, GB, CH, USA C) EU, GB, CH, USA, AUS
 <b>Data interface RS-232:</b> To connect the balance to a printer, PC or network	 <b>Recipe level B:</b> Internal memory for complete recipes with name and target value of the recipe ingredients. User guidance through display	 <b>Mains adapter:</b> 230V/50Hz in standard version for EU. On request GB, USA or AUS version available
 <b>RS-485 data interface:</b> To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible	 <b>Recipe level C:</b> Internal memory for complete recipes with name and target value of the recipe ingredients. User guidance through display, multiplier function, adjustment of recipe when dosages are exceeded or barcode recognition	 <b>Power supply:</b> Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, USA or AUS on request
 <b>USB data interface:</b> To connect the balance to a printer, PC or other peripherals	 <b>Totalising level A:</b> The weights of similar items can be added together and the total can be printed out	 <b>Weighing principle: Strain gauges</b> Electrical resistor on an elastic deforming body
 <b>Bluetooth* data interface:</b> To transfer data from the balance to a printer, PC or other peripherals	 <b>Percentage determination:</b> Determining the deviation in % from the target value (100 %)	 <b>Weighing principle: Tuning fork</b> A resonating body is electromagnetically excited, causing it to oscillate
 <b>WLAN data interface:</b> To transfer data from the balance to a printer, PC or other peripherals	 <b>Weighing units:</b> Can be switched to e.g. nonmetric units at the touch of a key. See balance model. Please refer to KERN's website for more details	 <b>Weighing principle: Electromagnetic force compensation</b> Coil inside a permanent magnet. For the most accurate weighings
 <b>Control outputs (optocoupler, digital I/O):</b> To connect relays, signal lamps, valves, etc.	 <b>Weighing with tolerance range:</b> (Check-weighing) Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model	 <b>Weighing principle: Single cell technology</b> Advanced version of the force compensation principle with the highest level of precision
 <b>Interface for second balance:</b> For direct connection of a second balance	 <b>Hold function:</b> (Animal weighing program) When the weighing conditions are unstable, a stable weight is calculated as an average value	 <b>Verification possible:</b> The time required for verification is specified in the pictogram +3 DAYS
 <b>Network interface:</b> For connecting the scale to an Ethernet network	 <b>Protection against dust and water splashes IPxx:</b> The type of protection is shown in the pictogram.	 <b>DAkkS calibration possible (DKD):</b> The time required for DAkkS calibration is shown in days in the pictogram +3 DAYS
 <b>Wireless data transfer:</b> between the weighing unit and the evaluation unit using an integrated radio module	 <b>Stainless steel:</b> The balance is protected against corrosion	 <b>Package shipment:</b> The time required for internal shipping preparations is shown in days in the pictogram 1 DAY
 <b>KERN Communication Protocol (KCP):</b> It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems		 <b>Pallet shipment:</b> The time required for internal shipping preparations is shown in days in the pictogram 2 DAYS

## KERN – Precision is our business

To ensure the high precision of your balance KERN offers you the the appropriate test weight in the international OIML error limit classes E1-M3 from 1 mg - 2500 kg. In combination with a DAkkS calibration certificate the best pre-requisite for proper balance calibration.

The KERN DAkkS calibration laboratory today is one of the most modern and best-equipped DAkkS calibration laboratories for balances, test weights and force-measurement in Europe.

Thanks to the high level of automation, we can carry out DAkkS calibration of balances, test weights and force-measuring devices 24 hours a day, 7 days a week.

### Range of services:

- DAkkS calibration of balances with a maximum load of up to 50 t
- DAkkS calibration of weights in the range of 1 mg – 2500 kg
- Volume determination and measuring of magnetic susceptibility (magnetic characteristics) for test weights
- Database supported management of checking equipment and reminder service
- Calibration of force-measuring devices
- DAkkS calibration certificates in the following languages DE, GB, FR, IT, ES, NL, PL
- Conformity evaluation and reverification of balances and test weights

## Your KERN specialist dealer: