

D SUB FE turned contact_AWG 18-22_PL1



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 67 000 3476 |
| Specification | D SUB FE turned contact_AWG 18-22_PL1 |
| HARTING eCatalogue | https://b2b.harting.com/09670003476 |

Identification

| | |
|-----------------|---------------|
| Category | Contacts |
| Series | D-Sub |
| Identification | Standard |
| Type of contact | Crimp contact |

Version

| | |
|-----------------------|-----------------|
| Gender | Female |
| Manufacturing process | Turned contacts |

Technical characteristics

| | |
|-------------------------|-------------------------------|
| Conductor cross-section | 0.33 ... 0.82 mm ² |
| Conductor cross-section | AWG 22 ... AWG 18 |
| Contact resistance | ≤10 mΩ |
| Stripping length | 4 mm |
| Performance level | 1 acc. to CECC 75301-802 |

Material properties

| | |
|---------------------|--|
| Material (contacts) | Copper alloy |
| Surface (contacts) | Noble metal over Ni |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |



Pushing Performance

Material properties

| | |
|--------------------------------------|--------------------------------------|
| China RoHS | 50 |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |
| ECHA SCIP number | 339476a1-86ba-49e9-ab4b-cd336420d72a |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Nickel Lead |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 100 |
| Net weight | 0.227 g |
| Country of origin | Switzerland |
| European customs tariff number | 85366990 |
| eCl@ss | 27440204 Contact for industrial connectors |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09670003476](#)