

EFC4K105NUZ

Power MOSFET for 1-2 Cells Lithium-ion Battery Protection

22 V, 3.55 mΩ, 25 A, Dual N-Channel

This Power MOSFET features a low on-state resistance. This device is suitable for applications such as power switches of portable machines. Best suited for 1-2 cells lithium-ion battery applications.

Features

- 2.5 V Drive
- Common-Drain Type
- ESD Diode-Protected Gate
- This device is Pb-Free, Halogen Free and RoHS Compliance

Applications

- 1-2 Cells Lithium-ion Battery Charging and Discharging Switch

Specifications

ABSOLUTE MAXIMUM RATINGS (T_A = 25°C)

| Parameter | Symbol | Value | Unit |
|---|------------------|-------------|------|
| Source to Source Voltage | V _{SSS} | 22 | V |
| Gate to Source Voltage | V _{GSS} | ±12 | V |
| Source Current (DC) | I _S | 25 | A |
| Source Current (Pulse) PW ≤ 10 μs, duty cycle ≤ 1% | I _{SP} | 100 | A |
| Total Dissipation (Note 1) | P _T | 2.5 | W |
| Junction Temperature | T _J | 150 | °C |
| Storage Temperature | T _{stg} | -55 to +150 | °C |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE RATINGS

| Parameter | Symbol | Value | Unit |
|------------------------------|------------------|-------|------|
| Junction to Ambient (Note 1) | R _{θJA} | 50 | °C/W |

1. Surface mounted on ceramic substrate (5000 mm² × 0.8 mm).




ON Semiconductor®

www.onsemi.com

| V _{SSS} | R _{SS(ON)} MAX | I _S MAX |
|------------------|-------------------------|--------------------|
| 22 V | 3.55 mΩ @ 4.5 V | 25 A |
| | 3.65 mΩ @ 3.8 V | |
| | 5.3 mΩ @ 3.1 V | |
| | 7.2 mΩ @ 2.5 V | |


ELECTRICAL CONNECTION




PIN ASSIGNMENT



WLCSP10
(3.40 x 1.96 x 0.10)
CASE 567PL



MARKING DIAGRAM



NZ = Specific Device Code
A = Assembly Location
Y = Year
W = Work Week
ZZ = Assembly Lot

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

EFC4K105NUZ

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$)

| Symbol | Parameter | Conditions | Min | Typ | Max | Unit |
|---------------|---|---|-----|------|---------|------------------|
| $V_{(BR)SSS}$ | Source to Source Breakdown Voltage | $I_S = 1 \text{ mA}, V_{GS} = 0 \text{ V}$ | 22 | | | V |
| I_{SSS} | Zero-Gate Voltage Source Current | $V_{SS} = 17.6 \text{ V}, V_{GS} = 0 \text{ V}$ | | | 1 | μA |
| I_{GSS} | Gate to Source Leakage Current | $V_{GS} = \pm 8 \text{ V}, V_{SS} = 0 \text{ V}$ | | | ± 1 | μA |
| $V_{GS(th)}$ | Gate Threshold Voltage | $V_{SS} = 10 \text{ V}, I_S = 1 \text{ mA}$ | 0.4 | | 1.3 | V |
| $R_{SS(on)}$ | Static Source to Source On-State Resistance | $I_S = 5 \text{ A}, V_{GS} = 4.5 \text{ V}$ | 1.8 | 2.7 | 3.55 | $\text{m}\Omega$ |
| | | $I_S = 5 \text{ A}, V_{GS} = 3.8 \text{ V}$ | 1.9 | 2.8 | 3.65 | $\text{m}\Omega$ |
| | | $I_S = 5 \text{ A}, V_{GS} = 3.1 \text{ V}$ | 2.0 | 3.3 | 5.3 | $\text{m}\Omega$ |
| | | $I_S = 5 \text{ A}, V_{GS} = 2.5 \text{ V}$ | 2.2 | 4.0 | 7.2 | $\text{m}\Omega$ |
| $t_d(on)$ | Turn-ON Delay Time | $V_{SS} = 10 \text{ V}, V_{GS} = 3.8 \text{ V}, I_S = 5 \text{ A}$ $R_g = 10 \text{ k}\Omega$ Switching Test Circuit | | 13 | | μs |
| t_r | Rise Time | | | 35 | | μs |
| $t_d(off)$ | Turn-OFF Delay Time | | | 185 | | μs |
| t_f | Fall Time | | | 78 | | μs |
| Qg | Total Gate Charge | $V_{SS} = 10 \text{ V}, V_{GS} = 3.8 \text{ V}, I_S = 5 \text{ A}$ | | 43 | | nC |
| $V_{F(S-S)}$ | Forward Source to Source Voltage | $I_S = 3 \text{ A}, V_{GS} = 0 \text{ V}$ | | 0.75 | 1.2 | V |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.




Figure 1. Switching Test Circuit

ORDERING INFORMATION

| Device | Marking | Package | Shipping [†] (Qty / Packing) |
|----------------|---------|--|---------------------------------------|
| EFC4K105NUZTDG | NZ | WLCSOP10, 3.40 x 1.96 x 0.10 (Pb-Free / Halogen Free) | 5,000 / Tape & Reel |

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, [BRD8011/D](#).

EFC4K105NUZ

TYPICAL CHARACTERISTICS




Figure 2. On-Region Characteristics




Figure 3. Transfer Characteristics




Figure 4. On-Resistance vs. Gate-to-Source Voltage




Figure 5. On-Resistance vs. Temperature




Figure 6. Forward Source-to-Source Voltage vs. Current




Figure 7. Switching Time vs. Gate Resistance

EFC4K105NUZ

TYPICAL CHARACTERISTICS




Figure 8. Gate-to-Source Voltage vs. Total Charge




Figure 9. Safe Operating Area




Figure 10. Total Dissipation vs. Temperature




Figure 11. Thermal Response

Note on Usage: Since the EFC4K105NUZ is a MOSFET product, please avoid using this device in the vicinity of highly charged objects.

MECHANICAL CASE OUTLINE

PACKAGE DIMENSIONS


ON Semiconductor®



WLCSP10 3.40x1.96x0.10
CASE 567PL
ISSUE C


SCALE 4:1

DATE 14 MAR 2018




NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.

| DIM | MILLIMETERS | | |
|-----|-------------|------|------|
| | MIN | NOM | MAX |
| A | 0.08 | 0.10 | 0.12 |
| b | 0.22 | 0.25 | 0.28 |
| b1 | 0.50 | 0.53 | 0.56 |
| b2 | 1.78 | 1.81 | 1.84 |
| b3 | 0.32 | 0.35 | 0.38 |
| b4 | 0.32 | 0.35 | 0.38 |
| D | 3.40 BSC | | |
| E | 1.96 BSC | | |
| e | 0.64 BSC | | |
| e1 | 0.60 BSC | | |
| e2 | 0.525 BSC | | |
| e3 | 0.525 BSC | | |




RECOMMENDED SOLDERING FOOTPRINT*



DIMENSIONS: MILLIMETERS

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

GENERIC MARKING DIAGRAM*



A = Assembly Location
Y = Year
W = Work Week
ZZ = Assembly Lot
▪ = Pb-Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

| | | |
|-------------------------|-------------------------------|--|
| DOCUMENT NUMBER: | 98AON14524G | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION: | WLCSP10 3.40x1.96x0.10 | PAGE 1 OF 1 |

ON Semiconductor and ON are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[onsemi:](#)

[EFC4K105NUZTDG](#)