
Item no.: 279-831
Product description: 4-conductor through terminal block



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.08 - 1.5 mm ²
Cross section [AWG]	28 - 16 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	18 A
Weight	6.25 g
Color	gray
Wiring type	Front-entry
No. of connection Points	4
No. of potentials	1
Height	27 mm
Height	1.06 in
Width	4 mm
Width	0.157 in
Depth	73 mm
Depth	2.87 in

Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
279-831	ABS	05-HG476175/3-PDA	800	18	1,5
279-831	BV	07436/Co	800	18	1,5
279-831	CCA	NL6098	800	18	1,5
279-831	CSA	154112-1327715	600	10	28-16
279-831	DNV	E-10423	800	18	1,5
279-831	GL	17295-00HH	800	18	1,5
279-831	KEMA	2105357.01	800	18	1,5
279-831	LR	91/20112(E6)	800	18	1,5
279-831	PRS	TE/1718/880590/08	800	18	1,5
279-831	RMR	11130002	800	18	1,5
279-831	UR	E45172	600	10	28-16

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected