



NOTES:

1. MATERIALS AND FINISHES:  
 BODIES, COUPLING NUT - STAINLESS STEEL, PASSIVATED  
 CONTACT - BERYLLIUM COPPER, GOLD PLATED  
 RETAINING RING - PHOSPHOR BRONZE  
 INSULATOR - PTFE
2. ELECTRICAL:  
 A. IMPEDANCE: 50 OHM  
 B. DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS, MIN.  
 C. PHASE STABILITY: 5.0° MAX  
 D. AMPLITUDE STABILITY: 0.16 dB MAX
3. MECHANICAL:  
 A. DURABILITY: 5000 CYCLES MIN.  
 B. TEMPERATURE RANGE: -55°C TO 200°C
4. PACKAGING:  
 A. QUANTITY: SINGLE PACKED  
 B. MARKING: PACKAGING TO BE MARKED  
 "AMPHENOL RF, 95-902-466-XXX, AND DATE CODE"  
 C. CONTENTS: CABLE ASSEMBLY, VSWR AND INSERTION PLOT OF INCLUDED CABLE, AND ROHS.

THIRD ANGLE PROJ.

REVISIONS				
REV	DESCRIPTION	DATE	ECN	APPR
A	RELEASE TO MFG.	09-Aug-17	04643	BEW
B	ADD MARKING LABEL, UPDATED TABLE AND NOTES	07-May-19	11449	BEW
C	UPDATE LABEL CALLOUT	01-Oct-19	13124	BEW



PART NUMBER	LENGTH "L" IN INCHES [METERS]	INSERTION LOSS (MAX)
95-902-466-001	24.00 [0.601]	1.84 dB
95-902-466-002	36.00 [0.914]	2.61 dB
95-902-466-003	48.00 [1.219]	3.37 dB
95-902-466-004	72.00 [1.829]	4.90 dB
95-902-466-005	39.37 [1.000]	2.84 dB

**DESIGN REQUIREMENTS**

- |   |   |
|---|---|
| <input checked="" type="checkbox"/> FREQUENCY: DC TO 20 GHz | <input checked="" type="checkbox"/> CONTINUITY        |
| <input checked="" type="checkbox"/> VSWR: 1.27 :1 MAX       | <input checked="" type="checkbox"/> HI-POT: 1000 VRMS |
| <input checked="" type="checkbox"/> INS. LOSS: SEE TABLE    | <input type="checkbox"/> OTHER                        |

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:  
 <0.5mm ± 0.05mm    0.5 - 6mm ± 0.1mm    6 - 30mm ± 0.2mm    30 - 120mm ± 0.3mm    ANGLES ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

**CUSTOMER OUTLINE DRAWING**

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

MATERIAL	DRAWN B. WYMAN	DATE 15-Mar-17	TITLE ATC-PS TEST CABLE SMA PLUG TO SMA PLUG	Amphenol RF www.amphenolrf.com
REFERENCE EAR# 7108 REF: ---	ENGINEER B. WYMAN	DATE 15-Mar-17	SCALE: 1.3:1.0 SHEET 2 OF 2	
CONFIGURATION LEVEL: In Work	APPROVED K. CAPOZZI	DATE 09-Aug-17	DWG SIZE B	DRAWING NO. 95-902-466-XXX
FINISH	CAD FILE	REV C		ITEM NO. 95-902-466-XXX
				PART NO. 95-902-466-XXX