




### 5558872-1 Product Details

Share | Print | Email



5558872-1

TE Internal Number: 5558872-1

Active

View 3D PDF

#### PCB Mounted Jacks - Single Port, Multi-port and Stacked

Always EU RoHS/ELV Compliant (Statement of Compliance)

##### Product Highlights:

- Connector
- Preloaded
- Single Port Configuration
- 1 x 1 Jack Configuration
- Jack Type = RJ22

[View all Features](#)

##### Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

#### Documentation & Additional Information

##### Product Drawings:

- [MODULAR JACK ASSEMBLY, TOP ENTRY, 4 POSITION, WITHOU...](#) (PDF, English)

##### Catalog Pages/Data Sheets:

- [1-1773464-9\\_MODULAR JACKS\\_SINGLE\\_PORT\\_PCB\\_MOUNT](#) (PDF, English)

##### Product Specifications:

- [Modular Plugs, Thru-Hole and Surface Mount Jacks, Da...](#) (PDF, English)

##### Application Specifications:

- [Modular Jacks](#) (PDF, English)

##### Instruction Sheets:

- None Available

##### CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version B\)](#)
- [3D Model \(IGES, Version B\)](#)
- [3D Model \(STEP, Version B\)](#)

[List all Documents](#)

##### Additional Information:

- [Product Line Information](#)

##### Additional Product Images:

- [PCB Layout](#)
- [Panel Cutout](#)

##### Related Products:

- [Tooling](#)

#### Product Features (Please use the Product Drawing for all design activity)

##### Product Type Features:

- Product Type = Connector
- Jack Type = RJ22
- PCB Mounting Orientation = Top Entry (Vertical)
- PCB Mount Style = Through Hole
- Termination Method to PC Board = Solder
- Performance Category = Cat 3
- LED = Without
- Grounding Options = Without
- Panel Stops = Without
- Keyed = No
- Profile = Standard
- Color = Black
- Latch Style = Standard

##### Mechanical Attachment:

- Panel Mount Retention = With
- Flanged = No

##### Electrical Characteristics:

- Shielded = No

##### Termination Features:

- Solder Tail Contact Plating = Tin over Nickel

##### Dimensions:

- Height (mm [in]) = 16.50 [0.650]
- PCB Tail Length (mm [in]) = 3.18 [0.125]
- PCB Thickness, Recommended (mm [in]) = 1.57 [0.062]

##### Body Features:

- Inverted Jack Face = No

##### Contact Features:

- Contact Plating, Mating Area, Material = Gold (50)
- Contact Base Material = Phosphor Bronze

##### Housing Features:

- Housing Material = PBT - GF
- UL Flammability Rating = UL 94V-0

##### Configuration Features:

- Preloaded = Yes
- Port Configuration = Single
- Jack Configuration = 1 x 1
- Number of Positions = 4
- Number of Contacts Loaded = 4

##### Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

##### Packaging Features:

- Packaging Method = Tray

##### Product Availability:

- Region = Asia, North America

##### Other:

- Brand = AMP

#### Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

#### Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

#### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

#### Keep Me Informed

