# **Features**

- Efficiency up to 96%, Non isolated, no need for heatsinks
- Pin-out compatible with LM78XX Linears
- Low profile( L\*W\*H=11.5\*8.5\*17.5mm)
- High voltage input range, up to 72V
- Short circuit protection, Thermal shutdown
- Non standard outputs available as specials between 3.3V~24V
- Low ripple and noise
- "L" version with 90° pins
- See Innoline Application Notes for use as an inverter (alternative to LM79xx Linear)

# Description

The R-78HBxx-Series high efficiency, high input voltage switching regulators are ideally suited to replace 78xx linear regulators and are pin compatible. The efficiency of up to 96% means that very little energy is wasted as heat so there is no need for any heat sinks with their additional space and mounting costs.

An input voltage range of up to 8:1is unsurpassed by any other converter and allows the full stored energy utilisation of standard and high voltage batteries. The fully protected output is ideal for industrial applications (especially for industry standard 24VDC bus supplies) and the L-Version with 90° pins allows direct replacement for laid-flat regulators where component height is at a premium. Low ripple and noise figures and a short circuit input current of typically only 15mA round off the specifications of this versatile converter series.

Typical applications include telecommunication, automotive, industrial, aerospace and battery powered applications.

#### **Selection Guide** Part Input Output Output Efficiency Number 30V 72V Range Voltage Current Vmin. SIP3 (V) (V) (A) (%) (%) (%) R-78HB3.3-0.5 3.3 0.5 9 - 72 82 80 76 R-78HB5.0-0.5 9 - 72 5.0 0.5 87 85 81 R-78HB6.5-0.5 6.5 0.5 9 - 72 91 87 84 R-78HB9.0-0.5 14 - 72 9.0 0.5 92 90 86 R-78HB12-0.5 17 - 72 12 0.5 94 93 89 R-78HB15-0.5 20 - 72 15 0.5 95 94 91 R-78HB24-0.3 36 - 72 24 0.3 96 92

#### Specifications (refer to the standard application circuit, Ta: 25°C, minimum load = 10%)

Characteristics	Conditions	Min.	Тур.	Max.
Input Voltage Range	See table	9V	72V	75V max.
Output Voltage Range (for customized parts)	All Series	3.3V		24V
Output Current (see Note 1)	3.3V, 5V, 6.5V, 9V, 12V, 15V	10mA		500mA
	24V	6mA		300mA
Short Circuit Input Current	All Series		15mA	25mA
Internal Input Filter			1µF	Capacitor
Internal Power Dissipation				0.65W
Short Circuit Protection	ort Circuit Protection Continuous, automatic recovery			
Output Voltage Accuracy	At 100% Load		±2%	±3%
Line Voltage Regulation	Vin = min. to max. at full load		0.4%	1%
Load Regulation	10% to 100% full load		0.3%	0.6%
Dynamic Load Stability (with Output Capacitor=100µF)	vnamic Load Stability (with Output Capacitor=100 $\mu$ F) 100% <-> 50% load $\pm 75$ mV $\pm 100$ mV			±100mV
Ripple & Noise (without Output Capacitor)	10% to 100% full load 20mVp-p 60mVp-p			

continued on next page

# **INNOLINE**DC/DC-Converter

with year Warranty



# O.5 AMP SIP3 Single Output






EN-55022 Certified EN-55024 Certified EN-60950-1 Certified

**R-78HB** 

# **Derating-Graph**

(Ambient Temperature)



**Refer to Application Notes** 

<sup>\*</sup> add Suffix "L" for 90° bent pins, e.g. R-78HB5.0-0.5L


# **INNOLINE**

# DC/DC-Converter

# R-78HBxx-0.5 (L) Series

Specifications (refer to the standard application circuit, Ta: 25°C, minimum load = 10%)							
Characteristics	Conditions	Min.	Тур.	Max.			
Temperature Coefficient	-40°C ~ +85°C ambient			0.015%/°C			
Max capacitance Load	vith normal start-up time, no external components 100µF						
with	with $<1$ second start up time $+$ diode protection circuit 6800 $\mu$ F						
Switching Frequency (See Graph)	Full Load	120kHz		800kHz			
Quiescent Current	Vin = 48VDC. at minimum load	1mA		5mA			
Operating Temperature Range		-40°C		+85°C			
Operating Case Temperature				+100°C			
Storage Temperature Range		-55°C		+125°C			
Case Thermal Impedance				60°C/W			
Relative Humidity				95% RH			
Case Material			Non-Cond	ductive Black Plastic			
Potting Material				Epoxy (UL94V-0)			
Package Weight			4g				
Packing Quantity				42 pcs per Tube			
Soldering Temperature			,	265°C max./10 sec.			
Conducted Emissions	EN55022			Class B			
Radiated Emissions	EN55022			Class B			
ESD	EN61000-4-2			Class A			
Safety Certification	Report: SPCLVD 1301026-1		EN-60950-	1:2006 + A12:2011			
MTBF (+25°C) \ Detailed Information see	using MIL-HDBK 217F			7395 x 10 <sup>3</sup> hours			
(+71°C) \rightarrow Application Notes chapter "MTBF"	using MIL-HDBK 217F			1242 x 10 <sup>3</sup> hours			


# **Typical Application Circuit**



The converter has a built in soft start circuit. Rapidly changing the input voltage from  $Vin(min) \leftrightarrow Vin(max)$  can bypass this circuit and damage the converter.

# **Typical Characteristics**

Switching Frequency vs Load




Switching Frequency Vs Load (Vin=30~72V)




# R-78HBxx-0.5 (L) Series


**Typical Characteristics** 








# **Ripple**











\*Note: Operation under no load will not damage these devices, however they may not meet all specifications. A minimum load of 10mA is recommended

# **INNOLINE** DC/DC-Converter

# R-78HBxx-0.5 (L) Series


# **Optional Protection Circuit**

Add a blocking diode to Vout if current can flow backwards into the output, as this can damage the converter when it is powered down.

The diode can either be fitted across the device if the source is low impedance or fitted in series with the output (recommended).

## **Optional Protection 1:**

-Vin





-Vout


**Optional Protection 2:** 

-Vin

-Vout

### **Typical Application**


### **High Input Voltage Multiple Output Supply**





- Wide input range 18V to 72V can be used with 24V, 48V or 60V batteries
- +12V output for interface and display electronics
- +5V high current output for digital electronics
- Further decoupling filtering may be necessary between the converters


### Package Style and Pinning (mm)

## SIP3 PIN Package
















Pin Connections Pin#

1		+Vin
2		GND
3		+Vout
	+0.5mm	

 $xx.xx \pm 0.25mm$ 

The product information and specifications are subject to change without prior notice. All products are designed for non-safety critical commercial and industrial applications, The Buyer agrees to implement safeguards that anticipate the consequences of any failures that might cause harm, loss of life and/or damage property.