



Intel® Xeon® Processor E5-2640

15M Cache, 2.50 GHz, 7.20 GT/s Intel® QPI

Add to Compare

Specifications

Essentials

Performance

Supplemental Information

Memory Specifications

Expansion Options

Package Specifications

Advanced Technologies

Security & Reliability

Ordering and Compliance

Product Images

Compatible Products

Downloads and Software

Essentials

Export specifications

Product Collection	Intel® Xeon® Processor E5 Family
Code Name	Products formerly Sandy Bridge EP
Vertical Segment	Server
Processor Number	E5-2640
Status	Discontinued
Launch Date	Q1'12
Expected Discontinuance	Q2'15
Lithography	32 nm
Recommended Customer Price	-

Performance

# of Cores	6
# of Threads	12
Processor Base Frequency	2.50 GHz
Max Turbo Frequency	3.00 GHz
Cache	15 MB SmartCache
Bus Speed	7.2 GT/s QPI
# of QPI Links	2
TDP	95 W
VID Voltage Range	0.60V-1.35V

Supplemental Information

Embedded Options Available	No
Datasheet	View now

Memory Specifications

Max Memory Size (dependent on memory type)	384 GB
Memory Types	DDR3 800/1066/1333
Max # of Memory Channels	4
Max Memory Bandwidth	42.6 GB/s
ECC Memory Supported ‡	Yes

Expansion Options

Scalability	2S Only
PCI Express Revision ?	3.0
Max # of PCI Express Lanes ?	40

Package Specifications

Sockets Supported ?	FCLGA2011
Max CPU Configuration	2
T _{CASE} ?	73 °C
Package Size	52.5mm x 45.0mm

Advanced Technologies

Intel® Turbo Boost Technology [†] ?	1.0
Intel® vPro™ Platform Eligibility [‡] ?	Yes
Intel® Hyper-Threading Technology [†] ?	Yes
Intel® Virtualization Technology (VT-x) [‡] ?	Yes
Intel® Virtualization Technology for Directed I/O (VT-d) [‡] ?	Yes
Intel® VT-x with Extended Page Tables (EPT) [‡] ?	Yes
Intel® 64 [‡] ?	Yes
Instruction Set ?	64-bit
Instruction Set Extensions ?	Intel® AVX
Idle States ?	Yes
Enhanced Intel SpeedStep® Technology ?	Yes
Intel® Demand Based Switching ?	Yes
Thermal Monitoring Technologies ?	Yes
Intel® Flex Memory Access ?	No
Intel® Identity Protection Technology [‡] ?	No

Security & Reliability

Intel® AES New Instructions ?	Yes
Intel® Trusted Execution Technology [‡] ?	Yes
Execute Disable Bit [‡] ?	Yes

More support options for Intel® Xeon® Processor E5-2640 (15M Cache, 2.50 GHz, 7.20 GT/s Intel® QPI)



Product Support



Downloads and Software



Support Community



Warranty and Replacement



Need more help?

Contact support



Give Feedback

All information provided is subject to change at any time, without notice. Intel may make changes to manufacturing life cycle, specifications, and product descriptions at any time, without notice. The information herein is provided "as-is" and Intel does not make any representations or warranties whatsoever regarding accuracy of the information, nor on the product features, availability, functionality, or compatibility of the products listed. Please contact system vendor for more information on specific products or systems.

Intel classifications are for informational purposes only and consist of Export Control Classification Numbers (ECCN) and Harmonized Tariff Schedule (HTS) numbers. Any use made of Intel classifications are without recourse to Intel and shall not be construed as a representation or warranty regarding the proper ECCN or HTS. Your company as an importer and/or exporter is responsible for determining the correct classification of your transaction.

Refer to Datasheet for formal definitions of product properties and features.

"Announced" SKUs are not yet available. Please refer to the Launch Date for market availability.

Some products can support AES New Instructions with a Processor Configuration update, in particular, i7-2630QM/i7-2635QM, i7-2670QM/i7-2675QM, i5-2430M/i5-2435M, i5-2410M/i5-2415M. Please contact OEM for the BIOS that includes the latest Processor configuration update.

‡ This feature may not be available on all computing systems. Please check with the system vendor to determine if your system delivers this feature, or reference the system specifications (motherboard, processor, chipset, power supply, HDD, graphics controller, memory, BIOS, drivers, virtual machine monitor-VMM, platform software, and/or operating system) for feature compatibility. Functionality, performance, and other benefits of this feature may vary depending on system configuration.

See <http://www.intel.com/content/www/us/en/architecture-and-technology/hyper-threading/hyper-threading-technology.html?wapkw=hyper+threading> for more information including details on which processors support Intel® HT Technology.

Max Turbo Frequency refers to the maximum single-core processor frequency that can be achieved with Intel® Turbo Boost Technology. See www.intel.com/technology/turboboost/ for more information.

The Recommended Customer Price ("RCP") is pricing guidance for Intel products. Prices are for direct Intel customers, typically represent 1,000-unit purchase quantities, and are subject to change without notice. Taxes and shipping, etc. not included. Prices may vary for other package types and shipment quantities, and special promotional arrangements may apply. If sold in bulk, price represents individual unit. Listing of these RCP does not constitute a formal pricing offer from Intel. Please work with your appropriate Intel representative to obtain a formal price quotation.

System and Maximum TDP is based on worst case scenarios. Actual TDP may be lower if not all I/Os for chipsets are used.

For benchmarking data see <http://www.intel.com/performance>.

Intel processor numbers are not a measure of performance. Processor numbers differentiate features within each processor family, not across different processor families. See <http://www.intel.com/content/www/us/en/processors/processor-numbers.html> for details.

Processors that support 64-bit computing on Intel® architecture require an Intel 64 architecture-enabled BIOS.



[Company Information](#) [Our Commitment](#) [Communities](#) [Investor Relations](#) [Contact Us](#)

[Newsroom](#) [Jobs](#)



[© Intel Corporation](#) | [Terms of Use](#) | [*Trademarks](#) | [Privacy](#) | [Cookies](#) | [Supply Chain Transparency](#) | [Site Map](#)