



Terminals & Splices > Automotive Terminals > DEUTSCH STAMPED & FORMED CONTACTS



Terminal & Splice Type: **Pin**

Mating Pin Diameter: **1.02 mm [.04 in]**

Terminal Transmits: **0 – 24 A (Low Power)**

Wire Size: **.35 – 1.5 mm<sup>2</sup>**

[All DEUTSCH STAMPED & FORMED CONTACTS \(51\)](#)

## Features

### Product Type Features

Sealable	No
Primary Locking Feature	On the Terminal
Automotive Terminal Wire Type	Copper

### Body Features

Automotive Terminal Seal Type	Family Seal or Unsealed
-------------------------------	-------------------------

### Contact Features

Typical Current Rating	7.5 A
Crimp Type	F-Crimp
Terminal & Splice Type	Pin
Mating Pin Diameter	1.02 mm [.04 in]
Automotive Terminal Interface Plating	Nickel (Ni)
Contact Termination Area Plating Material	Nickel (Ni)

### Termination Features

Automotive Terminal Termination Method	F-Crimp
--	---------

### Dimensions

Wire Size	.35 – 1.5 mm <sup>2</sup>
Wire Size Search	.35 mm <sup>2</sup> , .5 mm <sup>2</sup> , .6 mm <sup>2</sup> , .75 mm <sup>2</sup> , 1 mm <sup>2</sup> ,

1.5 mm<sup>2</sup>

Wire Insulation Diameter	1.91 – 3.18 mm [.075 – .125 in]
--------------------------	---------------------------------

### Usage Conditions

Operating Temperature (Max)	125 °C [257 °F]
Operating Temperature Range	-55 – 125 °C [-67 – 257 °F]

### Packaging Features

Packaging Method	Reel
Packaging Quantity	4000

### Other

Customer Preferred Contact	Yes
Terminal Transmits	0 – 24 A (Low Power)

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Model / Part # CAT-H3930-CH8172  
DEUTSCH HD30 HOUSINGS




TE Model / Part # CAT-ST858-CH8172  
DEUTSCH STRIKE HOUSINGS



TE Model / Part # CAT-D485-CH8172  
DEUTSCH DTM HOUSINGS



TE Model / Part # CAT-H396-CH8172  
DEUTSCH HDP20 HOUSINGS



TE Model / Part # CAT-D781-CH8172  
DEUTSCH DRB HOUSINGS



TE Model / Part # CAT-D48-ST273  
DEUTSCH SOLID CONTACTS



TE Model / Part # CAT-D48-SFT273  
DEUTSCH STAMPED & FORMED CONTACTS



TE Model / Part # DTT-20-00  
CRIMP TOOL



TE Model / Part # CAT-D799-CH8172  
DEUTSCH DRC HOUSINGS



TE Model / Part # CAT-D487-CH8172  
DEUTSCH DT HOUSINGS



TE Model / Part # 2266116-1  
OCEAN\_2.0\_APPLICATOR-S-069F1100



TE Model / Part # 2266116-2  
OCEAN\_2.0\_APPLICATOR-S-069F1100A



TE Model / Part # 2266118-1  
OCEAN\_2.0\_APPLICATOR-S-069F0800



TE Model / Part # 5-2266118-1  
OCEAN\_2.0\_APPLICATOR-S-069F0800



TE Model / Part # 2-2266116-1  
OCEAN\_2.0\_APPLICATOR-S-069F1100



TE Model / Part # 2-2266116-2  
OCEAN\_2.0\_APPLICATOR-S-069F1100A



TE Model / Part # 2-2266117-1  
OCEAN-2.0-APPLICATOR-S-069F0900



TE Model / Part # 2-2266117-2  
OCEAN-2.0-APPLICATOR-S-069F0900A




TE Model / Part # 2-2266118-1  
OCEAN\_2.0\_APPLICATOR-S-069F0800



TE Model / Part # 2-2266118-2  
OCEAN\_2.0\_APPLICATOR-S-069F0800A

Also in the Series | **DEUTSCH Common Contact**



Automotive Terminals(95)



Insertion &amp; Extraction Tools(12)

## Customers Also Bought

TE Model / Part #DTM06-3S  
DEUTSCH DTM HOUSINGSTE Model / Part #WM-6S  
DEUTSCH DTM WEDGELOCKSTE Model / Part #0413-204-2005  
DEUTSCH SEALING PLUGSTE Model / Part #1062-16-0122  
DEUTSCH STAMPED & FORMED  
CONTACTS

## Documents

### Product Drawings

[PIN, SF, SIZE 20, 16-22, NI/NI](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1060-20-0122\\_J\\_c-1060-20-0122-j.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1060-20-0122\\_J\\_c-1060-20-0122-j.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1060-20-0122\\_J\\_c-1060-20-0122-j.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[CONNECTOR SELECTOR](#)

English

### Product Specifications

[Application Specification](#)

English



**Product Environmental Compliance**

[MD\\_1060-20-0122\\_0716201865\\_dmtec](#)

English

[MD\\_1060-20-0122\\_0716201865\\_dmtec](#)

English