PRIMETEST 100

POWERFUL APPLIANCE AND SOCKET TESTING AT THE PUSH OF A BUTTON



Top of its class, the Primetest 100 is a functional, diverse and highly useful tool. Featuring three operational modes, it is an ideal choice for those looking for an easy to us, comprehensive unit. Simply pushing a button will give you the option of either PAT Test mode, Class I and Class II, IEC Lead Test mode or Power Socket mode. To further add to its easy operation, a bright display shows the test results values as well as PASS or FAIL indication. And like the Primetest 100's family members, it is battery powered to help users be quicker and more efficient in their work. Thanks to our PATGuard Workabout software, asset information can be recorded on-site for storage in a PAT test record database. This is a great choice for those looking for a great, versatile tester.

Key Features

A Versatile Tester

It's a PAT tester, an IEC Lead Tester and a Power Socket Tester all in one super compact unit. This product provides everything you need for basic testing facilities.

Easy Use

Testing with the Primetest 100 couldn't be easier. In fact, it only takes the press of a button to choose your testing mode.

Hand-Sized -Highly Portable

Measuring only 26x10cm, the Primetest 100 fits into the palm of your hand. It's lighter too, under 1kg, making it one of the smallest testers available.

Power to the Battery

Like its big brothers, the Primetest 100 is battery powered, making it light, portable and extremely easy to use because there are no cables to plug in.

Primetest 100 Users

- Maintenance staff
- Schools and Colleges
- Care Homes
- Leisure industry



Web: www.seaward.co.uk Email: sales@seaward.co.uk

Seaward

Bracken Hill, South West Industrial Estate, Peterlee, SR8 2SW **Tel:** +44 (0) 191 5863511

Fax: +44 (0) 191 5860227

PRIMETEST 100 SPECIFICATIONS

PAT TESTS

Earth Continuity

Test Current +/- 200mA DC

Display Range 0.00ohms – 19.99ohms

Pass Value 0.2ohms

Insulation Range

Test Voltages 500V DC

Display Range 0.20Mohms – 19.99Mohms

Pass Value 2Mohms

IEC Lead Test

Tests Performed Earth Continuity

Insulation Resistance

Live, Neutral Continuity and Polarity

Equivalent Leakage Class I

Test Voltage 40V, 50Hz AC Nominal Display Range 0.10mA – 19.99 mA

Pass Value 0.75mA

Equivalent Leakage Class II

Test Voltage 40V, 50Hz AC Nominal Display Range 0.10mA – 19.99mA

Pass Value 0.25mA

Circuit Tests

Power Socket Test

Input Voltage Range 230V +10% - 15% AC
Indicators Phase to Earth Voltage
Phase to Neutral Voltage

Neutral Earth

Additional Information

Weight & Dimensions 800g/26cm (I) x 10cm (w) x 5.5cm (d)

Power Source 6 x AA Batteries

Basic PAT Solutions Package

PATSolutions is a total solutions philosophy that encompasses all aspects of electrical safety testing, from the testers themselves to information management software, through to label printers and much more.

Each tester and its accessories can be purchased separately or as an optional PATSolutions package which includes everything needed to run an efficient and effective PAT testing business.

Advanced PATSolution Package includes:

- Primetest 100 Tester
- Connectors
- Carry case
- PATGuard Software
- Calibration Certificate
- PATGuard Support Contractor
- Guide to PAT testing

Optional Extras

Hardware:

Battery charger (339A950) PATCheckbox (227A910)

Software:

PATGUARD (352A930)



Training: PRIMETEST 100

TRAINING COURSE

PATGUARD SOFTWARE

TRAINING COURSE

Services: SERVICE & CALIBRATION

Seaward test and measurement companies include:

JUMP START

PART NO: (344A910)



CLARE
INDUSTRIAL SAFETY INSTRUMENTS
CROPICO
PRECISION INSTRUMENTS

MEDICAL

SEAWARD
PORTABLE ELECTRICAL SAFETY INSTRUMENTS