

DSUB FE STR CRIMP CONTACT 75 OHMS COAX




Image is for illustration purposes only. Please refer to product description.

Part number	09 69 182 5230
Specification	DSUB FE STR CRIMP CONTACT 75 OHMS COAX
HARTING eCatalogue	https://b2b.harting.com/09691825230

Identification

Category	Contacts
Series	D-Sub
Identification	Mixed
Type of contact	Coaxial contact
Description of the contact	Straight for cables RG 179 BU, 187 AU
Features	Tool setting: 5 for AWG 24 and AWG 26, 4 for AWG 28, 3 for AWG 30 Outer ferrule: crimp in tool cavity B

Version

Termination method	Crimp/crimp termination
Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Operating current	≤ 2 A
Rated voltage	250 V
Insulation resistance	$> 10^9$ Ω
Contact resistance	≤ 10 m Ω
Impedance	75 Ω
Limiting temperature	-55 ... +135 °C
Insertion force	≤ 7 N
Withdrawal force	≤ 7 N



Pushing Performance

Technical characteristics

Performance level	NM 30 (S4) 1
Mating cycles	≥500
Test voltage $U_{r.m.s.}$	0.75 kV @ 50 Hz
Frequency	0 ... 2 GHz

Material properties

Material (contacts)	Copper alloy PBFE / PBTP / PI
Surface (contacts)	Noble metal over Ni
Layer thickness	≥0.76 μm
Layer thickness	≥30 μinch
Material (locking)	Copper alloy
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	20
Net weight	1 g
Country of origin	Czechia
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09691825230](#)