
DATA	SHEET		
PART NO. :	L-3142UW5W		
REV:	<u>A/4</u>		
CUSTOMER'S APPROVAL: DRAWING NO. : DS-33-04-0208	DCC: DATE: 2013-5-15	Page:	1
	22.2010 0 10	HD-R/RI	



L-3142UW5W

FEATURES

- * High-brightness
- * High reliability
- * Low-voltage characteristics
- * Narrow view angle
- * Pb FREE Products
- * RoHS Compliant

CHIP MATERIALS

- * Dice Material : GalnN/GaN
- * Light Color : ULTRA WHITE
- * Lens Color : WHITE DIFFUSED

ABSOLUTE MAXIMUM RATING:(Ta=25°C)

SYMBOL	DESCRIPTION	ULTRA WHITE	UNIT	
PD	Power Dissipation Per Chip	120	mW	
VR	Reverse Voltage Per Chip	5	V	
lF	Average Forward Current Per Chip	30 mA		
-	Derating Linear From 25°C Per Chip	0.4 mA/°C		
Topr	Operating Temperature Range	-40°C to 85°C		
Tstg	Storage Temperature Range	-40°C to 85°C		
Esd	the led can withstand the max static level when assembling or operation (HBM)	<3000V		

IFP Conditions : Pulse Width≤10msec. And Duty≤1/10

ELECTRO-OPTICAL CHARACTERISTICS:(Ta=25°C)


SYMBOL	DESCRIPTION	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
VF	VF Forward Voltage IF = 20mA		3.5	4.0	V	
IR	Reverse Current	VR = 5V			100	μA
201/2	Half Intensity Angle	IF = 20mA		60		deg
I٧	Luminous Intensity	IF = 20mA		800		mcd
Х	Chromoticity Coordinator	IF = 20mA		0.29		
Y	Chromaticity Coordinates	IF = 20mA		0.30		

DRAWING NO. : DS-33-04-0208


DATE: 2013-5-15

Page: 3

REV:A/4



Page: 4




DRAWING NO. : DS-33-04-0208

DATE: 2013-5-15

Page: 5

Release

by



L-3142UW5W

REV:A/4

Label Explanation

PART NO.	* *		
LOT NO.	۵ ۵		INSPECTED
BIN	• •		
Q' TY	• •	PCS	
N. W	* *	g	

PARA NO. : L-3142UW5W

Refer to page 15

LOT NO.: E L L 4 7 0009

ABCDE

F

A---E: For Serial number

B---L: Local F: Foreign

C---L: LAMP

D---Year

E---Month

F---Serial number

DRAWING NO. : DS-33-04-0208

DATE: 2013-5-15

Page: 7

Release	by
PARALIG	HTDCC


L-3142UW5W

REV:A/4


-SOLDERING

0

-SOLDERING	3	
METHOD	SOLDERING CONDITIONS	REMARK
DIP SOLDERING	Bath temperature: 260° C Immersion time: with 5 sec, 1 time	 Solder no closer than 3mm from the base of the package Using soldering flux," RESIN FLUX" is recommended.
SOLDERING IRON	Soldering iron: 30W or smaller Temperature at tip of iron: 300℃ or lower Soldering time: within 5 sec.	 During soldering, take care not to press the tip of iron against the lead. (To prevent heat from being transferred directly to the lead, hold the lead with a pair of tweezers while soldering
1) When solderi	ng the lead of LED in a condition that the	package is fixed with a panel (See
Fig.1), be car	eful not to stress the leads with iron tip.	
٥		



2) When soldering wire to the lead, work with a Fig (See Fig.2) to avoid stressing the package.



Regarding solution in the tinning oven for product-tinning, compound sub-solution made of tin & copper and sliver is proposed with the temperature of Celsius 260. The proportion of the alloyed solution is tin 95.5: copper 3.5: silver 0.5 by percentage. The time of tinning is constantly 3 seconds.


Release by PARALIGHTDCC

3.0 mm DIA LED LAMP

L-3142UW5W

REV:A/4

3) Similarly, when a jig is used to solder the LED to PC board, take care as much as possible to avoid steering the leads (See Fig.3).



- 4) Repositioning after soldering should be avoided as much as possible. If inevitable, be sure to preserve the soldering conditions with irons stated above: select a best-suited method that assures the least stress to the LED.
- Lead cutting after soldering should be performed only after the LED temperature has returned to normal temperature.

– STORAGE

0

- 1) The LEDs should be stored at 30° C or less and 70% RH or less after being shipped from PARA and the storage life limits are 3 months .
- 2) PARA LED lead frames are comprised of a stannum plated iron alloy. The silver surface may be affected by environments which contain corrosive gases and so on. Please avoid conditions which may cause the LEDs to corrode, tarnish or discolor. This corrosion or discoloration may cause difficulty during soldering operations. It is recommended that the LEDs be used as soon as possible.
- Please avoid rapid transitions in ambient temperature, especially, in high humidity environments where condensation can occur.

REV:A/4

3.0 mm DIA LED LAMP


L-3142UW5W


-STATIC ELECTRICITY


- Static electricity or surge voltage damages the LEDs.
 It is recommended that a wrist band or an anti-electrostatic glove be used when handling the LEDs.
- 2) All devices, equipment and machinery must be properly grounded. It is recommended that measures be taken against surge voltage to the equipment that mounts the LEDs.
- 3) When inspecting the final products in which LEDs were assembled, it is recommended to check whether the assembled LEDs are damaged by static electricity or not. It is easy to find static-damaged LEDs by a light-on test or a VF test at a lower current (below 1mA is recommended).
- Damaged LEDs will show some unusual characteristics such as the leak current remarkably increases, the forward voltage becomes lower, or the LEDs do not light at the low current. Criteria : (VF>2.0V at IF=0.5mA)

-LED MOUNTING METHOD

4) When mounting the LED by using a case, as shown Fig.4, ensure that the mounting holds on the PC board match the pitch of the leads correctly-tolerance of dimensions of the respective components including the LED should be taken into account especially when designing the case, PC board, etc. to prevent pitch misalignment between the leads and board holes, the diameter of the board holes should be slightly larger than the size of the lead. Alternatively, the shape of the holes should be made oval. (See Fig.4)








2)

Release

bv PARALIGHTDCC



REV:A/4

3.0 mm DIA LED LAMP

L-3142UW5W

-CHEMICAL RESISTANCE

- 1) Avoid exposure to chemicals as it may attack the LED surface and cause discoloration.
- 2) When washing is required, refer to the following table for the proper chemical to be sued.
- (Immersion time: within 3 minutes at room temperature.)

SOLVENT	ADAPTABILITY
Freon TE	\odot
Chlorothene	\times
Isopropyl Alcohol	\odot
Thinner	\times
Acetone	\times
Trichloroethylene	×

 \times --Do not use.

NOTE: Influences of ultrasonic cleaning of the LED resin body differ depending on such factors as the oscillator output, size of the PC board and the way in which the LED is mounted. Therefore, ultrasonic cleaning should only be performed after confirming there is no problem by conducting a test under practical.

-OTHERS

⊙--Usable

- 1) Care must be taken to ensure that the reverse voltage will not exceed the absolute maximum rating when using the LEDs with matrix drive.
- Flashing lights have been known to cause discomfort in people; you can prevent this by taking precautions during use. Also, people should be cautious when using equipment that has had LEDs incorporated into it.
- 3) The LEDs described in this brochure are intended to be used for ordinary electronic equipment (such as office equipment, communications equipment, measurement instruments and household appliances). Consult PARA's sales staff in advance for information on the applications in which exceptional quality and reliability are required, particularly when the failure or malfunction of the LEDs may directly jeopardize life or health (such as for airplanes, aerospace, submersible repeaters, nuclear reactor control systems, automobiles, traffic control equipment, life support systems and safety devices).
- 4) User shall not reverse engineer by disassembling or analysis of the LEDs without having prior written consent from PARA. When defective LEDs are found, the User shall inform PARA directly before disassembling or analysis.
- 5) The formal specifications must be exchanged and signed by both parties before large volume purchase begins.
- 6) The appearance and specifications of the product may be modified for improvement without notice.

L-3142UW5W

REV:A/4

Bin Code List:

Luminous Intensity(IV), Unit:mcd@20mA				
Bin Code	Max			
E	390	550		
F	550	770		
G	770	1080		
Н	1080	1510		
l	1510	2110		

Tolerance of each bin are±15%

Forward Voltage (VF), Unit:v@20mA						
Bin Code Min Max						
V0	2.8	3.0				
V1	3.0	3.2				
V2	3.2	3.4				
V3	3.4	3.6				
V4	3.6	3.8				
V5	3.8	4.0				

Tolerance of each bin are±0.1Volt

	WA3					W	A4		
Х	0.24	0.24	0.25	0.25	Х	0.25	0.25	0.26	0.26
Y	0.175	0.235	0.25	0.19	Y	0.19	0.25	0.265	0.205
		W	A5			a0			
Х	0.26	0.26	0.264	0.280	Х	0.280	0.264	0.283	0.296
Y	0.205	0.265	0.267	0.248	Y	0.248	0.267	0.305	0.276
		b11				b21			
Х	0.287	0.283	0.31	0.31	Х	0.296	0.287	0.31	0.31
Y	0.295	0.305	0.335	0.318	Y	0.276	0.295	0.318	0.293

DRAWING NO. : DS-33-04-0208

DATE: 2013-5-15

Page :14

