



DATE	REV	EON	APP'D. BY
3-29-16	A8	10646	TRM
11-14-17	A9	11149	TRM




B
 .69
 [17.53]
 MAX

1.51 [38.35]
 MAX

1.06 [26.93]
 MAX

.680 [17.27]
 MIN


.725
 [18.42]
 MAX



2

1

- NOTES:
- CONNECTOR MATERIALS:
 HOUSING: THERMOPLASTIC U194 V-0
 CONTACTS/SHIELD: COPPER ALLOY
 SHIELD PLATING: NICKEL
 FERRULE PLATING: NICKEL OR TIN
 CONTACT PLATING: SELECTIVE GOLD IN CONTACT AREA
 SEE CHART FOR PART NUMBER
 - FOR PRODUCT SPECIFICATIONS SEE PRO26-01.
 - DIMENSIONS AND TOLERANCES COMPLY WITH TIA-1096 STANDARD.




WIRING
 IDENTIFICATION
 LABEL

WIRE
 STRAIN RELIEF

LOAD BAR


INSERTION DIRECTION

PANEL




.619 [15.72] MAX.

(4) R.010 [0.25]
 MAX.



RECOMMENDED PANEL OPENING
 .074 [1.88] MAXIMUM PANEL THICKNESS



FERRULE
 P/N F-270-205

A


B

2

1

AutocAD

50 MICRO-INCHES [1.27um]	SS-82100-001
CONTACT PLATING IN MATING AREA	PART NUMBER



11118 Susquehanna Trail South
 Glen Rock, PA 17327-9199
 (717) 235-7512
<http://www.stewartconnector.com>

SHIELDED CABLE READY CAT5e JACK
 (SHOWN IN TERMINATED CONDITION)

THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING	THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF STEWART CONNECTOR AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF STEWART CONNECTOR. ONE OR MORE U.S. PATENTS MAY APPLY TO THIS PRODUCT. FOR DETAILS, PLEASE VISIT: HTTP://BELFUSE.COM/STEWART/PATENTS/
	DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS: INCHES [METRIC] UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1°	
SHEET NO. 1 OF 1	DRN BY: TRM	DATE: 7-18-05
	APP'D BY: DHG	DATE: 7-18-05
	DWG NO. CT820006	REV. A9

