

(2.54 mm) .100"

OPP SERIES


ONE-PIECE POWER INTERFACE

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?OPP

Insulator Material:
Black Liquid Crystal Polymer
Contact Material:
BeCu
Plating:
Sn over 50 μ" (1.27 μm) Ni
Operating Temp Range:
-55 °C to +105 °C
Current Rating:
9.6 A per pin
(1 pin powered)
Voltage Rating:
280 VAC
RoHS Compliant:
Yes

Processing:
Lead-Free Solderable:
Yes
SMT Lead Coplanarity:
(0.15 mm) .006" max




RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality








FILE NO. E111594



ALSO AVAILABLE (MOQ Required)

- Alternative alignment pin available
Contact Samtec.



-AD OPTION

Note: Some sizes, styles and options are non-standard, non-returnable.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[OPP-07-01-T-S-M-AB](#) [OPP-03-01-T-S-E](#) [OPP-03-01-T-S-E-AT](#) [OPP-03-01-T-S-M-AT](#) [OPP-07-01-T-S-M-AD](#) [OPP-10-01-T-S-E-AT](#) [OPP-03-01-T-S-AB](#) [OPP-03-01-T-S-AT](#) [OPP-03-01-T-S-M-AB](#) [OPP-07-01-TM-S-E-AD](#) [OPP-03-01-T-S](#) [OPP-03-01-T-S-M-AD](#) [OPP-07-01-T-S](#) [OPP-07-01-T-S-AT](#) [OPP-03-01-T-S-AD](#) [OPP-07-01-T-S-E-AB](#) [OPP-07-01-T-S-E-AT](#) [OPP-10-01-T-S-E-AD](#) [OPP-10-01-T-S-M-AB](#) [OPP-10-01-T-S-E-AB](#) [OPP-07-01-T-S-E-AD](#) [OPP-10-01-T-S-M-AD](#) [OPP-07-01-T-S-AB](#) [OPP-10-01-TM-S-M](#) [OPP-10-01-T-S-M](#) [OPP-10-01-T-S-AB](#) [OPP-10-01-T-S-AT](#) [OPP-03-01-T-S-E-AB](#) [OPP-07-01-T-S-AD](#) [OPP-07-01-T-S-E](#) [OPP-07-01-T-S-M](#) [OPP-07-01-T-S-M-AT](#) [OPP-07-01-TM-S-AB](#) [OPP-03-01-T-S-E-AD](#) [OPP-03-01-T-S-M](#) [OPP-10-01-T-S](#) [OPP-10-01-T-S-AD](#) [OPP-10-01-T-S-E](#) [OPP-10-01-T-S-M-AT](#) [OPP-07-01-TM-S-M-AD](#) [OPP-07-01-TM-S-M](#) [OPP-07-01-TM-S-E-AT](#) [OPP-10-01-TM-S-AT](#)