




AC and Pulse Metallized Polypropylene Film Capacitors MKP Radial Potted Type



FEATURES

- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



APPLICATIONS

- Pulse operations
- SMPS and thyristor circuits
- Storage, filter, timing, sample and hold circuits




| QUICK REFERENCE DATA | |
|--|--|
| Capacitance range | 4700 pF to 10 μF |
| Capacitance tolerances | ± 20 % (M), ± 10 % (K), ± 5 % (J) |
| Climatic testing class according to IEC 60068 | 55/100/56 |
| Operating temperature range | -55 °C to +100 °C |
| Dielectric | Polypropylene film |
| Electrodes | Metallized |
| Construction | Extended metallized film (refer to general information following the link in note below table) |
| Coating | Flame retardant plastic case, epoxy resin sealed UL-class 94 V-0 |
| Leads | Tinned wire |
| Rated voltages (U _R) | 100 V _{DC} , 160 V _{DC} , 250 V _{DC} , 400 V _{DC} , 630 V _{DC} |
| Insulation resistance | Measured at 100 V _{DC} after one minute For C ≤ 0.33 μF: 25 000 MΩ (U _R 100 V _{DC}) |
| Permissible AC voltages (RMS) up to 60 Hz | 63 V _{AC} , 100 V _{AC} , 160 V _{AC} , 220 V _{AC} , 250 V _{AC} |
| Test voltage (electrode/electrode) | 1.6 x U _R for 2 s |
| Time constant | Measured at 100 V _{DC} after one minute For C > 0.33 μF: 30 000 s minimum value |
| Temperature coefficient | -250 x 10 ⁻⁶ /°C (typical value) |
| Capacitance drift | Up to +40 °C, < 0.5 % for a period of two years |
| Dielectric absorption | 0.05 % (typical value) according to IEC 60068-2-21 |
| Derating for DC and AC category voltage U _C | At +85 °C: U _C = 1.0 U _R At +100 °C: U _C = 0.7 U _R |
| Self inductance | ~ 6 nH measured with 2 mm long leads |
| Pull test on leads | ≥ 30 N in direction of leads according to IEC 60068-2-21 |

Note

- For further details, please refer to the general information available at www.vishay.com/doc?26033



DIMENSIONS in millimeters



| LEAD DIAMETER d_t | W | PITCH |
|------------------------|-----------|--------------|
| 0.5 ± 0.05 | - | 5 to 7.5 |
| 0.6 ± 0.06 | - | 10 |
| 0.6 ± 0.06 | ≤ 6 | 15 |
| 0.8 ± 0.08 | > 6 | 15 |
| 0.8 ± 0.08 | < 16 | 22.5 to 37.5 |
| 1.0 ± 0.1 | ≥ 16 | 22.5 to 37.5 |

MAXIMUM PULSE RISE TIME

| PCM (mm) | MAXIMUM PULSE RISE TIME dV/dt [V/ μ s] | | | | |
|-------------|--|---------------------|---------------------|---------------------|---------------------|
| | 100 V _{DC} | 160 V _{DC} | 250 V _{DC} | 400 V _{DC} | 630 V _{DC} |
| 5 | 390 | - | - | - | - |
| 7.5 | - | 240 | 300 | - | - |
| 10 | - | 175 | 220 | 380 | 510 |
| 15 | - | 100 | 125 | 200 | 280 |
| 22.5 | - | 60 | 75 | 120 | 160 |
| 27.5 | - | 45 | 60 | 95 | 120 |
| 37.5 | - | 30 | 40 | 65 | 85 |

Note

- If the maximum pulse voltage is less than the rated voltage higher dV/dt values can be permitted.

DISSIPATION FACTOR $\tan \delta$

| MEASURED AT | $C \leq 0.1 \mu F$ | $0.1 \mu F < C \leq 1.0 \mu F$ | $C > 1.0 \mu F$ |
|----------------|--------------------------|--------------------------------|--------------------------|
| 1 kHz | $\leq 10 \times 10^{-4}$ | $\leq 10 \times 10^{-4}$ | $\leq 40 \times 10^{-4}$ |
| 10 kHz | $\leq 10 \times 10^{-4}$ | $\leq 10 \times 10^{-4}$ | - |
| 100 kHz | $\leq 10 \times 10^{-4}$ | - | - |
| Maximum values | | | |



| ELECTRICAL DATA | | | | | | |
|--------------------------------------|----------------------------|-----------------------------------|-------------------------------|-----------------------|--|---------------------------|
| U_{RDC} (V) | CAP. (μF) | CAPACITANCE CODE | VOLTAGE CODE | V_{AC} | DIMENSIONS w x h x l (mm) | PCM (mm) |
| 100 | 0.0047 | -247 | 01 | 63 | 3.5 x 8.0 x 7.2 | 5.0 |
| | 0.0068 | -268 | | | 3.5 x 8.0 x 7.2 | 5.0 |
| | 0.010 | -310 | | | 3.5 x 8.0 x 7.2 | 5.0 |
| | 0.015 | -315 | | | 3.5 x 8.0 x 7.2 | 5.0 |
| | 0.022 | -322 | | | 3.5 x 8.0 x 7.2 | 5.0 |
| | 0.033 | -333 | | | 3.5 x 8.0 x 7.2 | 5.0 |
| | 0.047 | -347 | | | 4.5 x 9.0 x 7.2 | 5.0 |
| | 0.068 | -368 | | | 4.5 x 9.0 x 7.2 | 5.0 |
| | 0.100 | -410 | | | 6.0 x 11.0 x 7.2 | 5.0 |
| 160 | 0.033 | -333 | 16 | 100 | 3.0 x 8.0 x 10.0 | 7.5 |
| | 0.047 | -347 | | | 3.0 x 8.0 x 10.0 | 7.5 |
| | 0.068 | -368 | | | 4.0 x 10.0 x 12.5 | 10.0 |
| | 0.10 | -410 | | | 4.0 x 10.0 x 12.5 | 10.0 |
| | 0.15 | -415 | | | 5.0 x 11.0 x 12.5 | 10.0 |
| | 0.22 | -422 | | | 5.0 x 11.0 x 17.5 | 15.0 |
| | 0.33 | -433 | | | 6.0 x 12.0 x 17.5 | 15.0 |
| | 0.47 | -447 | | | 7.0 x 13.5 x 17.5 | 15.0 |
| | 0.68 | -468 | | | 8.5 x 15.0 x 17.5 | 15.0 |
| | 1.0 | -510 | | | 7.0 x 16.5 x 26.0 | 22.5 |
| | 1.5 | -515 | | | 8.5 x 18.0 x 26.0 | 22.5 |
| | 2.2 | -522 | | | 9.0 x 19.0 x 31.5 | 27.5 |
| | 3.3 | -533 | | | 11.0 x 21.0 x 31.0 | 27.5 |
| | 4.7 | -547 | | | 12.5 x 22.5 x 41.5 | 37.5 |
| | 6.8 | -568 | | | 14.5 x 24.5 x 41.5 | 37.5 |
| 10.0 | -610 | 16.0 x 28.5 x 41.5 | 37.5 | | | |
| 250 | 0.010 | -310 | 25 | 160 | 3.0 x 8.0 x 10.0 | 7.5 |
| | 0.015 | -315 | | | 3.0 x 8.0 x 10.0 | 7.5 |
| | 0.022 | -322 | | | 3.0 x 8.0 x 10.0 | 7.5 |
| | 0.033 | -333 | | | 4.0 x 10.0 x 12.5 | 10.0 |
| | 0.047 | -347 | | | 4.0 x 10.0 x 12.5 | 10.0 |
| | 0.068 | -368 | | | 4.0 x 10.0 x 12.5 | 10.0 |
| | 0.10 | -410 | | | 4.0 x 10.0 x 12.5 | 10.0 |
| | 0.15 | -415 | | | 5.0 x 11.0 x 17.5 | 15.0 |
| | 0.22 | -422 | | | 5.0 x 11.0 x 17.5 | 15.0 |
| | 0.33 | -433 | | | 6.0 x 12.0 x 17.5 | 15.0 |
| | 0.47 | -447 | | | 7.0 x 13.5 x 17.5 | 15.0 |
| | 0.68 | -468 | | | 6.0 x 15.5 x 26.0 | 22.5 |
| | 1.0 | -510 | | | 7.0 x 16.5 x 26.0 | 22.5 |
| | 1.5 | -515 | | | 9.0 x 19.0 x 31.5 | 27.5 |
| | 2.2 | -522 | | | 11.0 x 21.0 x 31.0 | 27.5 |
| | 3.3 | -533 | | | 13.0 x 23.0 x 31.0 | 27.5 |
| | 4.7 | -547 | | | 12.5 x 22.5 x 41.5 | 37.5 |
| | 6.8 | -568 | | | 14.5 x 24.5 x 41.5 | 37.5 |
| 10.0 | -610 | 16.0 x 28.5 x 41.5 | 37.5 | | | |



| ELECTRICAL DATA | | | | | | |
|-------------------------|--------------|---------------------|--------------------|--------------------|---------------------------------|--------------------|
| U _{RDC} (V) | CAP. (µF) | CAPACITANCE CODE | VOLTAGE CODE | V _{AC} | DIMENSIONS w x h x l (mm) | PCM (mm) |
| 400 | 0.010 | -310 | 40 | 220 | 4.0 x 10.0 x 12.5 | 10.0 |
| | 0.015 | -315 | | | 4.0 x 10.0 x 12.5 | 10.0 |
| | 0.022 | -322 | | | 4.0 x 10.0 x 12.5 | 10.0 |
| | 0.033 | -333 | | | 4.0 x 10.0 x 12.5 | 10.0 |
| | 0.047 | -347 | | | 5.0 x 11.0 x 17.5 | 15.0 |
| | 0.068 | -368 | | | 5.0 x 11.0 x 17.5 | 15.0 |
| | 0.10 | -410 | | | 5.0 x 11.0 x 17.5 | 15.0 |
| | 0.15 | -415 | | | 6.0 x 12.0 x 17.5 | 15.0 |
| | 0.22 | -422 | | | 7.0 x 13.5 x 17.5 | 15.0 |
| | 0.33 | -433 | | | 6.0 x 15.5 x 26.0 | 22.5 |
| | 0.47 | -447 | | | 7.0 x 16.5 x 26.0 | 22.5 |
| | 0.68 | -468 | | | 9.0 x 19.0 x 31.5 | 27.5 |
| | 1.0 | -510 | | | 11.0 x 21.0 x 31.0 | 27.5 |
| | 1.5 | -515 | | | 13.0 x 23.0 x 31.0 | 27.5 |
| | 2.2 | -522 | | | 12.5 x 22.5 x 41.5 | 37.5 |
| | | 3.3 | | | -533 | 14.5 x 24.5 x 41.5 |
| | 4.7 | -547 | 18.0 x 32.5 x 41.5 | 37.5 | | |
| 630 | 0.010 | -310 | 63 | 250 ⁽¹⁾ | 4.0 x 10.0 x 12.5 | 10.0 |
| | 0.015 | -315 | | | 4.0 x 10.0 x 12.5 | 10.0 |
| | 0.022 | -322 | | | 4.0 x 10.0 x 12.5 | 10.0 |
| | 0.033 | -333 | | | 5.0 x 11.0 x 17.5 | 15.0 |
| | 0.047 | -347 | | | 5.0 x 11.0 x 17.5 | 15.0 |
| | 0.068 | -368 | | | 5.0 x 11.0 x 17.5 | 15.0 |
| | 0.10 | -410 | | | 6.0 x 12.0 x 17.5 | 15.0 |
| | 0.15 | -415 | | | 6.0 x 15.5 x 26.0 | 22.5 |
| | 0.22 | -422 | | | 7.0 x 16.5 x 26.0 | 22.5 |
| | 0.33 | -433 | | | 8.5 x 18.0 x 26.0 | 22.5 |
| | 0.47 | -447 | | | 9.0 x 19.0 x 31.5 | 27.5 |
| | 0.68 | -468 | | | 11.0 x 21.0 x 31.0 | 27.5 |
| | 1.0 | -510 | | | 13.0 x 23.0 x 31.0 | 27.5 |
| | 1.5 | -515 | | | 14.5 x 24.5 x 41.5 | 37.5 |
| | 2.2 | -522 | | | 16.0 x 28.5 x 43.0 | 37.5 |

Notes

- Further C-values upon request.
- ⁽¹⁾ Not suitable for mains applications.
Please refer to X-capacitors in our catalog "RFI Suppression Components".






| RECOMMENDED PACKAGING | | | | | | | | |
|-----------------------|----------------------|--------------------|--------------------------|---------------------------|------------------|-----------|---------------------|-------------|
| LETTER CODE | TYPE OF PACKAGING | HEIGHT (H) (mm) | REEL DIAMETER (mm) | ORDERING CODE EXAMPLES | PCM 7.5 TO 10 | PCM 15 | PCM 22.5 TO 27.5 | PCM 37.5 |
| D | Ammo | 16.5 | S ⁽¹⁾ | MKP1840310405D | x | x | - | - |
| G | Ammo | 18.5 | S ⁽¹⁾ | MKP1840310405G | x | x | - | - |
| F | Reel | 16.5 | 350 | MKP1840310405F | x | x | - | - |
| W | Reel | 18.5 | 350 | MKP1840310405W | x | x | - | - |
| V | Reel | 18.5 | 500 | MKP1840522255V | - | x | x | - |
| G | Ammo | 18.5 | L ⁽²⁾ | MKP1840522255G | - | - | x | - |
| - | Bulk | - | - | MKP1840547255 | x | x | x | x |

Notes


- ⁽¹⁾ S = box size 55 mm x 210 mm x 340 mm (w x h x l)
- ⁽²⁾ L = box size 60 mm x 360 mm x 510 mm (w x h x l)



PERMISSIBLE AC VOLTAGE VS. FREQUENCY



IMPEDANCE VS. FREQUENCY





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[MKP1840333634](#) [MKP1840410164](#) [MKP1840433164](#) [MKP1840422254](#) [MKP1840410254](#) [MKP1840510254](#)
[MKP1840433404](#) [MKP1840410634](#) [MKP1840347634](#)