

# **3-Pin Switch-Mode LED Lamp Driver ICs**

## Features

- Constant output current:
  - HV9921 20mA
  - HV9922 50mA
  - HV9923 30mA
- · Universal 85 264VAC operation
- · Fixed off-time buck converter
- Internal 475V power MOSFET

## Applications

- · Decorative lighting
- · Low power lighting fixtures

## Description

HV9921/HV9922/HV9923 are pulse-width modulated (PWM), high-efficiency, LED driver control ICs. They allow efficient operation of LED strings from voltage sources ranging up to 400VDC. HV9921/22/23 include an internal high voltage switching MOSFET controlled with fixed off-time ( $T_{OFF}$ ) of approximately 10µs. The LED string is driven at constant current, thus providing constant light output and enhanced reliability. The output current is internally fixed at 20mA for HV9921, 50mA for HV992, and 30mA for HV9923. The peak current control scheme provides good regulation of the output current throughout the universal AC line voltage range of 85 to 264VAC or DC input voltage of 20 to 400V.

# TO OUR VALUED CUSTOMERS

It is our intention to provide our valued customers with the best documentation possible to ensure successful use of your Microchip products. To this end, we will continue to improve our publications to better suit your needs. Our publications will be refined and enhanced as new volumes and updates are introduced.

If you have any questions or comments regarding this publication, please contact the Marketing Communications Department via E-mail at **docerrors@microchip.com**. We welcome your feedback.

### Most Current Data Sheet

To obtain the most up-to-date version of this data sheet, please register at our Worldwide Web site at:

#### http://www.microchip.com

You can determine the version of a data sheet by examining its literature number found on the bottom outside corner of any page. The last character of the literature number is the version number, (e.g., DS30000000A is version A of document DS30000000).

### Errata

An errata sheet, describing minor operational differences from the data sheet and recommended workarounds, may exist for current devices. As device/documentation issues become known to us, we will publish an errata sheet. The errata will specify the revision of silicon and revision of document to which it applies.

To determine if an errata sheet exists for a particular device, please check with one of the following:


- Microchip's Worldwide Web site; http://www.microchip.com
- Your local Microchip sales office (see last page)

When contacting a sales office, please specify which device, revision of silicon and data sheet (include literature number) you are using.


### **Customer Notification System**

Register on our web site at www.microchip.com to receive the most current information on all of our products.

## **PIN DIAGRAM**



# **TYPICAL APPLICATION CIRCUIT**



<sup>© 2014</sup> Microchip Technology Inc.

# 1.0 ELECTRICAL CHARACTERISTICS

# **ABSOLUTE MAXIMUM RATINGS**

Supply Voltage V <sub>DD</sub>	0.3V to +10V
Supply Current IDD	+5mA
Operating Ambient temperature	40°C to +85°C
Operating Junction Temperature	40°C to +125°C
Storage temperature	65°C to +150°C
Power dissipation @+25°C for TO-9	92740 mW
Power dissipation @+25°C for SOT	-89 1600 mW*

\* Mounted on FR4 board, 24mmx25mmx1.57mm

**Note**: Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions, above those indicated in the operational listings of this specification, is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability.

# 1.1 ELECTRICAL SPECIFICATIONS

### TABLE 1-1: ELECTRICAL CHARACTERISTICS<sup>1</sup>

Symbol	Parameter	Notes	Min	Тур	Мах	Units	Conditions
Regulator (	V <sub>DD</sub> )	· · · · ·					
V <sub>DD</sub>	V <sub>DD</sub> Regulator Output	-	-	7.5	-	V	
V <sub>DRAIN</sub>	V <sub>DRAIN</sub> Supply Voltage	-	20	-	-	V	
V <sub>UVLO</sub>	V <sub>DD</sub> Under-voltage Threshold	-	5.0	-	-	V	
$\Delta V_{UVLO}$	V <sub>DD</sub> Under-voltage Lockout Hysteresis	-	-	200	-	mV	
I <sub>DD</sub>	Operating Supply Current	-	-	200	350	μA	V <sub>DD(EXT)</sub> = 8.5V, V <sub>DRAIN</sub> = 40V
Output (DR	AIN)	·					
V <sub>BR</sub>	Breakdown Voltage	2	475	-	-	V	
R <sub>ON</sub>	ON Resistance	-	-	-	210	Ω	I <sub>DRAIN</sub> = 20mA (HV9921) I <sub>DRAIN</sub> = 50mA (HV9922) I <sub>DRAIN</sub> = 30mA (HV9923)
C <sub>DRAIN</sub>	Output Capacitance	3	-	1	5	pF	V <sub>DRAIN</sub> = 400V
I <sub>SAT</sub>	MOSFET Saturation Current	3	100	150	-	mA	
Current Ser	nse Comparator						
	Threshold Current - HV9921	2	18.5	-	25.5	mA	
I <sub>THL</sub>	Threshold Current - HV9922	2	49	-	63	mA	
	Threshold Current - HV9923	2	28.2	-	38.2	mA	
T <sub>BLANK</sub>	Leading Edge Blanking Delay	2,3	200	300	400	ns	
T <sub>ON(MIN)</sub>	Minimum ON Time	-	-	-	650	ns	
OFF-Time G	Senerator	·I					•
T <sub>OFF</sub>	OFF Time	-	8	10.5	13	μS	
1 Sr	Decifications are $T_A = 25^{\circ}C$ . VDRAIN = 50	)V unles	s other	wise no	ted		


1 Specifications are  $T_A = 25^{\circ}C$ ,  $V_{DRAIN} = 50V$  unless otherwise noted.

2 Applies over the full operating ambient temperature range of -40°C <  $T_A$  < +125°C.

3 For design guidance only

### THERMAL RESISTANCE

Package	θја
TO-92	132°C/W
TO-243AA(SOT-89)	133°C/W



<sup>© 2014</sup> Microchip Technology Inc.

# 2.0 PIN DESCRIPTION

See Pin Diagram on page 3 for the figures.

TABLE 2-1:	PIN DESCRIPTION

Pin #	Name	Description
1	Drain	Drain terminal of the output switching MOSFET and a linear regulator input
2	GND	Common connection for all circuits
3	VDD	Power Supply pin for all control circuits. By pass this pin with a 0.1 $\mu\text{F}$ low-impedance capacitor

# 3.0 FUNCTIONAL DESCRIPTION

The HV9921/22/23 are PWM peak current controllers designed to control a buck converter topology in continuous conduction mode (CCM). The output current is internally preset at 20mA for HV9921, 50mA for HV992, and 30mA for HV9923.

When the input voltage of 20 to 400V appears at the DRAIN pin, the internal high-voltage linear regulator seeks to maintain a voltage of 7.5VDC at the  $V_{DD}$  pin. Until this voltage exceeds the internally programmed under-voltage threshold, the output switching MOSFET is non-conductive. When the threshold is exceeded, the MOSFET turns on. The input current begins to flow into the DRAIN pin. Hysteresis is provided in the under-voltage comparator to prevent oscillation.

When the input current exceeds the internal preset level, a current sense comparator resets an RS flip-flop, and the MOSFET turns off. At the same time, a one-shot circuit is activated that determines the duration of the off-state ( $10.5\mu$ s typical). As soon as this time is over, the flip-flop sets again. The new switching cycle begins.

A "blanking" delay of 300ns is provided that prevents false triggering of the current sense comparator due to the leading edge spike caused by circuit parasitics.

# 4.0 APPLICATION INFORMATION

HV9921/22/23 are low-cost off-line buck converter ICs specifically designed for driving multi-LED strings. They can be operated from either universal AC line range of 85 to 264VAC, or 20 to 400VDC, and drive up to tens of high-brightness LEDs. All LEDs can be run in series, and the HV9921/22/23 regulate at constant current, yielding uniform illumination. HV9921/22/23 are compatible with triac dimmers. The output current is internally fixed at 20mA for HV9921, 50mA for HV9922, and 30mA for HV9923. These parts are available in space saving TO-92 and SOT-89 packages.

## 4.1 Selecting L1 and D1

There is a certain trade-off to be considered between optimal sizing of the output inductor L1 and the tolerated output current ripple. The required value of L1 is inversely proportional to the ripple current  $\Delta I_O$  in it.

$$L1 = \frac{V_O \bullet T_{OFF}}{\Delta I_O}$$

 $V_O$  is the forward voltage of the LED string.  $T_{OFF}$  is the off-time of HV9921/22/23. The output current in the LED string (I\_O) is calculated then as:

$$I_{O} = I_{TH} - (\frac{1}{2} \bullet \Delta I_{O})$$

where  $I_{TH}$  is the current sense comparator threshold. The ripple current introduces a peak-to-average error in the output current setting that needs to be accounted for. Due to the constant off-time control technique used in HV9921/22/23, the ripple current is independent of the input AC or DC line voltage variation. Therefore, the output current will remain unaffected by the varying input voltage.

Adding a filter capacitor across the LED string can reduce the output current ripple even further, thus permitting a reduced value of L1. However, keep in mind that the peak-to-average current error is affected by the variation of  $T_{OFF}$ . Therefore, the initial output current accuracy might be sacrificed at large ripple current in L1.

Another important aspect of designing an LED driver with the HV9921/22/23 is related to certain parasitic elements of the circuit, including distributed coil capacitance of L1, junction capacitance and reverse recovery of the rectifier diode D1, capacitance of the printed circuit board traces  $C_{PCB}$  and output capacitance  $C_{DRAIN}$ of the controller itself. These parasitic elements affect the efficiency of the switching converter and could potentially cause false triggering of the current sense comparator if not properly managed. Minimizing these parasitics is essential for efficient and reliable operation of the HV9921/22/23. Coil capacitance of inductors is typically provided in the manufacturer's data books either directly or in terms of the self-resonant frequency (SRF).

$$SRF = 1/(2\pi \sqrt{(L \bullet C_L)})$$

where L is the inductance value, and C<sub>L</sub> is the coil capacitance.) Charging and discharging this capacitance every switching cycle causes high-current spikes in the LED string. Therefore, connecting a small capacitor C<sub>O</sub> (~10nF) is recommended to bypass these spikes.

Using an ultra-fast rectifier diode for D1 is recommended to achieve high efficiency and reduce the risk of false triggering of the current sense comparator. Using diodes with shorter reverse recovery time,  $t_{rr}$ , and lower junction capacitance,  $C_J$ , achieves better performance. The reverse voltage rating,  $V_R$ , of the diode must be greater than the maximum input voltage of the LED lamp.

The total parasitic capacitance present at the DRAIN pin of the HV9921/22/23 can be calculated as:

$$C_{\mathsf{P}} = C_{\mathsf{DRAIN}} + C_{\mathsf{PCB}} + C_{\mathsf{L}} + C_{\mathsf{J}}$$

When the switching MOSFET turns on, the capacitance  $C_P$  is discharged into the DRAIN pin of the IC. The discharge current is limited to about 150mA typically. However, it may become lower at increased junction temperature. The duration of the leading edge current spike can be estimated as:

$$\mathsf{T}_{\mathsf{SPIKE}} = \frac{\mathsf{V}_{\mathsf{IN}} \bullet \mathsf{C}_{\mathsf{P}}}{\mathsf{I}_{\mathsf{SAT}}} + \mathsf{t}_{\mathsf{rr}}$$

In order to avoid false triggering of the current sense comparator,  $C_P$  must be minimized in accordance with the following expression:

$$C_{P} < \frac{I_{SAT} \bullet (T_{BLANK(MIN)} - t_{rr})}{V_{IN(MAX)}}$$

where  $T_{BLANK(MIN)}$  is the minimum blanking time of 200ns, and  $V_{IN(MAX)}$  is the maximum instantaneous input voltage.

### 4.2 Estimating Power Loss

Discharging the parasitic capacitance CP into the DRAIN pin of the HV9921/22/23 is responsible for the bulk of the switching power loss. It can be estimated using the following equation:

$$\mathsf{P}_{\mathsf{SWITCH}} = \left(\frac{\mathsf{V_{IN}}^2 \mathsf{C}_{\mathsf{P}}}{2} + \mathsf{V}_{\mathsf{IN}} \bullet \mathsf{I}_{\mathsf{SAT}} \bullet \mathsf{t_{rr}}\right) \bullet \mathsf{F}_{\mathsf{S}}$$

where  $F_S$  is the switching frequency,  $I_{SAT}$  is the saturated DRAIN current of the HV9921/22/23. The switching loss is the greatest at the maximum input voltage.

The switching frequency is given by the following equation.

$$\mathsf{F}_{\mathsf{S}} = \frac{\mathsf{V}_{\mathsf{IN}} - \mathsf{V}_{\mathsf{O}}}{\mathsf{V}_{\mathsf{IN}} \bullet \mathsf{T}_{\mathsf{OFF}}}$$

When the HV9921/22/23 LED driver is powered from the full-wave rectified AC input, the switching power loss can be estimated as:

$$\mathsf{P}_{\mathsf{SWITCH}} \approx \frac{1}{2 \bullet \mathsf{T}_{\mathsf{OFF}}} (\mathsf{V}_{\mathsf{AC}} \bullet \mathsf{C}_{\mathsf{P}} + 2 \bullet \mathsf{I}_{\mathsf{SAT}} \bullet \mathsf{t}_{\mathsf{rr}}) (\mathsf{V}_{\mathsf{AC}} - \mathsf{V}_{\mathsf{O}})$$

V<sub>AC</sub> is the input AC line voltage.

The switching power loss associated with turn-off transitions of the DRAIN pin can be disregarded. Due to the large amount of parasitic capacitance connected to this switching node, the turn-off transition occurs essentially at zero-voltage.

Conduction power loss in the HV9921/22/23 can be calculated as:


$$\mathsf{P}_{\mathsf{COND}} = \mathsf{D} \bullet \mathsf{I}_{\mathsf{O}}^{2} \bullet \mathsf{R}_{\mathsf{ON}} + \mathsf{I}_{\mathsf{DD}} \bullet \mathsf{V}_{\mathsf{IN}} \bullet (1 - \mathsf{D})$$

where  $D = V_O/V_{IN}$  is the duty ratio,  $R_{ON}$  is the on-resistance,  $I_{DD}$  is the internal linear regulator current.

When the LED driver is powered from the full-wave rectified AC line input, the exact equation for calculating the conduction loss is more cumbersome. However, it can be estimated using the following equation:

$$\mathsf{P}_{\mathsf{COND}} = \mathsf{K}_{\mathsf{C}} \bullet \mathsf{I}_{\mathsf{O}}^{2} \bullet \mathsf{R}_{\mathsf{ON}} + \mathsf{K}_{\mathsf{d}} \bullet \mathsf{I}_{\mathsf{DD}} \bullet \mathsf{V}_{\mathsf{AC}}$$

where  $V_{AC}$  is the input AC line voltage. The coefficients  $K_C$  and  $K_d$  can be determined from the minimum duty ratio of the HV9921/22/23.



## 4.3 EMI Filter

As with all off-line converters, selecting an input filter is critical to obtaining good EMI. A switching side capacitor, albeit of small value, is necessary in order to ensure low impedance to the high frequency switching currents of the converter. As a rule of thumb, this capacitor should be approximately 0.1-0.2  $\mu$ F/W of LED output power. A recommended input filter is shown in Figure 4-2 for the following design example.

### 4.3.1 DESIGN EXAMPLE

The following example designs a HV9921 LED lamp driver meeting the following specifications:

- Input: Universal AC, 85-265VAC
- Output Current: 20mA
- Load: String of 10 LED (LW541C by OSRAM VF = 4.1V max. each)

4.3.1.1 Step 1. Calculating L1.

The output voltage V<sub>O</sub> = 10 x V<sub>F</sub>  $\approx$  41V (max.). Use this equation assuming a 30% peak-to-peak ripple.

$$L1 = \frac{41V \bullet 10.5\mu s}{0.3 \bullet 20mA} = 72mH$$

Select L1 68mH, I = 30mA. Typical SRF = 170KHz. Calculate the coil capacitance.

$$C_{L} = \frac{1}{L1 \cdot (2\pi \cdot SRF)^{2}} = \frac{1}{68mH \cdot (2\pi \cdot 170KHz)^{2}} = 13pF$$

Usually, the reverse recovery characteristics of ultrafast rectifiers at  $I_F = 20 \sim 50$ mA are not provided in the manufacturer's data books. The designer may want to experiment with different diodes to achieve the best result.

Select D1 MUR160 with V<sub>R</sub> = 600V, t<sub>rr</sub>  $\approx$  20ns (I<sub>F</sub> = 20mA, I<sub>RR</sub> = 100mA) and C<sub>J</sub>  $\approx$  8pF (VF > 50V).

4.3.1.3 Step 3. Calculating total parasitic capacitance

$$C_p = 5pF + 5pF + 13pF + 8pF = 13pF$$

4.3.1.4 Step 4. Calculating the leading edge spike duration

 $T_{SPIKE} = \frac{264V \bullet \sqrt{2} \bullet 31pF}{100mA} + 20ns \approx 136ns < T_{BLANK(MIN)}$ 

4.3.1.5 Step 5. Estimating power dissipation in HV9921 at 265VAC

#### Switching power loss:

$$P_{SWITCH} \approx \frac{1}{2 \bullet 10.5 \mu s} (264V \bullet 31pF + 2 \bullet 100mA \bullet 20ns) \bullet (264V - 41V) \approx 131mW$$

#### Minimum duty ratio:

$$D_{M} = \frac{41V}{265V \bullet \sqrt{2}} \approx 0.11$$

#### Conduction power loss:

 $P_{COND} = 0.25 \bullet (20mA)^2 \bullet 210\Omega + 0.63 \bullet 200\mu A \bullet 264V \\\approx 55mW$ 

### Total power dissipation in HV9921:


$$P_{TOTAL} = 131 mW + 55 mW = 186 mW$$

### 4.3.1.6 Step 6. Selecting input capacitor C<sub>IN</sub>


OutputPower=41V•20mA=820mW

Select  $C_{IN}$  ECQ-E4104KF by Panasonic  $^{\textcircled{R}}$  (0.1µF, 400V, Metalized Polyester Film).

### FIGURE 4-2: UNIVERSAL 85-264VAC LED LAMP DRIVER





# FIGURE 4-3: TYPICAL EFFICIENCY




# FIGURE 4-4:

### SWITCH-OFF TRANSITION Ch1:V<sub>DRAIN</sub>, Ch3: I<sub>DRAIN</sub>





#### FIGURE 4-7: FUNCTIONAL BLOCK DIAGRAM



Trig'd

# 5.0 LAYOUT CONSIDERATIONS

For a recommended circuit board layout for the HV9921/22/23, see Figure 5-1.

### 5.1 Single Point Grounding

Use a single point ground connection from the input filter capacitor to the area of copper connected to the GND pin.

# 5.2 Bypass Capacitor (C<sub>DD</sub>)

The  $V_{DD}$  pin bypass capacitor  $C_{DD}$  should be located as near as possible to the  $V_{DD}$  and GND pins.

## 5.3 Switching Loop Areas

The area of the switching loop connecting the input filter capacitor  $C_{\rm IN},$  the diode D1 and the HV9921/22/23 together should be kept as small as possible.


The switching loop area connecting the output filter capacitor  $C_O$ , the inductor L1 and the diode D1 together should be kept as small as possible.

### 5.4 Thermal Considerations vs. Radiated EMI

The copper area where GND pin is connected acts not only as a single point ground, but also as a heat sink. This area should be maximized for good heat sinking, especially when the SOT-89 package is used. The same applies to the cathode of the free-wheeling diode D1. Both nodes are quiet; therefore, they will not cause radiated RF emission. The switching node copper area connected to the DRAIN pin of the HV9921/22/23, the anode of D1 and the inductor L1 needs to be minimized. A large switching node area can increase high frequency radiated EMI.

## 5.5 Input Filter Layout Considerations


The input circuits of the EMI filter must not be placed in the direct proximity to the inductor L1 in order to avoid magnetic coupling of its leakage fields. This consideration is especially important when unshielded construction of L1 is used. When an axial input EMI filter inductor L<sub>IN</sub> is selected, it must be positioned orthogonal with respect to L1. The loop area formed by C<sub>IN2</sub>, L<sub>IN</sub> and C<sub>IN</sub> should be minimized. The input lead wires must be twisted together.




<sup>© 2014</sup> Microchip Technology Inc.

# 6.0 PACKAGING INFORMATION

# 6.1 Package Marking Information



# 3-Lead TO-243AA (SOT-89) Package Outline (N8)




Note: For the most current package drawings, see the Microchip Packaging Specification at www.microchip.com/packaging.

Symbo	ol	Α	b	b1	С	D	D1	E	E1	е	e1	н	L
1	MIN	1.40	0.44	0.36	0.35	4.40	1.62	2.29	2.00†	1.50 BSC		3.94	0.73†
Dimensions (mm)	NOM	-	-	-	-	-	-	-	-		3.00 BSC	-	-
()	MAX	1.60	0.56	0.48	0.44	4.60	1.83	2.60	2.29	200	200	4.25	1.20

JEDEC Registration TO-243, Variation AA, Issue C, July 1986. **†** This dimension differs from the JEDEC drawing **Drawings not to scale**.

# 3-Lead TO-92 Package Outline (L/LL/N3)



**Bottom View** 

Note: For the most current package drawings, see the Microchip Packaging Specification at www.microchip.com/packaging.

Symbol		А	b	с	D	E	E1	е	e1	L
	MIN	.170	.014 <sup>†</sup>	.014 <sup>†</sup>	.175	.125	.080	.095	.045	.500
Dimensions (inches)	NOM	-	-	-	-	-	-	-	-	-
(inches)	MAX	.210	.022†	.022†	.205	.165	.105	.105	.055	.610*

JEDEC Registration TO-92. \* This dimension is not specified in the JEDEC drawing.

*†* This dimension differs from the JEDEC drawing. **Drawings not to scale.** 

# APPENDIX A: REVISION HISTORY

## Revision A (October 2014)

• Original Release of this Document.

<sup>© 2014</sup> Microchip Technology Inc.

# THE MICROCHIP WEB SITE

Microchip provides online support via our WWW site at www.microchip.com. This web site is used as a means to make files and information easily available to customers. Accessible by using your favorite Internet browser, the web site contains the following information:

- Product Support Data sheets and errata, application notes and sample programs, design resources, user's guides and hardware support documents, latest software releases and archived software
- General Technical Support Frequently Asked Questions (FAQ), technical support requests, online discussion groups, Microchip consultant program member listing
- Business of Microchip Product selector and ordering guides, latest Microchip press releases, listing of seminars and events, listings of Microchip sales offices, distributors and factory representatives

# CUSTOMER CHANGE NOTIFICATION SERVICE

Microchip's customer notification service helps keep customers current on Microchip products. Subscribers will receive e-mail notification whenever there are changes, updates, revisions or errata related to a specified product family or development tool of interest.

To register, access the Microchip web site at www.microchip.com. Under "Support", click on "Customer Change Notification" and follow the registration instructions.

# **CUSTOMER SUPPORT**

Users of Microchip products can receive assistance through several channels:

- Distributor or Representative
- · Local Sales Office
- Field Application Engineer (FAE)
- Technical Support

Customers should contact their distributor, representative or Field Application Engineer (FAE) for support. Local sales offices are also available to help customers. A listing of sales offices and locations is included in the back of this document.

Technical support is available through the web site at: http://microchip.com/support

# **PRODUCT IDENTIFICATION SYSTEM**

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

	XX - X - X       Package Environmental Reel Options	Ex a)	<b>amples:</b> HV9921N3-G:	20 mA output current, TO-92 package, 1000/ bag
Device:	<ul> <li>HV9921 = 3-Pin Switch-Mode LED Lamp Driver IC, 20 mA output current</li> <li>HV9922 = 3-Pin Switch-Mode LED Lamp Driver IC, 50 mA output current</li> <li>HV9923 = 3-Pin Switch-Mode LED Lamp Driver IC, 30 mA output current</li> </ul>	b)	HV9923N8-G:	30 mA output current, TO-243AA(SOT-89) package, 2000/reel
Package:	N3 = TO-92 N8 = TO-243AA (SOT-89)			
Environmental	G = Lead (Pb)-free/ROHS-compliant package			
Reel:	(nothing) = 1000/bag for N3 package, 2000/reel for N8 package			

<sup>© 2014</sup> Microchip Technology Inc.

#### Note the following details of the code protection feature on Microchip devices:

- · Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights.

# QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV = ISO/TS 16949=

#### Trademarks

The Microchip name and logo, the Microchip logo, dsPIC, FlashFlex, KEELOQ, KEELOQ logo, MPLAB, PIC, PICmicro, PICSTART, PIC<sup>32</sup> logo, rfPIC, SST, SST Logo, SuperFlash and UNI/O are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

FilterLab, Hampshire, HI-TECH C, Linear Active Thermistor, MTP, SEEVAL and The Embedded Control Solutions Company are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Silicon Storage Technology is a registered trademark of Microchip Technology Inc. in other countries.

Analog-for-the-Digital Age, Application Maestro, BodyCom, chipKIT, chipKIT logo, CodeGuard, dsPICDEM, dsPICDEM.net, dsPICworks, dsSPEAK, ECAN, ECONOMONITOR, FanSense, HI-TIDE, In-Circuit Serial Programming, ICSP, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, mTouch, Omniscient Code Generation, PICC, PICC-18, PICDEM, PICDEM.net, PICkit, PICtail, REAL ICE, rfLAB, Select Mode, SQI, Serial Quad I/O, Total Endurance, TSHARC, UniWinDriver, WiperLock, ZENA and Z-Scale are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

GestIC and ULPP are registered trademarks of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2014, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

Printed on recycled paper.

ISBN: 978-1-63276-708-0

Microchip received ISO/TS-16949:2009 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC<sup>®</sup> MCUs and dsPIC<sup>®</sup> DSCs, KEELOQ<sup>®</sup> code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and mulfacture of development systems is ISO 9001:2000 certified.



# **Worldwide Sales and Service**

### AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

**Cleveland** Independence, OH Tel: 216-447-0464 Fax: 216-447-0643

Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

**Detroit** Novi, MI Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608

New York, NY Tel: 631-435-6000

San Jose, CA Tel: 408-735-9110

Canada - Toronto Tel: 905-673-0699 Fax: 905-673-6509

### ASIA/PACIFIC

Asia Pacific Office Suites 3707-14, 37th Floor Tower 6, The Gateway Harbour City, Kowloon Hong Kong Tel: 852-2943-5100 Fax: 852-2401-3431

Australia - Sydney Tel: 61-2-9868-6733 Fax: 61-2-9868-6755

**China - Beijing** Tel: 86-10-8569-7000 Fax: 86-10-8528-2104

**China - Chengdu** Tel: 86-28-8665-5511 Fax: 86-28-8665-7889

**China - Chongqing** Tel: 86-23-8980-9588 Fax: 86-23-8980-9500

**China - Hangzhou** Tel: 86-571-8792-8115 Fax: 86-571-8792-8116

China - Hong Kong SAR Tel: 852-2943-5100

Fax: 852-2401-3431

China - Nanjing Tel: 86-25-8473-2460 Fax: 86-25-8473-2470 China - Qingdao

Tel: 86-532-8502-7355 Fax: 86-532-8502-7205 **China - Shanghai** 

Tel: 86-21-5407-5533 Fax: 86-21-5407-5066

China - Shenyang Tel: 86-24-2334-2829 Fax: 86-24-2334-2393

**China - Shenzhen** Tel: 86-755-8864-2200 Fax: 86-755-8203-1760

**China - Wuhan** Tel: 86-27-5980-5300 Fax: 86-27-5980-5118

**China - Xian** Tel: 86-29-8833-7252 Fax: 86-29-8833-7256

**China - Xiamen** Tel: 86-592-2388138 Fax: 86-592-2388130

**China - Zhuhai** Tel: 86-756-3210040 Fax: 86-756-3210049

### ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444 Fax: 91-80-3090-4123

**India - New Delhi** Tel: 91-11-4160-8631 Fax: 91-11-4160-8632

India - Pune Tel: 91-20-3019-1500

Japan - Osaka Tel: 81-6-6152-7160 Fax: 81-6-6152-9310

**Japan - Tokyo** Tel: 81-3-6880- 3770 Fax: 81-3-6880-3771

Korea - Daegu Tel: 82-53-744-4301 Fax: 82-53-744-4302

Korea - Seoul Tel: 82-2-554-7200 Fax: 82-2-558-5932 or 82-2-558-5934

Malaysia - Kuala Lumpur Tel: 60-3-6201-9857 Fax: 60-3-6201-9859

**Malaysia - Penang** Tel: 60-4-227-8870 Fax: 60-4-227-4068

Philippines - Manila Tel: 63-2-634-9065 Fax: 63-2-634-9069

**Singapore** Tel: 65-6334-8870 Fax: 65-6334-8850

Taiwan - Hsin Chu Tel: 886-3-5778-366 Fax: 886-3-5770-955

Taiwan - Kaohsiung Tel: 886-7-213-7830

**Taiwan - Taipei** Tel: 886-2-2508-8600 Fax: 886-2-2508-0102

Thailand - Bangkok Tel: 66-2-694-1351 Fax: 66-2-694-1350

### EUROPE

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393 Denmark - Copenhagen Tel: 45-4450-2828 Fax: 45-4485-2829

France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

Germany - Dusseldorf Tel: 49-2129-3766400

**Germany - Munich** Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Germany - Pforzheim Tel: 49-7231-424750

**Italy - Milan** Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Venice Tel: 39-049-7625286

Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340

Poland - Warsaw Tel: 48-22-3325737

**Spain - Madrid** Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

Sweden - Stockholm Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820

03/25/14

### **zhou** 792-8115