

# MMBFJ309L, MMBFJ310L, SMMBFJ309L, SMMBFJ310L



**ON Semiconductor®**

[www.onsemi.com](http://www.onsemi.com)

## JFET - VHF/UHF Amplifier Transistor

### N-Channel

#### Features

- Drain and Source are Interchangeable
- S Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

#### MAXIMUM RATINGS

| Rating               | Symbol   | Value | Unit |
|----------------------|----------|-------|------|
| Drain-Source Voltage | $V_{DS}$ | 25    | Vdc  |
| Gate-Source Voltage  | $V_{GS}$ | 25    | Vdc  |
| Gate Current         | $I_G$    | 10    | mAdc |

#### THERMAL CHARACTERISTICS

| Characteristic   | Symbol          | Max         | Unit                       |
|--|-----------------|-------------|----------------------------|
| Total Device Dissipation FR-5 Board,<br>(Note 1) $T_A = 25^\circ\text{C}$<br>Derate above $25^\circ\text{C}$ | $P_D$           | 225<br>1.8  | mW<br>mW/ $^\circ\text{C}$ |
| Thermal Resistance, Junction-to-Ambient  | $R_{\theta JA}$ | 556         | $^\circ\text{C}/\text{W}$  |
| Junction and Storage Temperature   | $T_J, T_{stg}$  | -55 to +150 | $^\circ\text{C}$           |


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. FR-5 = 1.0 x 0.75 x 0.062 in.



**SOT-23 (TO-236)  
CASE 318  
STYLE 10**

#### MARKING DIAGRAM



6x = Device Code

x = U for MMBFJ309L, SMMBFJ309L

x = T for MMBFJ310L, SMMBFJ310L

M = Date Code\*

▪ = Pb-Free Package

(Note: Microdot may be in either location)

\*Date Code orientation and/or overbar may vary depending upon manufacturing location.

#### ORDERING INFORMATION

| Device                         | Package             | Shipping†               |
|--------------------------------|---------------------|-------------------------|
| MMBFJ309LT1G,<br>SMMBFJ309LT1G | SOT-23<br>(Pb-Free) | 3,000 / Tape &<br>Reel  |
| MMBFJ310LT1G,<br>SMMBFJ310LT1G | SOT-23<br>(Pb-Free) | 3,000 / Tape &<br>Reel  |
| SMMBFJ310LT3G                  | SOT-23<br>(Pb-Free) | 10,000 / Tape &<br>Reel |

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

## MMBFJ309L, MMBFJ310L, SMMBFJ309L, SMMBFJ310L

### ELECTRICAL CHARACTERISTICS ( $T_A = 25^\circ\text{C}$ unless otherwise noted)

| Characteristic   | Symbol        | Min          | Typ | Max          | Unit                            |
|--|---------------|--------------|-----|--------------|---------------------------------|
| <b>OFF CHARACTERISTICS</b>   |               |              |     |              |                                 |
| Gate–Source Breakdown Voltage<br>( $I_G = -1.0 \mu\text{Adc}$ , $V_{DS} = 0$ )   | $V_{(BR)GSS}$ | -25          | -   | -            | Vdc                             |
| Gate Reverse Current ( $V_{GS} = -15 \text{ Vdc}$ )<br>( $V_{GS} = -15 \text{ Vdc}$ , $T_A = 125^\circ\text{C}$ )              | $I_{GSS}$     | -            | -   | -1.0<br>-1.0 | nAdc<br>$\mu\text{Adc}$         |
| Gate Source Cutoff Voltage<br>( $V_{DS} = 10 \text{ Vdc}$ , $I_D = 1.0 \text{ nAdc}$ )   | $V_{GS(off)}$ | -1.0<br>-2.0 | -   | -4.0<br>-6.5 | Vdc                             |
|  |               |              |     |              | MMBFJ309<br>MMBFJ310, SMMBFJ310 |
| <b>ON CHARACTERISTICS</b>  |               |              |     |              |                                 |
| Zero–Gate–Voltage Drain Current<br>( $V_{DS} = 10 \text{ Vdc}$ , $V_{GS} = 0$ )  | $I_{DSS}$     | 12<br>24     | -   | 30<br>60     | mAdc                            |
|  |               |              |     |              | MMBFJ309<br>MMBFJ310, SMMBFJ310 |
| Gate–Source Forward Voltage<br>( $I_G = 1.0 \text{ mAdc}$ , $V_{DS} = 0$ )   | $V_{GS(f)}$   | -            | -   | 1.0          | Vdc                             |
| <b>SMALL–SIGNAL CHARACTERISTICS</b>  |               |              |     |              |                                 |
| Forward Transfer Admittance<br>( $V_{DS} = 10 \text{ Vdc}$ , $I_D = 10 \text{ mAdc}$ , $f = 1.0 \text{ kHz}$ )                 | $ Y_{fs} $    | 8.0          | -   | 18           | mmhos                           |
| Output Admittance<br>( $V_{DS} = 10 \text{ Vdc}$ , $I_D = 10 \text{ mAdc}$ , $f = 1.0 \text{ kHz}$ )                           | $ y_{os} $    | -            | -   | 250          | $\mu\text{mhos}$                |
| Input Capacitance<br>( $V_{GS} = -10 \text{ Vdc}$ , $V_{DS} = 0 \text{ Vdc}$ , $f = 1.0 \text{ MHz}$ )                         | $C_{iss}$     | -            | -   | 5.0          | pF                              |
| Reverse Transfer Capacitance<br>( $V_{GS} = -10 \text{ Vdc}$ , $V_{DS} = 0 \text{ Vdc}$ , $f = 1.0 \text{ MHz}$ )              | $C_{rss}$     | -            | -   | 2.5          | pF                              |
| Equivalent Short–Circuit Input Noise Voltage<br>( $V_{DS} = 10 \text{ Vdc}$ , $I_D = 10 \text{ mAdc}$ , $f = 100 \text{ Hz}$ ) | $\bar{e}_n$   | -            | 10  | -            | $\text{nV}/\sqrt{\text{Hz}}$    |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

MMBFJ309L, MMBFJ310L, SMMBFJ309L, SMMBFJ310L




Figure 1. Drain Current and Transfer Characteristics versus Gate-Source Voltage



Figure 2. Common-Source Output Admittance and Forward Transconductance versus Drain Current



Figure 3. On Resistance and Junction Capacitance versus Gate-Source Voltage

MMBFJ309L, MMBFJ310L, SMMBFJ309L, SMMBFJ310L




Figure 4. Common-Gate Y Parameter Magnitude versus Frequency




Figure 5. Common-Gate S Parameter Magnitude versus Frequency




Figure 6. Common-Gate Y Parameter Phase-Angle versus Frequency




Figure 7. S Parameter Phase-Angle versus Frequency

# MECHANICAL CASE OUTLINE

## PACKAGE DIMENSIONS

ON Semiconductor®



**SOT-23 (TO-236)**  
CASE 318-08  
ISSUE AS

DATE 30 JAN 2018

SCALE 4:1



**NOTES:**

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF THE BASE MATERIAL.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.

| DIM | MILLIMETERS |      |      | INCHES |       |       |
|-----|-------------|------|------|--------|-------|-------|
|     | MIN         | NOM  | MAX  | MIN    | NOM   | MAX   |
| A   | 0.89        | 1.00 | 1.11 | 0.035  | 0.039 | 0.044 |
| A1  | 0.01        | 0.06 | 0.10 | 0.000  | 0.002 | 0.004 |
| b   | 0.37        | 0.44 | 0.50 | 0.015  | 0.017 | 0.020 |
| c   | 0.08        | 0.14 | 0.20 | 0.003  | 0.006 | 0.008 |
| D   | 2.80        | 2.90 | 3.04 | 0.110  | 0.114 | 0.120 |
| E   | 1.20        | 1.30 | 1.40 | 0.047  | 0.051 | 0.055 |
| e   | 1.78        | 1.90 | 2.04 | 0.070  | 0.075 | 0.080 |
| L   | 0.30        | 0.43 | 0.55 | 0.012  | 0.017 | 0.022 |
| L1  | 0.35        | 0.54 | 0.69 | 0.014  | 0.021 | 0.027 |
| HE  | 2.10        | 2.40 | 2.64 | 0.083  | 0.094 | 0.104 |
| T   | 0°          | ---  | 10°  | 0°     | ---   | 10°   |

**RECOMMENDED SOLDERING FOOTPRINT**



**GENERIC MARKING DIAGRAM\***



XXX = Specific Device Code  
M = Date Code  
▪ = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present.

STYLE 1 THRU 5:  
CANCELLED

STYLE 6:  
PIN 1. BASE  
2. EMITTER  
3. COLLECTOR

STYLE 7:  
PIN 1. EMITTER  
2. BASE  
3. COLLECTOR

STYLE 8:  
PIN 1. ANODE  
2. NO CONNECTION  
3. CATHODE

STYLE 9:  
PIN 1. ANODE  
2. ANODE  
3. CATHODE

STYLE 10:  
PIN 1. DRAIN  
2. SOURCE  
3. GATE

STYLE 11:  
PIN 1. ANODE  
2. CATHODE  
3. CATHODE-ANODE

STYLE 12:  
PIN 1. CATHODE  
2. CATHODE  
3. ANODE

STYLE 13:  
PIN 1. SOURCE  
2. DRAIN  
3. GATE

STYLE 14:  
PIN 1. CATHODE  
2. GATE  
3. ANODE

STYLE 15:  
PIN 1. GATE  
2. CATHODE  
3. ANODE

STYLE 16:  
PIN 1. ANODE  
2. CATHODE  
3. CATHODE

STYLE 17:  
PIN 1. NO CONNECTION  
2. ANODE  
3. CATHODE

STYLE 18:  
PIN 1. NO CONNECTION  
2. CATHODE  
3. ANODE

STYLE 19:  
PIN 1. CATHODE  
2. ANODE  
3. CATHODE-ANODE

STYLE 20:  
PIN 1. CATHODE  
2. ANODE  
3. GATE

STYLE 21:  
PIN 1. GATE  
2. SOURCE  
3. DRAIN

STYLE 22:  
PIN 1. RETURN  
2. OUTPUT  
3. INPUT

STYLE 23:  
PIN 1. ANODE  
2. ANODE  
3. CATHODE

STYLE 24:  
PIN 1. GATE  
2. DRAIN  
3. SOURCE

STYLE 25:  
PIN 1. ANODE  
2. CATHODE  
3. GATE

STYLE 26:  
PIN 1. CATHODE  
2. ANODE  
3. NO CONNECTION

STYLE 27:  
PIN 1. CATHODE  
2. CATHODE  
3. CATHODE

STYLE 28:  
PIN 1. ANODE  
2. ANODE  
3. ANODE

|                         |                        |  |
|-------------------------|------------------------|--|
| <b>DOCUMENT NUMBER:</b> | <b>98ASB42226B</b>     | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>SOT-23 (TO-236)</b> | <b>PAGE 1 OF 1</b>   |

ON Semiconductor and ON are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Email Requests to: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**onsemi Website:** [www.onsemi.com](http://www.onsemi.com)

### TECHNICAL SUPPORT

**North American Technical Support:**  
Voice Mail: 1 800-282-9855 Toll Free USA/Canada  
Phone: 011 421 33 790 2910

**Europe, Middle East and Africa Technical Support:**

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[onsemi:](#)

[MMBFJ309LT1](#) [MMBFJ309LT1G](#) [MMBFJ310LT1](#) [MMBFJ310LT1G](#) [MMBFJ310LT3](#) [MMBFJ310LT3G](#)  
[SMMBFJ310LT3G](#) [SMMBFJ310LT1G](#) [SMMBFJ309LT1G](#)