

(0.635 mm) .025" PITCH • QTS/QSS SERIES

**QTS**  
Board Mates:  
QSS

**QSS**  
Board Mates:  
QTS

**QTS/QSS**  
Cable Mates:  
SQCD

**Standoffs:**  
SO



**NO. OF POSITIONS PER ROW**  
-025, -050, -075  
(50 total positions per bank)


**LEAD STYLE**  
Specify LEAD STYLE from Chart

**PLATING OPTION**  
-F = Gold flash on contact, Matte Tin on tail  
-L = 10 μm (0.25 μm) Gold on contact, Matte Tin on tail  
-C = 50 μm (1.27 mm) Electro-Polished Selective Gold on contact, Matte Tin on tail (passes 10 year MFG testing)

**OTHER OPTIONS**  
-K = (7.00 mm) .275" DIA Polyimide film Pick & Place Pad  
-TR = Tape & Reel  
-FR = Full Reel Tape & Reel (must order maximum quantity per reel; contact Samtec for quantity breaks)

**SPECIFICATIONS**

**Insulator Material:**  
Liquid Crystal Polymer  
**Contact Material:**  
Phosphor Bronze  
**Plating:**  
Au or Sn over 50 μm (1.27 μm) Ni  
**Current Rating:**  
**Contact:**  
1.8 A per pin (2 pins powered)  
**Ground Plane:**  
23.1 A per ground plane (1 ground plane powered)  
**Operating Temp Range:**  
-55 °C to +125 °C  
**Voltage Rating:**  
285 VAC  
**Max Cycles:**  
100



QTS LEAD STYLE	A	MATED HEIGHT WITH QSS
-01	(4.27) .168	(5.00) .197
-02	(7.26) .286	(8.00) .315

\*Processing conditions will affect mated height. See SO Series for board space tolerances.

View complete specifications at: [samtec.com?QTS](http://samtec.com?QTS)

**PROCESSING**



**Lead-Free Solderable:**  
Yes  
**QTS SMT Lead Coplanarity:**  
(0.10 mm) .004" max (025-075)  
**QSS SMT Lead Coplanarity:**  
(0.10 mm) .004" max (025-050)  
(0.15 mm) .006" max (075)\*  
\*(.004" stencil solution may be available; contact ipg@samtec.com)  
**Board Stacking:**  
For applications requiring more than two connectors contact ipg@samtec.com



**NO. OF POSITIONS PER ROW**  
-025, -050, -075  
(50 total positions per bank)

**PLATING OPTION**  
-F = Gold flash on contact, Matte Tin on tail  
-L = 10 μm (0.25 μm) Gold on contact, Matte Tin on tail  
-C = 50 μm (1.27 mm) Electro-Polished Selective Gold on contact, Matte Tin on tail (passes 10 year MFG testing)

**OTHER OPTIONS**  
-GP = Guide Holes for mating with QTS-RA  
-K = (8.25 mm) .325" DIA Polyimide Film Pick & Place Pad  
-TR = Tape & Reel  
-FR = Full Reel Tape & Reel (must order maximum quantity per reel; contact Samtec for quantity breaks)



**Note:**  
Some lengths, styles and options are non-standard, non-returnable.

See pg 46-47 for Right-Angle & Edge Mount options.

View complete specifications at: [samtec.com?QSS](http://samtec.com?QSS)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Samtec:

[QTS-025-02-L-D-A](#) [QTS-050-01-L-D-RA-WT](#) [QTS-025-01-L-D-RA](#) [QTS-075-01-L-D-A-K](#) [QTS-075-01-F-D-RA-WT](#)  
[QTS-050-01-F-D-RA-WT](#) [QTS-075-01-L-D-RA-WT](#) [QTS-050-02-F-D-A](#) [QTS-050-01-F-D-A](#) [QTS-050-02-L-D-A](#) [QTS-](#)  
[025-01-F-D-A](#) [QTS-025-02-F-D-A](#) [QTS-025-01-L-D-A-K-TR](#) [QTS-048-02-L-D-DP-A](#) [QTS-025-01-F-D-A-K-TR](#) [QTS-](#)  
[050-03-L-D-A](#) [QTS-050-02-L-D-A-K-TR](#) [QTS-025-01-L-D-A](#) [QTS-050-01-L-D-A](#) [QTS-050-01-L-D-A-K-TR](#) [QTS-075-](#)  
[01-L-D-A](#) [QTS-025-01-L-D-A-K](#) [QTS-075-02-L-D-A](#) [QTS-032-01-L-D-DP-RA-WT](#) [QTS-075-02-F-D-RA-WT](#) [QTS-025-](#)  
[02-L-D-A-K](#) [QTS-075-01-L-D-A-GP](#) [QTS-048-02-F-D-DP-A](#) [QTS-025-01-F-D-RA](#) [QTS-050-01-F-D-A-K](#) [QTS-050-03-](#)  
[C-D-A-K-TR](#) [QTS-075-01-F-D-RA-WT-P](#) [QTS-075-01-L-D-EM2](#) [QTS-075-02-L-D](#) [QTS-025-01-L-D-EM2](#) [QTS-025-03-](#)  
[L-D-A](#) [QTS-025-04-L-D-A](#) [QTS-050-01-L-D-EM2](#) [QTS-075-02-L-D-LC-K](#) [QTS-025-02-L-D](#) [QTS-075-01-L-D-LC](#) [QTS-](#)  
[075-03-L-D-A](#) [QTS-075-04-L-D-A](#) [QTS-025-01-F-D-EM2](#) [QTS-025-01-H-D-RA](#) [QTS-025-03-F-D-A-K-TR](#) [QTS-048-](#)  
[01-L-D-RA-DP-WT](#) [QTS-050-01-H-D-EM2](#) [QTS-075-01-F-D-A-TR](#) [QTS-075-02-L-D-A-K](#) [QTS-050-01-F-D-TR](#) [QTS-](#)  
[050-02-F-D-A-TR](#) [QTS-075-02-F-D-A](#) [QTS-016-01-L-D-DP-A](#) [QTS-025-04-F-D-A](#) [QTS-048-01-L-D-DP-A](#) [QTS-050-](#)  
[04-F-D-A](#) [QTS-050-04-F-D-A-TR](#) [QTS-075-01-F-D-LC](#) [QTS-050-01-F-D-EM2](#) [QTS-050-03-F-D-A-K](#) [QTS-050-03-F-D-](#)  
[A-TR](#) [QTS-075-01-H-D-EM2](#) [QTS-075-01-L-D-A-TR](#) [QTS-016-01-L-D-DP-RA](#) [QTS-025-03-F-D-A](#) [QTS-050-01-L-D](#)  
[QTS-050-04-F-D-A-K-TR](#) [QTS-075-01-F-D-EM2](#) [QTS-016-03-L-D-DP](#) [QTS-025-01-F-D-A-GP](#) [QTS-025-03-L-D](#) [QTS-](#)  
[025-03-L-D-A-K](#) [QTS-050-04-L-D-A](#) [QTS-075-01-F-D](#) [QTS-075-03-F-D](#) [QTS-075-03-F-D-A](#) [QTS-025-01-H-D-EM2](#)  
[QTS-025-01-L-D](#) [QTS-050-01-H-D-A](#) [QTS-050-02-F-D-A-K](#) [QTS-050-03-L-D-A-K](#) [QTS-025-01-F-D](#) [QTS-025-03-L-D-](#)  
[A-K-TR](#) [QTS-025-03-L-D-A-TR](#) [QTS-050-01-L-D-A-GP](#) [QTS-050-01-L-D-A-K](#) [QTS-075-01-F-D-A](#) [QTS-075-01-F-D-A-](#)  
[K](#) [QTS-075-04-L-D-A-K](#) [QTS-025-02-L-D-A-K-TR](#) [QTS-032-01-L-D-DP-A](#) [QTS-048-01-L-D-DP-EM2](#) [QTS-050-02-F-D](#)  
[QTS-075-01-F-D-LC-TR](#) [QTS-075-02-F-D-LC](#) [QTS-025-03-F-D](#) [QTS-050-01-L-D-TR](#) [QTS-075-03-L-D-A-K-TR](#)  
[QTS-025-01-L-D-A-GP](#)