



Neohm | Neohm NTC

TE Internal #: 1624348-2

15K Ω Thermistor, 0805, 4100 K Beta Value, Negative Temperature Coefficient, 5 %, Neohm NTC

[View on TE.com >](#)

Passive Components > Resistors > Thermistors



Resistance Value: 15K Ω

Package Size Code: 0805

Beta Value: 4100 K

Thermistor Mode of Operation: **Negative Temperature Coefficient**

Passive Component Tolerance: 5 %

Features

Product Type Features

Package Size Code	0805
-------------------	------

Electrical Characteristics

Resistance Value	15K Ω
Passive Component Tolerance	5 %

Dimensions

Passive Component Dimensions	2 x 1.25 x.5 mm
------------------------------	-----------------

Operation/Application

Thermistor Mode of Operation	Negative Temperature Coefficient
------------------------------	----------------------------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

Beta Value	4100 K
------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023 (235)

Candidate List Declared Against: JUNE 2023 (235)

Does not contain REACH SVHC

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1624345-1
NTC0805 5% 10K


TE Part # 1624352-1
NTC0805 5% 220R

TE Part # 1624368-2
NTC0805 5% 6K8

TE Part # 1624344-2
NTC0805 5% 100K

TE Part # 1624360-2
NTC0805 5% 3K0

Also in the Series | [Neohm NTC](#)




Thermistors(25)


Customers Also Bought



TE Part #2-1879021-3
SMW3 R82 5%



TE Part #1623783-4
SQM7 1K0 5% (METAL FILM)



TE Part #282856-4
TERMI-BLOK PCB MOUNT 4P



TE Part #170721-2
SOLISTRAND RINGTONG



TE Part #6-2301994-0
RJ45 JACK INT.MAG. 1GB LED 1X1



TE Part #3-2176349-1
CRGCQ 2512 3K3 1%



TE Part #2-1571999-9
ADP08STR04=PIANO DIP SWITCH



TE Part #796690-6
TERMI-BLOK PCB MOUNT 6P

Documents

Product Drawings

[NTC0805 5% 15K](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1624348-2_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1624348-2_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1624348-2_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



[Datasheets & Catalog Pages](#)

[1309350_PASSIVE_COMPONENT](#)

English

[Negative Temperature Coefficient Chip Thermistors - Type NTC Series](#)

English