

HUBER+SUHNER® DATA SHEET

Coaxial Cable Connector: 11_MMBX-50-2-1/111_N



Description

Straight cable plug for flexible cable

Interface standards
SUHNER-MMBX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 12.4 GHz

Mechanical Data

Centre contact crimped
Outer contact crimped
Weight 0.0007 kg

Environmental Data

Operating Temperature -55 °C to 155 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts

Centre contact	Copper Beryllium / Brass
Outer contact	Copper Beryllium Alloy
Body	Brass
Insulator	PFA / PTFE
Crimp ferrule	Copper

Surface Plating

Gold Plating (Nickel underplated)
SUCOPRO Plating
SUCOPRO Plating
Gold Plating (without Nickel underplating)

Related Documents

Outline drawing	DOU-00006163
Catalogue drawing	DOU-00006165
Assembly instruction	DOC-0000179377

Ordering Information

Single package 11_MMBX-50-2-1/111_NE

Additional Information

Suitable cables RG_316_U, RG_188_A/U, RG_174_U

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions